



SIMATIC S7-1200, Digital input SM 1221, 8 DI, 24 V DC, Sink/Source

General information	
Product type designation	SM 1221, DI 8x24 V DC
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V
Input current	
from backplane bus 5 V DC, max.	105 mA
Digital inputs	
<ul style="list-style-type: none"> from load voltage L+ (without load), max. 	4 mA; per channel
Output voltage	
Power supply to the transmitters	
<ul style="list-style-type: none"> present 	Yes
Power loss	
Power loss, typ.	1.5 W
Digital inputs	
Number of digital inputs	8
<ul style="list-style-type: none"> in groups of 	2
Input characteristic curve in accordance with IEC 61131, type 1	Yes
Number of simultaneously controllable inputs	
all mounting positions	
— up to 40 °C, max.	8
horizontal installation	
— up to 40 °C, max.	8
— up to 50 °C, max.	8
vertical installation	
— up to 40 °C, max.	8
Input voltage	
<ul style="list-style-type: none"> Rated value (DC) for signal "0" for signal "1" 	24 V 5 V DC at 1 mA 15 V DC at 2.5 mA
Input current	
<ul style="list-style-type: none"> for signal "0", max. (permissible quiescent current) for signal "1", min. for signal "1", typ. 	1 mA 2.5 mA 4 mA
Input delay (for rated value of input voltage)	
for standard inputs	
— parameterizable	Yes; 0.2 ms, 0.4 ms, 0.8 ms, 1.6 ms, 3.2 ms, 6.4 ms and 12.8 ms, selectable in groups of four

for interrupt inputs	
— parameterizable	Yes
Cable length	
• shielded, max.	500 m
• unshielded, max.	300 m
Interrupts/diagnostics/status information	
Alarms	
• Diagnostic alarm	Yes
Diagnostics indication LED	
• for status of the inputs	Yes
Potential separation	
Potential separation digital inputs	
• between the channels, in groups of	2
Degree and class of protection	
IP degree of protection	IP20
Standards, approvals, certificates	
CE mark	Yes
CSA approval	Yes
UL approval	Yes
cULus	Yes
FM approval	Yes
RCM (formerly C-TICK)	Yes
KC approval	Yes
Marine approval	Yes
Ecological footprint	
• environmental product declaration	Yes
Global warming potential	
— global warming potential, (total) [CO2 eq]	123 kg
— global warming potential, (during production) [CO2 eq]	12.1 kg
— global warming potential, (during operation) [CO2 eq]	111 kg
— global warming potential, (after end of life cycle) [CO2 eq]	-0.434 kg
Ambient conditions	
Free fall	
• Fall height, max.	0.3 m; five times, in product package
Ambient temperature during operation	
• min.	-20 °C
• max.	60 °C
• horizontal installation, min.	-20 °C
• horizontal installation, max.	60 °C
• vertical installation, min.	-20 °C
• vertical installation, max.	50 °C
• permissible temperature change	5°C to 55°C, 3°C / minute
Ambient temperature during storage/transportation	
• min.	-40 °C
• max.	70 °C
Air pressure acc. to IEC 60068-2-13	
• Storage/transport, min.	660 hPa
• Storage/transport, max.	1 080 hPa
Relative humidity	
• Operation at 25 °C without condensation, max.	95 %
Connection method	
required front connector	Yes
Mechanics/material	
Enclosure material (front)	
• Plastic	Yes
Dimensions	

Width	45 mm
Height	100 mm
Depth	75 mm
Weights	
Weight, approx.	170 g

Classifications		
	Version	Classification
eClass	14	27-24-22-04
eClass	12	27-24-22-04
eClass	9.1	27-24-22-04
eClass	9	27-24-22-04
eClass	8	27-24-22-04
eClass	7.1	27-24-22-04
eClass	6	27-24-22-04
ETIM	10	EC001419
ETIM	9	EC001419
ETIM	8	EC001419
ETIM	7	EC001419
IDEA	4	3566
UNSPSC	15	32-15-17-05

Approvals / Certificates

General Product Approval



[Miscellaneous](#)

[Manufacturer Declaration](#)



General Product Approval **EMV** **For use in hazardous locations**



[China RoHS](#)

[Manufacturer Declaration](#)



For use in hazardous locations **Maritime application**

[FM](#)



[Miscellaneous](#)

[CCC-Ex](#)



Maritime application



[NK / Nippon Kaiji Kyokai](#)



[CCS \(China Classification Society\)](#)

[KR \(Korean Register of Shipping\)](#)

Environment



last modified:

4/6/2025

