

Siemens
EcoTech



SITOP PSE200U/4X3-10A/SEO

SITOP PSE200U 10 A selectivity module 4-channel input: 24 V DC/40 A output: 24 V DC/4x 10 A threshold adjustable 3-10 A with status message for each output

General information	
Technical Product Detail Page	https://i.siemens.com/1P6EP1961-2BA41
input	
type of the power supply network	Controlled DC voltage
supply voltage at DC rated value	24 V
input voltage at DC	22 ... 30 V
overvoltage overload capability	35 V
input current at rated input voltage 24 V rated value	40 A
output	
voltage curve at output	controlled DC voltage
formula for output voltage	$V_{in} - \text{approx. } 0.2 \text{ V}$
relative overall tolerance of the voltage note	In accordance with the supplying input voltage
number of outputs	4
output current up to 60 °C per output rated value	10 A
adjustable current response value current of the current-dependent overload release	3 ... 10 A
type of response value setting	via potentiometer
response delay maximum	5 s
product feature parallel switching of outputs	No
type of outputs connection	simultaneous switch-on of all outputs after power-up of the supply voltage > 20 V, delay time of 25 ms, 100 ms, or "load-optimized" via DIP switch configurable for sequential switch-on
efficiency	
efficiency in percent	99 %
power loss [W] at rated output voltage for rated value of the output current typical	10 W
switch-off characteristic	
switching characteristic	
• of the excess current	$I_{out} = 1.0 \dots 1.5 \times \text{set value}$, switch-off after approx. 5 s
• of the current limitation	$I_{out} = 1.5 \times \text{set value}$, switch-off after typ. 100 ms
• of the immediate switch-off	$I_{out} > \text{set value}$ and $V_{in} < 20 \text{ V}$, switch-off after approx. 0.5 ms
residual current at switch-off typical	1 mA
design of the reset device/resetting mechanism	via sensor per output
remote reset function	non-isolated 24 V input (signal level "high" at > 15 V)
protection and monitoring	
fuse protection type at input	15 A per output (not accessible)
display version for normal operation	Three-color LED per output: green LED for "Output switched through"; yellow

	LED for "Output switched off manually"; red LED for "Output switched off due to overcurrent"
design of the switching contact for signaling function	Status signal output (pulse/pause signal, can be evaluated via Simatic function block)
safety	
galvanic isolation between input and output at switch-off	No
standard for safety	according to EN 62368-1
operating resource protection class	Class III
protection class IP	IP20
standard	
<ul style="list-style-type: none"> • for emitted interference • for interference immunity 	EN 55022 Class B EN 61000-6-2
standards, specifications, approvals	
certificate of suitability	
<ul style="list-style-type: none"> • CE marking • UL approval 	Yes Yes; UL-Recognized (UL 2367) File E328600; cULus-Listed (UL 508, CSA C22.2 No. 107.1) File E197259
<ul style="list-style-type: none"> • UKCA marking • EAC approval 	Yes Yes
type of certification	
<ul style="list-style-type: none"> • CB-certificate 	Yes
MTBF at 40 °C	540 979 h
standards, specifications, approvals hazardous environments	
certificate of suitability	
<ul style="list-style-type: none"> • IECEx • ATEX 	No No
standards, specifications, approvals marine classification	
shipbuilding approval	Yes
Marine classification association	
<ul style="list-style-type: none"> • American Bureau of Shipping Europe Ltd. (ABS) • Det Norske Veritas (DNV) 	Yes Yes
standards, specifications, approvals Environmental Product Declaration	
Environmental Product Declaration	Yes
global warming potential [CO2 eq]	
<ul style="list-style-type: none"> • total • during manufacturing • during operation • after end of life 	322 kg 8.8 kg 313 kg 0.2 kg
Siemens Eco Profile (SEP)	Siemens EcoTech
ambient conditions	
ambient temperature	
<ul style="list-style-type: none"> • during operation • during transport • during storage 	-25 ... +60 °C; with natural convection -40 ... +85 °C -40 ... +85 °C
environmental category according to IEC 60721	Climate class 3K3, 5 ... 95% no condensation
connection method	
type of electrical connection	screw terminal
<ul style="list-style-type: none"> • at input • at output • for auxiliary contacts • for signaling contact 	+24 V: 2 screw terminals for 0.5 ... 16 mm ² ; 0 V: 2 screw terminals for 0.5 ... 4 mm ² Output 1 ... 4: 1 screw terminal each for 0.5 ... 4 mm ² Remote reset: 1 screw terminal for 0.5 ... 4 mm ² 1 screw terminal for 0.5 ... 4 mm ²
mechanical data	
width × height × depth of the enclosure	72 × 80 × 72 mm
installation width × mounting height	72 mm × 180 mm
required spacing	
<ul style="list-style-type: none"> • top • bottom • left • right 	50 mm 50 mm 0 mm 0 mm

fastening method	Snaps onto DIN rail EN 60715 35x7.5/15
<ul style="list-style-type: none"> • DIN-rail mounting • S7 rail mounting • wall mounting 	Yes No No
housing can be lined up	Yes
net weight	0.2 kg

accessories

mechanical accessories	Device identification label 20 mm × 7 mm, TI-grey 3RT2900-1SB20
------------------------	---

further information internet links

internet link	
<ul style="list-style-type: none"> • to website: Industry Mall • to web page: selection aid TIA Selection Tool • to web page: power supplies • to website: CAx-Download-Manager • to website: Industry Online Support 	https://mall.industry.siemens.com https://www.siemens.com/tstcloud https://siemens.com/sitop https://siemens.com/cax https://support.industry.siemens.com

identification link	Yes; acc. to IEC 61406-1:2022
---------------------	-------------------------------

additional information

other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)
-------------------	---

security information

security information	<p>Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement - and continuously maintain - a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under https://www.siemens.com/cert. (V4.7)</p>
----------------------	---

Classifications

	Version	Classification
eClass	14	27-37-18-02
eClass	12	27-37-18-02
eClass	9.1	27-37-18-02
eClass	9	27-37-18-02
eClass	8	27-37-18-02
eClass	7.1	27-37-18-02
eClass	6	27-37-18-02
ETIM	10	EC001440
ETIM	9	EC001440
ETIM	8	EC001440
ETIM	7	EC001440
IDEA	4	4727
UNSPSC	15	39-12-15-21

Approvals Certificates

General Product Approval



[Manufacturer Declaration](#)



EG-Konf.



[Declaration of Conformity](#)

[China RoHS](#)



[Miscellaneous](#)



last modified:

5/5/2026