

T-1 3/4 (5mm) INFRARED EMITTING DIODE

Part Number: L-7113F3C


Features

- Mechanically and spectrally matched to the phototransistor.
- RoHS compliant.

Description

F3 Made with Gallium Arsenide Infrared Emitting diodes.

Package Dimensions



- 1. All dimensions are in millimeters (inches).
- 2. Tolerance is ±0.25(0.01") unless otherwise noted.
- Lead spacing is measured where the leads emerge from the package.
 The specifications, characteristics and technical data described in the datasheet are subject to change without prior notice.

DATE: JUL/03/2014 SPEC NO: DSAB6712 **REV NO: V.22A** PAGE: 1 OF 6 ERP: 1101004993 **APPROVED: WYNEC CHECKED: Allen Liu** DRAWN: L.Q.Xie

Selection Guide

| Part No. | Dice | Lens Type | Po (mW/sr) [2] @ 20mA | | Po (mW/sr) [2] @ 50mA | | Viewing Angle [1] |
|-----------|-----------|-------------|--------------------------|------|--------------------------|------|----------------------|
| | | | Min. | Тур. | Min. | Тур. | 201/2 |
| L-7113F3C | F3 (GaAs) | Water Clear | 15 | 30 | 55 | 100 | - 20° |
| | | | *8 | *20 | *25 | *50 | |

Notes:

- 1. θ 1/2 is the angle from optical centerline where the luminous intensity is 1/2 of the optical peak value.

Electrical / Optical Characteristics at TA=25°C

| Parameter | P/N | Symbol | Тур. | Max. | Units Test Condition | | |
|--------------------------|-----|--------|------|------|----------------------|---------------------|--|
| Forward Voltage [1] | F3 | VF | 1.2 | 1.6 | V | IF=20mA | |
| Reverse Current | F3 | lR | | 10 | uA | V _R = 5V | |
| Capacitance | F3 | С | 90 | | pF | VF=0V;f=1MHz | |
| Peak Spectral Wavelength | F3 | λP | 940 | | nm IF=20mA | | |
| Spectral Bandwidth | F3 | Δλ1/2 | 50 | | nm | IF=20mA | |

- 1. Forward Voltage: +/-0.1V.
- 2. Wavelength value is traceable to the CIE127-2007 compliant national standards.

Absolute Maximum Ratings at TA=25°C


| Parameter | Symbol | F3 | Units | | | |
|-----------------------------|---------------------|------------|-------|--|--|--|
| Power dissipation | Pp | 80 | mW | | | |
| DC Forward Current | lF | 50 | mA | | | |
| Peak Forward Current [1] | iFS | 1.2 | A | | | |
| Reverse Voltage | VR | 5 | V | | | |
| Operating Temperature | TA | -40 To +85 | °C | | | |
| Storage Temperature | Тѕтс | -40 To +85 | °C | | | |
| Lead Solder Temperature [2] | 260°C For 3 Seconds | | | | | |
| Lead Solder Temperature [3] | 260°C For 5 Seconds | | | | | |

Notes:


- 1. 1/100 Duty Cycle, 10µs Pulse Width.
- 2. 2mm below package base.
- 3. 5mm below package base.


DATE: JUL/03/2014 SPEC NO: DSAB6712 **REV NO: V.22A** PAGE: 2 OF 6 **APPROVED: WYNEC CHECKED: Allen Liu** DRAWN: L.Q.Xie ERP: 1101004993


Radiant Intensity/ luminous flux: +/-15%.
 *Radiant Intensity value is traceable to the CIE127-2007 compliant national standards.




L-7113F3C










SPEC NO: DSAB6712 REV NO: V.22A DATE: JUL/03/2014 PAGE: 3 OF 6
APPROVED: WYNEC CHECKED: Allen Liu DRAWN: L.Q.Xie ERP: 1101004993




Terms and conditions for the usage of this document

- 1. The information included in this document reflects representative usage scenarios and is intended for technical reference only.
- 2.The part number, type, and specifications mentioned in this document are subject to future change and improvement without notice. Before production usage customer should refer to the latest datasheet for the updated specifications.
- 3. When using the products referenced in this document, please make sure the product is being operated within the environmental and electrical limits specified in the datasheet. If customer usage exceeds the specified limits, Kingbright will not be responsible for any subsequent issues.
- 4. The information in this document applies to typical usage in consumer electronics applications. If customer's application has special reliability requirements or have life-threatening liabilities, such as automotive or medical usage, please consult with Kingbright representative for further assistance.
- 5. The contents and information of this document may not be reproduced or re-transmitted without permission by Kingbright.
- 6.All design applications should refer to Kingbright application notes available at http://www.kingbright.com/application notes


SPEC NO: DSAB6712 REV NO: V.22A DATE: JUL/03/2014 PAGE: 4 OF 6
APPROVED: WYNEC CHECKED: Allen Liu DRAWN: L.Q.Xie ERP: 1101004993

PRECAUTIONS

1. The lead pitch of the LED must match the pitch of the mounting holes on the PCB during component placement. Lead—forming may be required to insure the lead pitch matches the hole pitch. Refer to the figure below for proper lead forming procedures. (Fig. 1)




- "()" Correct mounting method "imes" Incorrect mounting method
- 2. When soldering wire to the LED, use individual heat—shrink tubing to insulate the exposed leads to prevent accidental contact short—circuit. (Fig.2)
- 3. Use stand—offs (Fig.3) or spacers (Fig.4) to securely position the LED above the PCB.




- 4. Maintain a minimum of 3mm clearance between the base of the LED lens and the first lead bend. (Fig. 5 and 6)
- 5. During lead forming, use tools or jigs to hold the leads securely so that the bending force will not be transmitted to the LED lens and its internal structures. Do not perform lead forming once the component has been mounted onto the PCB. (Fig. 7)

SPEC NO: DSAB6712 APPROVED: WYNEC REV NO: V.22A CHECKED: Allen Liu DATE: JUL/03/2014 DRAWN: L.Q.Xie PAGE: 5 OF 6 ERP: 1101004993


6. Do not bend the leads more than twice. (Fig. 8)



7. During soldering, component covers and holders should leave clearance to avoid placing damaging stress on the LED during soldering.



- 8. The tip of the soldering iron should never touch the lens epoxy.
- 9. Through—hole LEDs are incompatible with reflow soldering.
- 10. If the LED will undergo multiple soldering passes or face other processes where the part may be subjected to intense heat, please check with Kingbright for compatibility.
- 11. Recommended Wave Soldering Profiles:



Notes:

- 1.Recommend pre-heat temperature of 105°C or less (as measured with a thermocouple attached to the LED pins) prior to immersion in the solder wave with a maximum solder bath temperature of 260°C
- 2.Peak wave soldering temperature between 245°C \sim 255°C for 3 sec (5 sec max).
- 3.Do not apply stress to the epoxy resin while the temperature is above 85°C.
- 4.Fixtures should not incur stress on the component when mounting and during soldering process. 5.SAC 305 solder alloy is recommended.
- 6.No more than one wave soldering pass.

SPEC NO: DSAB6712 REV NO: V.22A DATE: JUL/03/2014 PAGE: 6 OF 6
APPROVED: WYNEC CHECKED: Allen Liu DRAWN: L.Q.Xie ERP: 1101004993