

GU10 Glass PAR16 4.4W (50W) 4000K 400lm Non-Dimmable Lamp*Quick Order Code: 343715 / Page: 1***Product Details**

Partcode: ILGU104.4N04KWDNA

Quick Order Code: 343715

Range Name: Classic

Placement / Application: Indoor, General Lighting

Market Segment: Commercial indoor, Residential indoor

Product Type: GU10

Warranty: 3 Years

CE / RoHS: Yes

Physical Data

Lamp Base: GU10 PAR16

Base Type: GU10

Globe Finish: Clear

Spot Type: SMD with "COB like effect"

Optic: Designed to give a Halogen look

Material: Glass, Plastic

Construction: Glass and Plastic heat-sink, Injection moulded diffuser

Physical Data

Length: 54mm

Width: 50mm

Weight (Unpackaged Single Unit): 42g

Lamp or Luminaire Shape: Round

Lamp Fixing: Downlight

Electrical Data

Voltage Range: 220-240V

Power Consumption: 4.4 Watts

Driver included: Yes

Driver IC Manufacturer: Silergy

Electric Current: AC

Ampage: 41.00mA

Frequency Range: 50 Hz

Power Factor: ≥ 0.40

Wattage Equivalent: 50 Watts

Dimming: Non-dimmable

LVD Certified: Yes

EN: EN-62560

Light Data

Useful Lumens: 360lm (Rated luminous flux in a 90° cone)

Lumens: 400lm

Lumens per Watt: 91.0lm/W

Peak Intensity: 890Cd

Beam Angle: 36°

Correlated Colour Temperature (CCT): 4,000k

Colour Temperature: White

Colour Rendering Index (CRI): ≥ 80

LED Manufacturer: Seoul

LED Type: Surface mounted device (SMD)

Instant on - Less than 1 second: Yes

Lifetime: 25,000 hrs

Switching Cycles: >12,500 X

Environmental

Energy Rating: A+

Lowest Operating Temperature: -20 degrees

Maximum Operating Temperature: 40 degrees

Hg 0% (Mercury Free): Yes

Packaging



EAN Barcode (unit of 1): 5055788212133

Packaged Weight (Unit of 1): 63g

Length (unit of 1): 65mm

Width (unit of 1): 54mm

Depth (unit of 1): 54mm

Outer packaging info available on website

Product data last updated on: Friday, May 13, 2016 - 13:28