

Candle Omni-Lamp 2W (25W) 2700K 250lm B22 Non-Dimmable 300 deg Beam Angle*Quick Order Code: 544935 / Page: 1*

This cutting edge A++, 2W retro-fit Integral LED Candle (large bayonet base) from the Omni-Lamp range delivers a warm white light and brightness, similar to a 25W filament bulb. It has the appearance, feel and weight of a traditional light bulb. Featuring an LED filament, which enables a super-wide 300 degree beam angle. A decorative lamp ideal for living rooms, dining rooms, bedrooms and hotels, in classic or modern wall or floor/table lamp fittings and chandeliers.

Product Details

Partcode: ILB35B22C2.0N27KCCWA

Quick Order Code: 544935

Range Name: Omni

Product Type: Candle

Warranty: 2 Years

CE / RoHS: Yes

Physical Data

Lamp Base: B22

Base Type: Bayonet cap

Globe Type: Candle

Globe Finish: Clear

Material: Glass

Physical Data

Length: 93mm
Width: 35mm
Weight (Unpackaged Single Unit): 13g
Lamp or Luminaire Shape: Oval
Lamp Fixing: Pendant, Chandelier, Wall

Electrical Data

Voltage Range: 220-240V
Power Consumption: 2.0 Watts
Driver included: Yes
Electric Current: AC
Ampage: 19.00mA
Frequency Range: 50 Hz
Power Factor: ≥ 0.45
Wattage Equivalent: 25 Watts
Dimming: Non-dimmable
LVD Certified: Yes
EN: EN-62560

Light Data

Lumens: 250lm
Lumens per Watt: 125.0lm/W
Beam Angle: 300°
Correlated Colour Temperature (CCT): 2,700k
Colour Temperature: Warm
Colour Rendering Index (CRI): ≥ 80
LED Type: Filament chip
Instant on - Less than 1 second: Yes
Lifetime: 15,000 hrs
Switching Cycles: $>7,500$ X

Environmental

Energy Rating: A++

Lowest Operating Temperature: -20 degrees

Maximum Operating Temperature: 40 degrees

IP (Ingress Protection) Rating: IP20

Hg 0% (Mercury Free): Yes

Packaging



EAN Barcode (unit of 1): 5055788210894

Packaged Weight (Unit of 1): 28g

Length (unit of 1): 120mm

Width (unit of 1): 40mm

Depth (unit of 1): 40mm

Outer packaging info available on website

Product data last updated on: Friday, May 13, 2016 - 13:27