HF14FF

MINIATURE HIGH POWER RELAY



File No.:E134517



File No.:R50140759



File No.:CQC10002046169



Features

- 10A switching capability
- 5kV dielectric strength (between coil and contacts)
- Sockets available
- Plastic sealed and flux proofed types available
- UL insulation system: Class F available
- Environmental friendly product (RoHS compliant)
- Outline Dimensions: 29.0mm x 13.0mm x 26.0mm

CONTACT DAT	A
Contact arrangement	1A, 1C
Contact resistance ¹⁾	50mΩ max.(at 1A 24VDC)
Contact material	AgSnO ₂ , AgNi, AgCdO
Contact rating	Resistive: 10A 277VAC/30VDC
Contact rating	TV-5 120VAC
Max. switching voltage	277VAC / 30VDC
Max. switching current	10A
Max. switching power	2770VA / 300W
Mechanical endurance	1 x 10 ⁷ ops
	1 x 10 ⁵ ops (10A 277VAC,
Electrical endurance	Resistive load, Room temp., 1s on 9s off)
	1 x 10 ⁵ OPS (10A 30VDC, Resistive load, Room temp., 1s on 9s off)

Notes:1) The data shown above are initial values.
2) For plastic sealed type, the venting-hole should be excised in electrical endurance test.

CHAR	ACTE	RISTICS		
Insulation	Insulation resistance		1000MΩ (at 500VDC	
Dielectric strength	Between coil & contacts		5000VAC 1min	
	Between open contacts		1000VAC 1mi	
Operate time (at nomi. volt.)		omi. volt.)	15ms max.	
Release time (at nomi. volt.)		omi. volt.)	5ms max.	
Vibration resistance		Э	10Hz to 55Hz 1.5mm DA	
Shock resistance		Functional	98m/s	
		Destructive	980m/s²	
Humidity			5% to 85% RH	
Ambient temperature		re	-40°C to 70°C	
Termination			PCB	
Unit weight			Approx. 18	
Construction			Plastic sealed, Flux proofed	

- Notes: 1) The data shown above are initial values.
 - 2) Please find coil temperature curve in the characteristic curves below.
 - 3) UL insulation system: Class F, Class B.

COIL	
Coil power	Approx. 530mV

COIL D	at 23°C			
Nominal Voltage VDC	Pick-up Voltage VDC max. ²⁾	Drop-out Voltage VDC min. ²⁾	Max. Voltage VDC ³⁾	Coil Resistance Ω
3	2.25	0.3	4.2	17 x (1±10%)
5	3.75	0.5	7.0	47 x (1±10%)
6	4.50	0.6	8.4	68 x (1±10%)
9	6.75	0.9	12.6	160 x (1±10%)
12	9.00	1.2	16.8	275 x (1±10%)
18	13.5	1.8	25.2	620 x (1±10%)
24	18.0	2.4	33.6	1100 x (1±10%)
48	36.0	4.8	67.2	4170 x (1±10%)
60	45.0	6.0	84.0	7000 x (1±10%)

Notes: 1) When requiring pick-up voltage < 75% of nominal voltage, special order allowed.

- 2) The data shown above are initial values.
- 3) Maximum voltage refers to the maximum voltage which relay coil could endure in a short period of time.
- Under ambient temperature, applying more than 80% of rating voltage to coil, relay will take action accordingly. But in order to meet the stated product performance, please apply rated voltage to coli.

SAFETY APPROVAL RATINGS					
UL/CUL	AgCdO	1 Form A	TV-5 120VAC 10A 277VAC General purpose 10A 30VDC Resistive 1/3HP 250VAC 1/4HP 125VAC		
		1 Form C	TV-5 120VAC 10A 277VAC General purpose 10A 30VDC Resistive 1/3HP 250VAC NO:1/4HP 125VAC		
	AgSnO ₂ AgNi		10A 277VAC General purpose 10A 30VDC Resistive 1/3HP 250VAC 1/4HP 125VAC TV-5 120VAC		
ΤÜV	AgCdO AgSnO2		10A 250VAC 10A 30VDC		

Notes: 1) All values unspecified are at room temperature.

2) Only typical loads are listed above. Other load specifications can be available upon request.



ISO9001, ISO/TS16949, ISO14001, OHSAS18001, IECQ QC 080000 CERTIFIED

2018 Rev. 1.00

ORDERING INFORMATION HF14FF / 012 -1H (XXX) **Type** Coil voltage 3, 5, 6, 9, 12, 18, 24, 48, 60VDC **Contact arrangement 1H**: 1 Form A 1Z: 1 Form C S: Plastic sealed(No smoky-gray cover) Construction 1) Nil: Flux proofed **Contact material** T: AgSnO₂ 3: AgNi Nil: AgCdO Insulation standard F: Class F Nil: Class B Special code⁴⁾ XXX: Customer special requirement Nil: Standard

Notes: 1) We recommend flux proofed types for a clean environment (free from contaminations like H₂S, SO₂, NO₂, dust, etc.).

We suggest to choose plastic sealed types and validate it in real application for an unclean environment (with contaminations like H₂S, SO₂, NO₂, dust, etc.).

2) Contact is recommended for suitable condition and specifications if water cleaning or surface process is involved in assembling relays on PCB.

Unit: mm

- 3) The standard type is made of black cover. If smoke cover is required, please add a special suffix (611) when ordering. Please take note that smoke cover is only available for flux proofed type.
- 4) The customer special requirement express as special code after evaluating by Hongfa.

OUTLINE DIMENSIONS, WIRING DIAGRAM AND PC BOARD LAYOUT

1 Form A 1 Form C 29 max 29 max 13max 13max Outline 26 max max **Dimensions** 261 0.6 ± 0.1 0.5 ± 0.1 0.5 ± 0.1 0.25 ± 0.1 0.5 ± 0 (Bottom view) (Bottom view) Wiring Diagram (Bottom view) 20 **PCB** Layout (Bottom view)

Remark: 1) In case of no tolerance shown in outline dimension: outline dimension \leq 1mm, tolerance should be ±0.2mm; outline dimension >1mm and \leq 5mm, tolerance should be ±0.3mm; outline dimension >5mm, tolerance should be ±0.4mm.

5xØ1.3


2) The tolerance without indicating for PCB layout is always ±0.1mm.

4xØ1.3

3) The width of the gridding is 2.5mm.

CHARACTERISTIC CURVES

ENDURANCE CURVE




Test conditions:

NO, Resistive load,

Flux proofed, Room temp., 1s on 9s off.

COIL TEMPERATURE RISE



Relay Sockets



Features


- The insulation resistance is 1000MΩ
- Three mounting types are available: PCB, screw mounting and DIN rail mounting.
- With finger protection device
- Many kinds of plug-in modules are available with the function of energizing indication and wiring protection.
- Environmental friendly product (RoHS compliant)

CHARACTERISTICS

Туре	Nominal Voltage	Nominal Current	Ambient Temperature	Dielectric Strength s.	Screw Torque	Wire Strip Length	Unit weight
14FF-1Z-A1	250VAC	10A	-40 °C to 70°C	5000VAC		_	Approx. 3g
14FF-1Z-C2	250VAC	10A	-40 °C to 70°C	5000VAC	0.6N · m	7mm	Approx. 33g
14FF-1Z-C3	250VAC	10A	-40 °C to 70°C	5000VAC	0.6N · m	7mm	Approx. 39g

OUTLINE DIMENSIONS, WIRING DIAGRAM AND PC BOARD LAYOUT

Unit: mm



OUTLINE DIMENSIONS, WIRING DIAGRAM AND PC BOARD LAYOUT Unit: mm Wiring Diagram / PCB Layout Socket **Outline Dimensions** Components Available 14FF-1Z-C2 12 NC plastic retainer 14FF-H6 14 NO marker 14FF-M1 plug-in module HFAA to HFHU* 0 Screw terminal, A2 COIL PCB or Screw mounting (Top View) With finger protection device (Top View) 61 14FF-1Z-C3 43 [22] NC 24.2 СОМ plastic retainer 14FF-H6 11 0 24 NO marker 14FF-M1 plug-in module HFAA to HFHU* Screw terminal COIL DIN rail or Screw mounting With finger protection device 43 (Top View) (Top View)

Notes: * Please refer to the product datasheet if plug-in module is required.


DIMENSION OF RELATED COMPONENT (AVAILABLE)

Unit: mm

Retainer

0.8 30.6 2xR1.4


14FF-H2 (Metallic retainer)



14FF-H6 (Plastic retainer)

Marker

14FF-M1



Things to be noticed when selecting sockets:

- 1. Please choose suitable relay socket according to the actual mounting environment, relay contact poles and terminal layout. If there is any query on selection, please contact Hongfa for the technical service.
- 2. Socket which can be mounted with markers is furnished with a marker; as for other related components, they should be selected separately. Please do give clear indication of the types of relay sockets and related components you choose while placing order.
- 3. The above is only an example of typical socket and related component type which is suitable to HF14FF relay. If you have any special requirements, please contact us.
- 4. Main outline dimension(L, W, H) \geqslant 50mm, tolerance should be \pm 1mm; outline dimension >20mm and <50mm, tolerance should be \pm 0.5mm; outline dimension \leqslant 20mm, tolerance should be \pm 0.3mm.
- 5. DIN rail mounting: recommend to use standard rail $35\times7.5\times1$ mm, $35\times15\times1$ mm.

Disclaimer

The specification is for reference only. See to "Terminology and Guidelines" for more information. Specifications subject to change without notice. We could not evaluate all the performance and all the parameters for every possible application. Thus the user should be in a right position to choose the suitable product for their own application. If there is any query, please contact Hongfa for the technical service. However, it is the user's responsibility to determine which product should be used only.

© Xiamen Hongfa Electroacoustic Co., Ltd. All rights of Hongfa are reserved.