




# ANTISTAT


## Conductive Laminating Film Sheets

### Features

- Our ESD laminating sheets will work with any standard document laminating system found from any office supply stores
- Made from PET / EVA
- 80 micron thickness
- Grammage of 95gram/m<sup>2</sup>
- Elongation: MDI61% / TD120



### Construction



### Specification

Details	Standard	Typical Value
Surface Resistance R <sub>s</sub>	EN 61340-5-1	<10 <sup>9</sup> Ω/sq
Decay Time	EN 61340-5-1	<2 secs

Product Code	Description	Size	Pack Size
105-0069	Conductive Laminating Sheets	A4	Pack of 100
105-0066	Conductive Laminating Sheets	A3	Pack of 100

**Important Notice:** This data sheet and its contents (the "Information") belong to Antistat or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but Antistat assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where Antistat was aware of the possibility of such loss or damage arising) is excluded. © Antistat.



WWW.ANTISTAT.CO.UK