



■ Features :

- 180-264VAC input only
- Fully encapsulated with IP67 level (Note.5)
- Protections:Short circuit / Overload / Over voltage / Over temperature
- Cooling by free air convection
- Class Ⅱ power unit, no FG
- Pass LPS
- 100% full load burn-in test
- Suitable for LED lighting and moving sign applications
- High reliability / Low cost
- 2 years warranty

SPECIFICATION

₽ F 110		IP67	TOUTH OF THE PROPERTY OF THE P	CB	(
----------------	--	------	--	----	---	--

MODEL		LPH-18-12	LPH-18-24	LPH-18-36			
	DC VOLTAGE	12V	24V	36V			
ОИТРИТ	RATED CURRENT	1.5A	0.75A	0.5A			
	CURRENT RANGE	0 ~ 1.5A	0 ~ 0.75A	0 ~ 0.5A			
	RATED POWER	18W	18W	18W			
	RIPPLE & NOISE (max.) Note.2	120mVp-p	150mVp-p	200mVp-p			
	VOLTAGE TOLERANCE Note.3	3 ±3.0%					
	LINE REGULATION	±1.0%					
	LOAD REGULATION	±2.0%					
	SETUP, RISE TIME	1500ms, 30ms / 230VAC					
	HOLD UP TIME (Typ.)	50ms/230VAC at full load					
	VOLTAGE RANGE	180 ~ 264VAC 254 ~ 370VDC					
	FREQUENCY RANGE	47 ~ 63Hz					
INDUT	EFFICIENCY(Typ.)	77%	82%	83%			
INPUT	AC CURRENT	0.3A/230VAC					
	INRUSH CURRENT(Typ.)	COLD START 50A(twidth=155µs measured at 50% lpeak) at 230VAC					
	LEAKAGE CURRENT	0.25mA / 240VAC					
	OVERLOAD	Above 105% rated output power					
PROTECTION	OVERLOAD	Protection type: Hiccup mode, recovers automatically after fault condition is removed					
	OVER VOLTAGE	13.8~ 16.2V	27.6~ 32.4V	41.4 ~ 48.6V			
		Protection type : Shut off o/p voltage, clamping by zener diode					
	OVER TEMPERATURE	Hiccup mode, recovers automatically after temperature goes down					
ENVIRONMENT	WORKING TEMP.	-30~ +70°C (Refer to "Derating Curve")					
	WORKING HUMIDITY	20 ~ 90% RH non-condensing					
	STORAGE TEMP., HUMIDITY	-40 ~ +80°C, 10 ~ 95% RH					
	TEMP. COEFFICIENT	±0.03%/°C (0~50°C)					
	VIBRATION	10 ~ 500Hz, 2G 10min./1cycle, period for 60min. each along X, Y, Z axes					
	SAFETY STANDARDS	TUV EN60950-1, TUV EN61347-1,EN61347-2-13,IP67 approved; design refer to UL1310 Class 2,CAN/CSA No. 223-M91					
SAFETY &	WITHSTAND VOLTAGE	I/P-O/P:3KVAC					
EMC	ISOLATION RESISTANCE	I/P-O/P:>100M Ohms / 500VDC / 25°C / 70% RH					
(Note 4)	EMC EMISSION	Compliance to EN55022 (CISPR22) Class B, EN61000-3-2 Class A, EN61000-3-3					
	EMC IMMUNITY	Compliance to EN61000-4-2,3,4,5,6,8,11, EN55024, light industry level, criteria A					
OTHERS	MTBF	1200.6K hrs min. MIL-HDBK-217F (25°ℂ)					
	DIMENSION	140*30*22(L*W*H)					
	PACKING	0.175Kg; 70pcs/13.3Kgs/0.71CUFT					
NOTE	Ripple & noise are measure Tolerance: includes set up The power supply is consident complete installation, the fire Suitable for indoor use or	lly mentioned are measured at 230VAC inped at 20MHz of bandwidth by using a 12" to tolerance, line regulation and load regulatio lered as a component that will be operated all equipment manufacturers must re-qualify utdoor use without direct sunlight exposure. ole for lighting applications in EU countries.	visted pair-wire terminated with a 0.1uf & 47 in. in combination with final equipment. Since I y EMC Directive on the complete installation	7uf parallel capacitor. EMC performance will be affected by th n again.			



