



10mm pitch low profile 45° rising clamp terminal blocks

Product overview

- 1 and 12 pole interlocking mechanism
- 45° mounting
- Captive screws
- Moulded in green UL94-V0 flame retardant PA
- Cable acceptance - 0.32-1.6mm² (28-14 AWG)
-  approved

CTBP4000




CTBP4000/1/15



SPECIFICATION	
Rating	15A / 300V
Withstand voltage	AC 1600V / 1Min
Working temperature	-40°C to +105°C
Moulding	UL94-V0 flame retardant PA
Pin/terminal	Tinned, nickel plated brass
Rising clamp	Zinc plated steel
Screw/torque	M3 steel zinc plated, 0.4Nm
Recommended PCB hole size	Ø1.6mm

PART NO.	POLES	LENGTH
CTBP4000/1	1	10mm
CTBP4000/1/15	1	15mm
CTBP4000/2	2	15mm
CTBP4000/3	3	25mm
CTBP4000/4	4	35mm
CTBP4000/5	5	45mm
CTBP4000/6	6	55mm
CTBP4000/7	7	65mm
CTBP4000/8	8	75mm
CTBP4000/9	9	85mm
CTBP4000/10	10	95mm
CTBP4000/11	11	105mm
CTBP4000/12	12	115mm



KEY FEATURES

Low profile | 45° cable entry | Rising clamp terminals

