



Features:





- 50W Single Output - Regulated
- Output Range: 12V - 24VDC
- Input: 90 - 305VAC , 47 - 440Hz
- Low Standby Power <0.1W
- Height 23.1mm
- Fully Isolated Pri - Sec 4000Vrms
- EMC Compliant without external components
- Materials: UL94-V0
- Safety: UL/IEC/EN62368-1, EN60335-1, CE,

Part Number	Power Rating Watts	Output Voltage (Vdc)	Output Current (mA)	Ambient Temp. (°C)	Efficiency Typical	Input Range
VTX-214-050-112	50	12	4167	70	>88%	90 - 305VAC (120-430VDC)
VTX-214-050-115	50	15	3333			
VTX-214-050-124	50	24	2083			
Note: Other output voltages are available upon request.						

Maximum Capacitive Load:

- 12V: 3500uF
- 15V: 3000uF
- 24V: 2200uF



Please contact Vigortronix for any enquiries. Products can be altered to suit custom requirements.
The information contained in this document is subject to change without notice.

Vigortronix, 16 De Havilland Way, Witney, Oxfordshire, OX29 0YG, UK

Tel. +44 (0)1993 777570 Fax. +44 (0)1993 777580 Web. www.vigortronix.com E-mail: sales@vigortronix.com

Vigortronix is a trading name of Vigortronix (UK) Limited

Vigortronix.com

Model: 50Watt		Specification
INPUT Pin 1: L Pin 2: N	Voltage Range	90 - 305VAC / 47 - 440Hz (120 ~ 430VDC)
	Current	1000mA Max (115VAC) / 600mA Max (230VAC)
	Inrush Current	45A Max (115VAC) / 90A Max (230VAC)
	No Load power	0.15W
	Leakage Current	0.25 mA Max (230VAC)
OUTPUT Pin 3: VDC+ Pin 5: VDC- Pin 4: No Pin	Voltage Accuracy	+/- 2%
	Ripple	<240mV Max (Vp-p)
	Noise	<240mV Max (Vp-p)
	Efficiency	>88%
	Load Regulation	+/-2.5%
	Hold Up Time	10mSec Min.
	Minimum Load	0
Protection	Over Power	Hiccup mode
	Over Voltage	Zener Diode clamp
	Short Circuit Protection	Hiccup mode
Dielectric Isolation	Input to Output	4000Vrms, 2Sec Min.
Enviroment	Operating Temperature	-40°C - +70°C (With Derating)
	Storage Temperature	-40°C - +85°C
	MTBF	>300,000Hrs @ 25°C (MIL-HDBK-217F)
	Weight	150g
	Cooling Method	Free Air convection
Safety	Compliant Standards	UL/IEC/EN62368-1, EN60335-1 In progress
EMC	EMI	Compliance with EN55022 Class B
	EMS	Compliance with EN55035

Please contact Vigortronix for any enquiries. Products can be altered to suit custom requirements.
The information contained in this document is subject to change without notice.


Vigortronix, 16 De Havilland Way, Witney, Oxfordshire, OX29 0YG, UK

Tel. +44 (0)1993 777570 Fax. +44 (0)1993 777580 Web. www.vigortronix.com E-mail: sales@vigortronix.com

Vigortronix is a trading name of Vigortronix (UK) Limited


Vigortronix.com

Schematic Diagram



Notes:

Mechanical Layout



Recommended PCB
Hole size: 1.2mm Dia.

Unit weight: 150g

Please contact Vigortronix for any enquiries. Products can be altered to suit custom requirements.
The information contained in this document is subject to change without notice.

Vigortronix, 16 De Havilland Way, Witney, Oxfordshire, OX29 0YG, UK

Tel. +44 (0)1993 777570 Fax. +44 (0)1993 777580 Web. www.vigortronix.com E-mail: sales@vigortronix.com

Vigortronix is a trading name of Vigortronix (UK) Limited

Vigortronix.com