



## BLM3 DC LATCHING SOLENOID


**Availability**  
PULL & THRUST (PUSH)  
PULL  
THRUST (PUSH)

**Solenoid shown in energised position**

Weight complete 167g  
Plunger weight 45g max

Solenoid CLOSSES with  
**RED** Lead + VE  
Solenoid OPENS with  
**BLACK** Lead + VE


Minimum Pulse duration - 100ms  
De-latch power - 2.5W



LEADS 24AWG 200MM - ONE RED ONE BLACK

DIMENSIONS IN MM

(Mechanical assistance is required when de-latching,  
ie via mechanism or return spring)



**Optional**  
Return Spring  
Nylon Tip

### Example Applications

- Electronic Locks
- Medical Cabinets
- Vending Machines
- Battery Operated Locks

**\*\* Please note: Fixing, plunger coupling, thrust rods and lead length can all be customised \*\***  
*We reserve the right to alter or amend designs without prior notice.*

**HE & BS Benson Ltd**

**1 Laureate Industrial Estate, Exning Road, Newmarket, Suffolk UK CB8 0AR**

**T. +44(0)1638 663535 – 663130 E. sales@hebsbenson.co.uk www.hebsbenson.co.uk**