L-7113YT

YELLOW


Features

- •LOW POWER CONSUMPTION.
- ●POPULAR T-1 3/4 DIAMETER PACKAGE.
- •GENERAL PURPOSE LEADS.
- •RELIABLE AND RUGGED.
- •LONG LIFE SOLID STATE RELIABILITY.
- •AVAILABLE ON TAPE AND REEL.
- RoHS COMPLIANT.

Description

The Yellow source color devices are made with Gallium Arsenide Phosphide on Gallium Phosphide Yellow Light Emitting Diode.

Package Dimensions



- 1. All dimensions are in millimeters (inches).
- 2. Tolerance is $\pm 0.25(0.01")$ unless otherwise noted.
- 3. Lead spacing is measured where the lead emerge from the package.
- 4. Specifications are subject to change without notice.

SPEC NO: DSAB7798 **REV NO: V.5 DATE: MAR/25/2005** PAGE: 1 OF 3 **CHECKED: Allen Liu** DRAWN: S.H.CHEN

APPROVED: J. Lu

Kingbright

Selection Guide

Part No.	Dice	Lens Type	Iv (mcd) @ 10mA		Viewing Angle
			Min.	Тур.	201/2
L-7113YT	YELLOW (GaAsP/GaP)	YELLOW TRANSPARENT	18	40	20°

Note:

Electrical / Optical Characteristics at T_A=25°C

Symbol	Parameter	Device	Тур.	Max.	Units	Test Conditions
λpeak	Peak Wavelength	Yellow	590		nm	IF=20mA
λD	Dominant Wavelength	Yellow	588		nm	IF=20mA
Δλ1/2	Spectral Line Half-width	Yellow	35		nm	IF=20mA
С	Capacitance	Yellow	20		pF	VF=0V;f=1MHz
VF	Forward Voltage	Yellow	2.1	2.5	V	IF=20mA
IR	Reverse Current	Yellow		10	uA	VR = 5V

Absolute Maximum Ratings at Ta=25°C

Parameter	Yellow	Units		
Power dissipation	105	mW		
DC Forward Current	30	mA		
Peak Forward Current [1]	140	mA		
Reverse Voltage	5	V		
Operating / Storage Temperature	-40°C To +85°C			
Lead Solder Temperature [2]	older Temperature [2] 260°C For 3 Seconds			
ead Solder Temperature [3] 260°C For 5 Seconds				


Notes:

- 1. 1/10 Duty Cycle, 0.1ms Pulse Width.
- 2. 2mm below package base.
- 3. 5mm below package base.

SPEC NO: DSAB7798 REV NO: V.5 DATE: MAR/25/2005 PAGE: 2 OF 3
APPROVED: J. Lu CHECKED: Allen Liu DRAWN: S.H.CHEN


^{1.} θ 1/2 is the angle from optical centerline where the luminous intensity is 1/2 the optical centerline value.


Kingbright





Yellow


L-7113YT











Pamarke:

If special sorting is required (e.g. binning based on forward voltage, luminous intensity, or wavelength), the typical accuracy of the sorting process is as follows:

1. Wavelength: +/-1nm

2. Luminous Intensity: +/-15%

3. Forward Voltage: +/-0.1V

Note: Accuracy may depend on the sorting parameters.

SPEC NO: DSAB7798 REV NO: V.5 DATE: MAR/25/2005 PAGE: 3 OF 3
APPROVED: J. Lu CHECKED: Allen Liu DRAWN: S.H.CHEN