

DATA SHEET

5mm LEDs

1	Order code	Manufacturer code	Description
	56-1550	L-7113ID-12V	5MM 12V HE RED LED (RC)

From LEDo	Page 1 of
The enclosed information is believed to be correct, Information may change 'without notice' due to	Revision A
product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	12/12/2006

Sales: 01206 751166 Sales@rapidelec.co.uk Technical: 01206 835555
Tech@rapidelec.co.uk

Fax: 01206 751188 www.rapidelectronics.co.uk

L-7113ID-12V

HIGH EFFICIENCY RED


Features

- •LOW POWER CONSUMPTION.
- ●POPULAR T-1 3/4 DIAMETER PACKAGE.
- •GENERAL PURPOSE LEADS.
- •RELIABLE AND RUGGED.
- •LONG LIFE SOLID STATE RELIABILITY.
- •AVAILABLE ON TAPE AND REEL.
- ●12V INTERNAL RESISTOR.
- ●RoHS COMPLIANT.

Description

The High Efficiency Red source color devices are made with Gallium Arsenide Phosphide on Gallium Phosphide Orange Light Emitting Diode.

Package Dimensions



- 1. All dimensions are in millimeters (inches).
- 2. Tolerance is $\pm 0.25(0.01")$ unless otherwise noted. 3. Lead spacing is measured where the leads emerge from the package.
- 4. Specifications are subject to change without notice.

SPEC NO: DSAE8444 **REV NO: V.2** DATE: MAR/22/2005 PAGE: 1 OF 3 APPROVED: J. Lu **CHECKED: Allen Liu** DRAWN: H.Q.YUAN

Kingbright

Selection Guide

Part No. Dice		Lens Type	Iv (mcd) V= 12V		Viewing Angle	
		,	Min.	Тур.	201/2	
L-7113ID-12V	HIGH EFFICIENCY RED (GaAsP/GaP)	RED DIFFUSED	12	30	30°	

Note:

Electrical / Optical Characteristics at T_A=25°C

Symbol	Parameter	Device	Тур.	Max.	Units	Test Conditions
λpeak	Peak Wavelength	High Efficiency Red	627		nm	VF=12V
λD	Dominant Wavelength	High Efficiency Red	625		nm	VF=12V
Δλ1/2	Spectral Line Half-width	High Efficiency Red	45		nm	VF=12V
I _F	Forward Current	High Efficiency Red	8.5	11.5	mA	VF=12V
lR	Reverse Current	High Efficiency Red		10	uA	VR = 5V

Absolute Maximum Ratings at Ta=25°C

Parameter	High Efficiency Red	Units	
Power dissipation	120	mW	
Forward Voltage	14	V	
Reverse Voltage	5	V	
Operating Temperature	-40°C To +70°C		
Storage Temperature	-40°C To +85°C		
Lead Solder Temperature[1]	260°C For 3 Seconds		
Lead Solder Temperature[2]	er Temperature[2] 260°C For 5 Seconds		


Notes:

- 1. 2mm below package base.
- 2. 5mm below package base.

SPEC NO: DSAE8444 REV NO: V.2 DATE: MAR/22/2005 PAGE: 2 OF 3
APPROVED: J. Lu CHECKED: Allen Liu DRAWN: H.Q.YUAN


 $^{1.\,\}theta1/2$ is the angle from optical centerline where the luminous intensity is 1/2 the optical centerline value.


Kingbright





High Efficiency Red

L-7113ID-12V









Remarks

If special sorting is required (e.g. binning based on luminous intensity, or wavelength),

the typical accuracy of the sorting process is as follows:

- 1. Wavelength: +/-1nm
- 2. Luminous Intensity: +/-15%

Note: Accuracy may depend on the sorting parameters.

SPEC NO: DSAE8444 REV NO: V.2 DATE: MAR/22/2005 PAGE: 3 OF 3
APPROVED: J. Lu CHECKED: Allen Liu DRAWN: H.Q.YUAN