

EVO-STIK WOOD ADHESIVE INTERIOR
Supersedes Date: 18-Sep-2019

Revision date 22-Mar-2021
Revision Number 1.02

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product Name EVO-STIK WOOD ADHESIVE INTERIOR
Pure substance/mixture Mixture

1.2. Relevant identified uses of the substance or mixture and uses advised against

Recommended use Building and construction work.
Uses advised against None known

1.3. Details of the supplier of the safety data sheet

Company Name

Bostik Limited
Common Rd
ST16 3EH
Stafford UK
Tel: +44 (1785) 27 26 25
Fax: +44 (1785) 25 72 36

E-mail address SDS.box-EU@bostik.com

1.4. Emergency telephone number

United Kingdom +44 (1785) 272650
Ireland +353 (1) 8624900 (Monday- Friday 9am-5pm)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Regulation (EC) No 1272/2008

This mixture is classified as not hazardous according to regulation (EC) 1272/2008 [CLP]

2.2. Label elements

This mixture is classified as not hazardous according to regulation (EC) 1272/2008 [CLP]

Signal word

None

Hazard statements

This mixture is classified as not hazardous according to regulation (EC) 1272/2008 [CLP]

EU Specific Hazard Statements

EUH208 - Contains reaction mass of 5-chloro-2-methyl-2H-isothiazol-3-one and 2-methyl-2H-isothiazol-3-one (3:1) [C(M)IT/MIT]. May produce an allergic reaction

Precautionary Statements - EU (§28, 1272/2008)

P101 - If medical advice is needed, have product container or label at hand
P102 - Keep out of reach of children

2.3. Other hazards

No information available.

SAFETY DATA SHEET

EVO-STIK WOOD ADHESIVE INTERIOR
Supersedes Date: 18-Sep-2019

Revision date 22-Mar-2021
Revision Number 1.02

PBT & vPvB

This mixture contains no substance considered to be persistent, bioaccumulating or toxic (PBT). This mixture contains no substance considered to be very persistent nor very bioaccumulating (vPvB).

SECTION 3: Composition/information on ingredients

3.1 Substances

Not applicable

3.2 Mixtures

Chemical name	EC No	CAS No	Weight-%	Classification according to Regulation (EC) No. 1272/2008 [CLP]	Specific concentration limit (SCL)	REACH registration number
Propylene carbonate	203-572-1	108-32-7	1 - <5	Eye Irrit. 2 (H319)		01-2119537232-48-XXXX
reaction mass of 5-chloro-2-methyl-2H-isothiazol-3-one and 2-methyl-2H-isothiazol-3-one (3:1) [C(M)IT/MIT]	611-341-5	55965-84-9	<0.0015	Acute Tox. 3 (H301) Acute Tox. 2 (H310) Acute Tox. 2 (H330) Skin Corr. 1C (H314) Eye Dam. 1 (H318) Skin Sens. 1A (H317) Aquatic Acute 1 (H400) Aquatic Chronic 1 (H410) M Factor Acute = 100 M Factor Chronic = 100	Eye Dam. 1 :: C>=0.6% Irrit. 2 :: 0.06%<=C<0.6% Skin Corr. 1C :: C>=0.6% Skin Irrit. 2 :: 0.06%<=C<0.6% Skin Sens. 1 :: C>=0.0015%	01-2120764691-48-XXXX

Full text of H- and EUH-phrases: see section 16

This product does not contain candidate substances of very high concern at a concentration $\geq 0.1\%$ (Regulation (EC) No. 1907/2006 (REACH), Article 59)

SECTION 4: First aid measures

4.1. Description of first aid measures

General advice	Show this safety data sheet to the doctor in attendance.
Inhalation	Remove to fresh air. IF exposed or concerned: Get medical advice/attention.
Eye contact	Rinse thoroughly with plenty of water for at least 15 minutes, lifting lower and upper eyelids. Consult a doctor.
Skin contact	Wash skin with soap and water. In the case of skin irritation or allergic reactions see a

SAFETY DATA SHEET

EVO-STIK WOOD ADHESIVE INTERIOR
Supersedes Date: 18-Sep-2019

Revision date 22-Mar-2021
Revision Number 1.02

doctor.

Ingestion Clean mouth with water. Do NOT induce vomiting. Drink 1 or 2 glasses of water. Never give anything by mouth to an unconscious person.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms No information available.

4.3. Indication of any immediate medical attention and special treatment needed

Note to doctors Treat symptomatically.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable Extinguishing Media Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media No information available.

5.2. Special hazards arising from the substance or mixture

Specific hazards arising from the chemical No information available.

Hazardous combustion products Carbon dioxide (CO₂).

5.3. Advice for firefighters

Special protective equipment and precautions for fire-fighters Firefighters should wear self-contained breathing apparatus and full firefighting turnout gear. Use personal protection equipment.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions Ensure adequate ventilation.

For emergency responders Use personal protection recommended in Section 8.

6.2. Environmental precautions

Environmental precautions See Section 12 for additional Ecological Information.

6.3. Methods and material for containment and cleaning up

Methods for containment Prevent further leakage or spillage if safe to do so.

Methods for cleaning up Take up mechanically, placing in appropriate containers for disposal.

Prevention of secondary hazards Clean contaminated objects and areas thoroughly observing environmental regulations.

6.4. Reference to other sections

Reference to other sections See section 8 for more information. See section 13 for more information.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

SAFETY DATA SHEET

EVO-STIK WOOD ADHESIVE INTERIOR
 Supersedes Date: 18-Sep-2019

Revision date 22-Mar-2021
 Revision Number 1.02

Advice on safe handling Ensure adequate ventilation.

General hygiene considerations Handle in accordance with good industrial hygiene and safety practice.

7.2. Conditions for safe storage, including any incompatibilities

Storage Conditions Keep container tightly closed in a dry and well-ventilated place.

7.3. Specific end use(s)

Specific use(s)
 Building and construction work.

Risk Management Methods (RMM) The information required is contained in this Safety Data Sheet.

Other information Observe technical data sheet.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure Limits

Derived No Effect Level (DNEL) No information available

Derived No Effect Level (DNEL)			
Propylene carbonate (108-32-7)			
Type	Exposure route	Derived No Effect Level (DNEL)	Safety factor
worker Long term Systemic health effects	Inhalation	70.53 mg/m ³	
worker Long term Local health effects	Inhalation	20 mg/m ³	
worker Long term Systemic health effects	Dermal	20 mg/kg bw/d	
worker Long term Local health effects	Dermal	10 mg/cm ²	

Derived No Effect Level (DNEL)			
Propylene carbonate (108-32-7)			
Type	Exposure route	Derived No Effect Level (DNEL)	Safety factor
Consumer Long term Systemic health effects	Inhalation	17.4 mg/m ³	
Consumer Long term Local health effects	Inhalation	10 mg/m ³	
Consumer Long term Systemic health effects	Dermal	10 mg/kg bw/d	
Consumer Long term Systemic health effects	Oral	10 mg/kg bw/d	

SAFETY DATA SHEET

EVO-STIK WOOD ADHESIVE INTERIOR
Supersedes Date: 18-Sep-2019

Revision date 22-Mar-2021
Revision Number 1.02

Predicted No Effect Concentration (PNEC) No information available.

Predicted No Effect Concentration (PNEC)	
Propylene carbonate (108-32-7)	
Environmental compartment	Predicted No Effect Concentration (PNEC)
Freshwater	0.9 mg/l
Marine water	0.09 mg/l
Soil	0.81 mg/kg dry weight
Sewage treatment plant	7400 mg/l

8.2. Exposure controls

Engineering controls Ensure adequate ventilation, especially in confined areas.

Personal protective equipment

Eye/face protection

Wear safety glasses with side shields (or goggles). Eye protection must conform to standard EN 166.

Hand protection

Wear suitable gloves. Gloves must conform to standard EN 374. Recommended Use: Polyvinyl chloride (PVC). The breakthrough time for the mentioned glove material is in general greater than 480 min. Ensure that the breakthrough time of the glove material is not exceeded. Refer to glove supplier for information on breakthrough time for specific gloves.

Skin and body protection

Wear suitable protective clothing. Material, acid-resistant.

Respiratory protection

No protective equipment is needed under normal use conditions. If exposure limits are exceeded or irritation is experienced, ventilation and evacuation may be required.

Environmental exposure controls Do not allow uncontrolled discharge of product into the environment.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	Liquid
Appearance	Liquid
Colour	White
Odour	Sweet
Odour threshold	No information available

Property	Values	Remarks • Method
pH	2.8 - 3.6	
pH (as aqueous solution)	No data available	
Melting point / freezing point	No data available	
Initial boiling point and boiling range	100 °C	
Flash point	No data available	
Evaporation rate	No data available	
Flammability	Not applicable for liquids	
Flammability Limit in Air		
Upper flammability or explosive limits	No data available	
Lower flammability or explosive limits	No data available	
Vapour pressure	24	hPa
Relative vapour density	No data available	
Relative density	No data available	
Water solubility	Miscible in water	
Solubility(ies)	No data available	
Partition coefficient	No data available	
Autoignition temperature	No data available	
Decomposition temperature	No data available	
Kinematic viscosity	No data available	

SAFETY DATA SHEET

EVO-STIK WOOD ADHESIVE INTERIOR
Supersedes Date: 18-Sep-2019

Revision date 22-Mar-2021
Revision Number 1.02

Dynamic viscosity	9000 - 15000 mPa s
Explosive properties	No data available
Oxidising properties	No data available

9.2. Other information

Solid content (%)	No information available
VOC Content (%)	
Density	1.03 - 1.13 g/cm ³

SECTION 10: Stability and reactivity

10.1. Reactivity

Reactivity No information available.

10.2. Chemical stability

Stability Stable under normal conditions.

Explosion data

Sensitivity to mechanical impact None.

Sensitivity to static discharge None.

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions None under normal processing.

10.4. Conditions to avoid

Conditions to avoid None known based on information supplied.

10.5. Incompatible materials

Incompatible materials None known based on information supplied.

10.6. Hazardous decomposition products

Hazardous decomposition products Carbon monoxide. Carbon dioxide (CO₂). Hydrocarbons.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Information on likely routes of exposure

Product Information

Inhalation Based on available data, the classification criteria are not met.

Eye contact Based on available data, the classification criteria are not met.

Skin contact Based on available data, the classification criteria are not met.

Ingestion Based on available data, the classification criteria are not met.

Symptoms related to the physical, chemical and toxicological characteristics

Symptoms No information available.

SAFETY DATA SHEET

EVO-STIK WOOD ADHESIVE INTERIOR
Supersedes Date: 18-Sep-2019

Revision date 22-Mar-2021
Revision Number 1.02

Numerical measures of toxicity

Acute toxicity

Component Information

Chemical name	Oral LD50	Dermal LD50	Inhalation LC50
Propylene carbonate 108-32-7	LD50 > 5000 mg/kg (Rattus) OECD 401	> 3000 mg/kg (Oryctolagus cuniculus)	
reaction mass of 5-chloro-2-methyl-2H-isothiazol- 3-one and 2-methyl-2H-isothiazol-3-one (3:1) [C(M)IT/MIT] 55965-84-9	=53 mg/kg (Rattus)	LD50 = 87.12 mg/kg (Oryctolagus cuniculus)	

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Skin corrosion/irritation Based on available data, the classification criteria are not met.

Serious eye damage/eye irritation Based on available data, the classification criteria are not met.

Respiratory or skin sensitisation Based on available data, the classification criteria are not met.

Germ cell mutagenicity Based on available data, the classification criteria are not met.

Carcinogenicity Based on available data, the classification criteria are not met.

Reproductive toxicity Based on available data, the classification criteria are not met.

STOT - single exposure Based on available data, the classification criteria are not met.

STOT - repeated exposure Based on available data, the classification criteria are not met.

Aspiration hazard Based on available data, the classification criteria are not met.

11.2. Information on other hazards

11.2.1. Endocrine disrupting properties

Endocrine disrupting properties No information available.

11.2.2. Other information

Other adverse effects No information available.

SECTION 12: Ecological information

SAFETY DATA SHEET

EVO-STIK WOOD ADHESIVE INTERIOR
Supersedes Date: 18-Sep-2019

Revision date 22-Mar-2021
Revision Number 1.02

12.1. Toxicity

Ecotoxicity

Chemical name	Algae/aquatic plants	Fish	Toxicity to microorganisms	Crustacea	M-Factor	M-Factor (long-term)
Propylene carbonate 108-32-7	EC50: >500mg/L (72h, Desmodesmus subspicatus)	LC50 96 h > 1000 mg/L (Cyprinus carpio semi-static)	EC50 > 10000 mg/L 17 h	EC50: >500mg/L (48h, Daphnia magna)		
reaction mass of 5-chloro-2-methyl-2H-is othiazol-3-one and 2-methyl-2H-isothiazol- 3-one (3:1) [C(M)IT/MIT] 55965-84-9	EC50 (72h) =0.048 mg/L (Pseudokirchner iella subcapitata) (OECD 201)	EC50 (96h) = 0.22 mg/L (Oncorhynchus mykiss) (OECD 211)	-	EC50 (48h) =0.1 mg/L (Daphnia magna) (OECD 202)	100	100

12.2. Persistence and degradability

Persistence and degradability No information available.

12.3. Bioaccumulative potential

Bioaccumulation There is no data for this product.

Component Information

Chemical name	Partition coefficient	Bioconcentration factor (BCF)
Propylene carbonate 108-32-7	0.079	-
reaction mass of 5-chloro-2-methyl-2H-isothiazol-3-one and 2-methyl-2H-isothiazol-3-one (3:1) [C(M)IT/MIT] 55965-84-9	-	3.16

12.4. Mobility in soil

Mobility in soil No information available.

12.5. Results of PBT and vPvB assessment

PBT and vPvB assessment . The product does not contain any substance(s) classified as PBT or vPvB.

Chemical name	PBT and vPvB assessment
Propylene carbonate 108-32-7	The substance is not PBT / vPvB
reaction mass of 5-chloro-2-methyl-2H-isothiazol-3-one and 2-methyl-2H-isothiazol-3-one (3:1) [C(M)IT/MIT] 55965-84-9	The substance is not PBT / vPvB

12.6. Other adverse effects

Other adverse effects No information available.

SECTION 13: Disposal considerations

SAFETY DATA SHEET

EVO-STIK WOOD ADHESIVE INTERIOR
Supersedes Date: 18-Sep-2019

Revision date 22-Mar-2021
Revision Number 1.02

13.1. Waste treatment methods

Waste from residues/unused products	Dispose of in accordance with local regulations. Dispose of waste in accordance with environmental legislation.
Contaminated packaging	Do not reuse empty containers.
Other information	Waste codes should be assigned by the user based on the application for which the product was used.

SECTION 14: Transport information

Land transport (ADR/RID)

14.1 UN number or ID number	Not regulated
14.2 Proper Shipping Name	Not regulated
14.3 Transport hazard class(es)	Not regulated
14.4 Packing group	Not regulated
14.5 Environmental hazards	Not applicable
14.6 Special Provisions	None

IMDG

14.1 UN number or ID number	Not regulated
14.2 Proper Shipping Name	Not regulated
14.3 Transport hazard class(es)	Not regulated
14.4 Packing group	Not regulated
14.5 Marine pollutant	NP
14.6 Special Provisions	None
14.7 Transport in bulk according to Annex II of MARPOL and the IBC Code	Not applicable

Air transport (ICAO-TI / IATA-DGR)

14.1 UN number or ID number	Not regulated
14.2 Proper Shipping Name	Not regulated
14.3 Transport hazard class(es)	Not regulated
14.4 Packing group	Not regulated
14.5 Environmental hazards	Not applicable
14.6 Special Provisions	None

Section 15: REGULATORY INFORMATION

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

European Union

Take note of Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work

Check whether measures in accordance with Directive 94/33/EC for the protection of young people at work must be taken.

Take note of Directive 92/85/EC on the protection of pregnant and breastfeeding women at work

Registration, Evaluation, Authorization, and Restriction of Chemicals (REACH) Regulation (EC 1907/2006)

SVHC: Substances of Very High Concern for Authorisation:

This product does not contain candidate substances of very high concern at a concentration $\geq 0.1\%$ (Regulation (EC) No. 1907/2006 (REACH), Article 59)

SAFETY DATA SHEET

EVO-STIK WOOD ADHESIVE INTERIOR
Supersedes Date: 18-Sep-2019

Revision date 22-Mar-2021
Revision Number 1.02

EU-REACH (1907/2006) - Annex XVII - Substances subject to Restriction

This product does not contain substances subject to restriction (Regulation (EC) No. 1907/2006 (REACH), Annex XVII).

Substance subject to authorisation per REACH Annex XIV

This product does not contain substances subject to authorisation (Regulation (EC) No. 1907/2006 (REACH), Annex XIV)

Biocidal Products Regulation (EU) No 528/2012 (BPR)

Contains a biocide : Contains C(M)IT/MIT (3:1). May produce an allergic reaction

Ozone-depleting substances (ODS) regulation (EC) 1005/2009

Not applicable

Persistent Organic Pollutants

Not applicable

National regulations

15.2. Chemical safety assessment

Chemical Safety Assessments have been carried out by the Reach registrants for substances registered at >10 tpa. No
Chemical Safety Assessment has been carried out for this mixture

SECTION 16: Other information

Key or legend to abbreviations and acronyms used in the safety data sheet

Full text of H-Statements referred to under section 3

H301 - Toxic if swallowed
H310 - Fatal in contact with skin
H314 - Causes severe skin burns and eye damage
H317 - May cause an allergic skin reaction
H318 - Causes serious eye damage
H319 - Causes serious eye irritation
H330 - Fatal if inhaled
H400 - Very toxic to aquatic life
H410 - Very toxic to aquatic life with long lasting effects

Legend

TWA	TWA (time-weighted average)
STEL	STEL (Short Term Exposure Limit)
Ceiling	Ceiling Limit Value
*	Skin designation
SVHC	Substance(s) of Very High Concern
PBT	Persistent, Bioaccumulative, and Toxic (PBT) Chemicals
vPvB	Very Persistent and very Bioaccumulative (vPvB) Chemicals
STOT RE	Specific target organ toxicity - Repeated exposure
STOT SE	Specific target organ toxicity - Single exposure
EWC	European Waste Catalogue

Key literature references and sources for data

No information available

Prepared By Product Safety & Regulatory Affairs

SAFETY DATA SHEET

EVO-STIK WOOD ADHESIVE INTERIOR
Supersedes Date: 18-Sep-2019

Revision date 22-Mar-2021
Revision Number 1.02

Revision date 22-Mar-2021

Indication of changes

Revision note Not applicable.

Training Advice No information available

Further information No information available

This material safety data sheet complies with the requirements of Regulation (EC) No. 1907/2006

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet