

**SAFETY DATA SHEET**  
Doff Complete Lawn Feed, Weed & Moss Killer

---

**1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING**

**1.1 Product Identifier:**

**Product names:** Doff Complete Lawn Feed, Weed & Moss killer

**Product codes:** F-LM-xxx-DOF

**1.2 Relevant uses of the substance or mixture and uses advised against:**

Supplied for amateur use as a herbicide weed killer and moss killer

**1.3 Details of the supplier of the safety data sheet:**

Doff Portland Limited  
Aerial Way  
Hucknall  
Nottingham  
NG15 6DW  
UK

Telephone number: +44 (0) 115 9834 300

Email: [help@doff.co.uk](mailto:help@doff.co.uk)

**1.4 Emergency phone number**

Emergency telephone number: +44 (0) 115 9834 300 (office hours only)

---

**2. HAZARDS IDENTIFICATION**

**2.1 Classification of the substance or mixture**

CLASSIFICATION according to Regulation EC 1272/2008 Classification, Labelling and Packaging

**Eye Irritation 2**                    **H319**    **Causes serious eye irritation.**

**Aquatic Chronic 2**                **H411**    **Toxic to aquatic life with long lasting effects.**

**2.2 Label Elements**

Product Name:                    **Doff Complete Lawn Feed, Weed & Moss killer**

Pictogram(s):



Signal word:

Warning

Hazard statements:

H319    Causes serious eye irritation.

H411    Toxic to aquatic life with long lasting effects.



- Precautionary statements:
- P101 If medical advice is needed, have product container or label at hand.
  - P102 Keep out of reach of children.
  - P264 Wash Hands thoroughly after handling
  - P280 Wear protective gloves/protective clothing/eye protection/face protection
  - P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
  - P337 + P313 If eye irritation persists: Get medical advice/attention.
  - P391 Collect spillage
  - P501 Dispose of contents/container to a licensed hazardous waste disposal contractor or collection site except for triple rinsed empty containers which can be disposed of as non-hazardous waste

### 2.3 Other Hazards





EUH208 — Contains 2,4-D. May produce an allergic reaction

EUH401 – To avoid risks to human health and the environment comply with the instructions for use.





Mixture not classed as PBT or vPvB

## 3. COMPOSITION/INFORMATION ON INGREDIENTS

### 3.2 Mixtures

Name:	CAS/EC No.	Index No./REACH Registration No.	Pictogram(s) according to 1272/2008:	H-phrase(s) according to 1272/2008:	Concentrations [% w/w]
Iron (II) sulfate heptahydrate	7782-63-0 231-753-5	Index No. 026-003-01-4	 GHS07	Acute Tox. 4 (Oral); H302 Skin Irrit. 2; H315 Eye Irrit. 2; H319	25 - 30
Single super phosphate	8011-76-5/ 232-379-5	-	 GHS05	Eye Dam. 1; H318	5.0 – 9.9
(R)-2-(4-chloro-2-methyl phenoxy) propionic acid, dimethylamine salt	66423-09-04/ 240-539-0	Index No. 607-434-00-5	 GHS05  GHS07	Acute Tox. 4 (Oral); H302 Eye Dam. 1; H318 Aquatic chronic 2; H411	< 0.5



			 GHS09		
(2,4-dichlorophenoxy) acetic acid, dimethylamine salt	2008-39-1/ 217-915-8	607-040-00-3	 GHS05   GHS07   GHS09	Acute Tox. 4 (Oral); H302 Eye Dam. 1; H318 Skin Sens. 1; H317 Aquatic Chronic 2; H411	< 0.5

The full hazard information for individual components if not displayed in section 2 or 3 are displayed in Section 16.

#### 4.0. FIRST AID MEASURES

##### 4.1 Description of first aid measures

###### 4.1.1 Inhalation

If symptoms arise remove from source of exposure to fresh air; seek medical attention.

###### 4.1.2 Skin & Eye exposure

Skin: Drench immediately with water. Remove any contaminated clothing and launder before re-use. Obtain medical attention if symptoms persist or develop.

Eyes: Immediately rinse with clean water for 15 minutes. Obtain medical attention if symptoms occur or persist.

###### 4.1.3 Ingestion

Do not induce vomiting. Wash out mouth with water and give water to drink. Obtain medical attention immediately.

##### 4.2 Most important symptoms and effects, both acute and delayed

Causes serious eye irritation. May produce an allergic reaction.

See SECTION 11 for more detailed information on health effects and symptoms.

##### 4.3 Indications of any immediate medical attention and special treatment needed

###### Notes to physician

No specific treatment. Treat symptomatically.



---

## 5. FIRE-FIGHTING MEASURES

### 5.1 Extinguishing media

#### **Suitable**

Use Foam, carbon dioxide, dry powder, sand. The mixture is not classified as flammable as such extinguishing media should be chosen as appropriate for surrounding materials.

#### **Not suitable**

No information available.

### 5.2 Special hazards arising from the substance or mixture

Possible irritant fumes arising from combustion

### 5.3 Advice for firefighters

#### **Special precautions for fire-fighters**

Promptly isolate the scene by removing all persons from the vicinity of the incident if there is a fire. No action shall be taken involving any personal risk or without suitable training.

Cool down containers/equipment exposed to heat with a water spray. Contain spread of extinguishing fluids (these fluids may be hazardous for the environment).

#### **Special protective equipment for fire-fighters**

Fire-fighters should wear appropriate protective equipment and self-contained breathing apparatus (SCBA) with a full face-piece operated in positive pressure mode.

---

## 6. ACCIDENTAL RELEASE MEASURES

### 6.1 Personal precautions, protective equipment and emergency procedures

The following precautions are considered to be good practice when using any chemicals irrespective of their classification unless otherwise specified.

Ensure adequate ventilation

Use personal protective equipment,

- Gloves
- Eye protection
- Suitable respirator if dust is generated during handling

### 6.2 Environmental Precautions

Do not allow to enter storm drains or water courses. If this product enters a water course or a sewer (including via contaminated soil & vegetation) in large quantities contact local water authority and inform the Environment Agency

### 6.3 Methods and material for containment and cleaning up

Sweep avoiding generating dust into labelled containers for recovery or contact specialist waste disposal contractor.

### 6.4 Reference to other sections

**Note:** see SECTION 1 for emergency contact information, SECTION 8 for personal protection and section 13 for waste disposal.



## 7. Handling and storage

### 7.1 Precaution for safe handling

Avoid contact with skin and eyes. Ensure sufficient ventilation of the area. Wash Hands thoroughly after handling  
Do not eat, drink or smoke when using this product

### 7.2 Conditions for safe storage, including any incompatibilities

Store in a cool dry atmosphere, in original labelled containers. Refer to manufacturer for maximum safe stacking height.

### 7.3 Specific end use(s)

The substance has not been assessed for the specified end-points listed in 1.2, so its hazardous property in this regard is not known

## 8. Exposure controls/personal protection

### 8.1 Control Parameters

Workplace exposure Limits as defined by UK HSE in document EH40/2005:

Substance	CAS number	Workplace Exposure Limit				Comments
		Long-term exposure limit (8-hr TWA reference period)		Short-term exposure limit (15 minute reference period)		
		ppm	mg.m <sup>-3</sup>	ppm	mg.m <sup>-3</sup>	
Iron salts (as Fe)		-	1	-	2	The Carc, Sen and Sk notations are not exhaustive. Notations have been applied to the substances identified in IOELV Directives*

\*IOELV – Indicative Occupational Exposure Limit Values (IOELV).

### 8.2 Exposure controls

#### General

Avoid contact with skin, eyes and clothing.

#### Hygiene measures:

Wash hands, forearms and face thoroughly after handling chemical products, before eating, smoking and using the lavatory and at the end of the working period. Appropriate techniques should be used to remove potentially contaminated clothing. Wash contaminated clothing before reusing. Ensure that eyewash stations and safety showers are close to the workstation location. Ensure that there is sufficient ventilation of the area.

#### Eye and face protection

Wear tightly fitting safety goggles and Face shield that meet EN 166 a/o ANSI Z87.1 standards

#### Skin protection

When handling product wear chemical-resistant gloves.

Suitability and durability of a glove is dependent on usage, e.g. frequency and duration of contact. Always seek advice from glove suppliers. Select gloves approved to EU standard EN407.



Wear impermeable protective clothing, butyl rubber apron and boots.

### **Inhalation**

Provide a good standard of general ventilation. Use outdoors or ensure adequate air changes.

---

## **9. PHYSICAL AND CHEMICAL PROPERTIES**

### **9.1 Information on basic physical and chemical properties**

Physical state: Solid granules

Odour: not specified

Odour threshold: No data

pH: ca 3.0 (1% dilution in water)

Melting Point: No data

Initial boiling point and boiling range: Information not available

Flash point: Not flammable

Flammability: Not flammable

Explosion limits: No evidence of explosion risk

Vapour pressure: Information not available.

Vapour density: Not applicable

Bulk Density: Pour Density 0.9 g/ml Tap Density 0.94 g/mL

Solubility: Granules soluble in water

Partition coefficient: n-octanol/water Information not available.

Auto-ignition temperature: No data

Decomposition temperature: No data

Viscosity: Not applicable

### **9.2 Other Information**

No other relevant information available.

---

## **10. STABILITY AND REACTIVITY**

### **10.1 Reactivity**

Unknown.

### **10.2 Chemical stability**

Stable under normal conditions.

### **10.3 Possibility of hazardous reactions**

Information not available.

### **10.4 Conditions to avoid**

Extremes of temperature.

### **10.5 Incompatible materials**

Not known.

### **10.6 Hazardous decomposition products**

Possible irritant fumes.



---

## 11. TOXICOLOGICAL INFORMATION

### 11.1 Information on toxicological effects

Acute toxicity:	Not expected to be toxic.
Skin corrosion/irritation:	Skin Irritation: Not classified as skin irritant (OECD No.439)
Serious eye damage/irritation:	Product is classified as irritating to eyes (OECD No.438)
Skin sensitisation:	Product is not classified as causing skin sensitisation.
Germ cell mutagenicity:	No information specified.
Carcinogenicity:	No information specified.
Reproductive toxicity:	No information specified.
STOT-single exposure:	Product is not classified as having Specific Target Organ Toxicity for single exposure
STOT-repeated exposure:	No information specified.
Aspiration hazard:	No information specified.

### Toxicological information on hazardous ingredients where available:

#### Iron (II) sulphate heptahydrate

##### Acute toxicity:

Oral LD50 (rat) 1185-1750 mg/kg bw/day

#### Single super phosphate

##### Acute toxicity:

Oral LD50 (rat) > 2000 mg/kg bw

---

## 12. ECOLOGICAL INFORMATION

### 12.1 Toxicity

Mixture classified as toxic to aquatic life with long lasting effects in accordance with Regulation EC 1272/2008.

### 12.2 Persistence and degradability

Information not available

### 12.3 Bioaccumulative potential

Information not available

### 12.4 Mobility in soil

Information not available

### 12.5 Results of PBT and vPvB assessment

This mixture does not contain any substances that are assessed to be PBT or vPvB.

### 12.6 Other adverse effects

Information not available.

---

## 13. DISPOSAL CONSIDERATIONS



### 13.1 Waste Treatment Methods

Use only licensed waste disposal companies. Do not re-use empty containers for any purpose.

---

## 14. TRANSPORT INFORMATION

**14.1 UN number:** 3077

**14.2 UN proper shipping name:** Environmentally hazardous substance, solid, N.O.S.

**14.3 Transport hazard:** 9

**14.4 Packing group:** 3

**14.5 Environmental hazards:** Product is classified as toxic to aquatic life with lasting effects

**14.6 Special precautions for user:** Tunnel code - 3

**14.7 Transport in bulk according to Annex II of MARPOL 73/78 and the IBC code**

Applicable for Maritime bulk transport only. Check with carrier.

---

## 15. REGULATORY INFORMATION

### 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture.

This substance is classified and labelled in accordance with regulation 1272/2008 and Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, including amendments.

### 15.2 Chemical Safety Assessment (CSA)

CSA not undertaken for this substance

---

## 16. OTHER INFORMATION

### Abbreviations:

Acute Tox. 4 (Oral)	Acute Toxicity Category 4 (Oral)
Aquatic Acute 2	Aquatic Acute Category 2
Eye Dam. 1	Eye Damage Category 1
Eye Irrit. 2	Eye Irritation Category 2
Flam. Liq. 1	Flammable Liquid Category 1
LC/LD50	Lethal Concentration/Dose 50%
NOAEL	No Observed Adverse Effect Level
PBT	Persistent, Bioaccumulative, Toxic
Skin Irrit. 2	Skin Irritation Category 2
Skin Sens. 1	Skin Sensitisation Category 1
STOT	Specific Target Organ Toxicity
vPvB	very Persistent, very Bioaccumulative

### Other Hazard Information assigned to individual ingredients, but not carried to final classification:

H302	Harmful if swallowed
H314	Causes severe skin burns and eye damage
H315	Causes skin irritation
H317	May cause an allergic skin reaction





H319 Causes serious eye irritation  
H411 Toxic to aquatic life with long lasting effects

**SDS information:**

This safety data sheet is compiled using data submitted for raw materials and practical experience. This product is intended for professional users only.

This Safety Data Sheet is prepared in compliance with regulation 1272/2008 and Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, including amendments.

THE INFORMATION GIVEN HEREIN IS, TO THE BEST OF OUR KNOWLEDGE, CORRECT AND IS PRESENTED IN GOOD FAITH BUT NO WARRANTY, EXPRESSED OR IMPLIED IS GIVEN.