



259


CUSTOMIZED

AUTO-BLOQUEO SELF-LOCKING COUPLE D'AUTOBLOCAGE SELBSTHEMMUNG	✓
RUEDA DE BRONCE BRONZE WHEEL ROUE EN BRONZE GETRIEBERAD AUS BRONZE	✓
EJE DELANTERO Y POSTERIOR FRONT AND REAR SHAFT ARBRE ARRIERE VORDERWELLE UND HINTERWELLE	✓
SENSOR HALL HALL SENSOR CAPTEUR HALL HALLSENSOR	✓

Y MUCHO MÁS - AND MANY MORE
ET BEAUCOUP D'AUTRES - UND VIELEN ANDEREN




REFERENCIA REFERENCE NUMBER REFERENZNUMMERN	TENSION NOMINAL NOMINAL VOLTAGE TENSION NOMINALE NENNSPANNUNG	PAR NOMINAL NOMINAL TORQUE COUPLE NOMINAL DREHMOMENT NOMINAL	VELOCIDAD NOMINAL NOMINAL SPEED VITESSE NOMINALE GESCHWINDIGKEIT NOMINAL	CORRIENTE NOMINAL NOMINAL CURRENT COURANT NOMINAL NOMINALSTROM	PAR DE ARRANQUE STARTING TORQUE COUPLE DE DEMARRAGE ANZUGSDREHMOMENT	CORRIENTE DE ARRANQUE STARTING CURRENT COURANT DE DEMARRAGE ANLAUFSTROM	EJE SHAFT ARBRE WELLE	CONEXIONES CONNECTIONS CONNEXIONS ANSCHLUSSART	ESQUEMA ELECTRICO WIRING DIAGRAM SCHEMA ELECTRIQUE SCHALTBLD	RELACION DE REDUCCION TRANSMISSION RATIO RAPPORT DE REDUCTEUR UNTERSEITZUNG	PESO APROXIMADO APPROXIMATE WEIGHT POIDS APPROXIMATIF GEWICHT (ca.)	GRADO DE ESTANQUEIDAD WATER TIGHTNESS ETANCHEITE FEUCHTIGKEITSSCHUTZKLASSE	MATERIAL RUEDA WHEEL MATERIAL MATERIAU ROUE MAT. DES SCHNECKENRADES	DESIGN: A,B,C DESSIN: A,B,C ABBILDUNG: A,B,C	CURVA CURVE KURVE
	Un (V)	Mn (N.m./lbf.in)	n (r.p.m.)	In (A)	Ma (N.m./lbf.in)	Ia (A)				i	P (kg/lb.t)	IP			
259.3710.20.00	12	20 / 177	22	12	130 / 1150	60	E37	C34	EE2	50:1	5.90 / 15.80	IP53	PLA	a	20
259.3710.30.00	24	20 / 177	22	6	130 / 1150	30	E37	C34	EE2	50:1	5.90 / 15.80	IP53	PLA	a	20
259.9001.20.00	12	15 / 132.7	40	18	120 / 1062	98	E37	C34	F2	50:1	5.90 / 15.80	IP53	PLA	a	21
259.9001.30.00	24	15 / 132.7	40	9	120 / 1062	49	E37	C34	F2	50:1	5.90 / 15.80	IP53	PLA	a	21
259.9008.30.00	24	25 / 221	25	7	135 / 1195	30	E37/E51	C34	EE2	50:1	5.90 / 15.80	IP40	PLA	b	22
259.9016.30.00	24	20 / 177	22	6	130 / 1150	30	E37	C34	EE2	50:1	5.90 / 15.80	IP53	CEL	a	20
259.9027.20.00	12	20 / 177	22	12	130 / 1150	60	E61/E62	C40	EE1	50:1	6.0 / 16.07	IP53	CEL	c	20




mm / inch

DOGA


EJE - SHAFT - ARBRE - WELLE




E61



E62




E37




E51


ESQUEMA ELÉCTRICO - WIRING DIAGRAM - SCHÉME ÉLECTRIQUE - SCHALTBIKD



EE1




EE2




F2

CONEXIONES - CONNECTIONS - CONNEXIONS - ANSCHLUSSART




C40




C34


CURVAS - CURVES - COURBES - KURVEN



20



21



22