

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

EVERBUILD Wood Filler 2-Part High Performance (A)

Revision Date 27.07.2017

Version 2.1



BUILDING TRUST



Print Date 27.07.2017

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade name : EVERBUILD Wood Filler 2-Part High Performance (A)

1.2 Relevant identified uses of the substance or mixture and uses advised against

1.3 Details of the supplier of the safety data sheet

Company : Everbuild – A Sika Company
Site 41
Knowsthorpe Way
Cross Green Industrial Estate
Leeds
West Yorkshire LS9 0SW
United Kingdom

Telephone : 0113 240 3456

E-mail address : everbuild.sds@uk.sika.com

1.4 Emergency telephone number

Emergency telephone number : 0044 113 240 3456 (office hours only)

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Type of product : Mixture

Classification (REGULATION (EC) No 1272/2008)

Eye irritation, Category 2 H319: Causes serious eye irritation.

Skin sensitisation, Category 1 H317: May cause an allergic skin reaction.

Acute aquatic toxicity, Category 1 H400: Very toxic to aquatic life.

Chronic aquatic toxicity, Category 1 H410: Very toxic to aquatic life with long lasting effects.

2.2 Label elements

Labelling (REGULATION (EC) No 1272/2008)

Hazard pictograms :



Signal word : Warning

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

EVERBUILD Wood Filler 2-Part High Performance (A)

Revision Date 27.07.2017

Version 2.1



BUILDING TRUST



Print Date 27.07.2017

Hazard statements	: H317 H319 H410	May cause an allergic skin reaction. Causes serious eye irritation. Very toxic to aquatic life with long lasting effects.
Precautionary statements	: Prevention: P261 P273 P280 Response: P333 + P313 P337 + P313 P362 + P364	Avoid breathing dust/ fume/ gas/ mist/ vapours/ spray. Avoid release to the environment. Wear protective gloves/ eye protection/ face protection. If skin irritation or rash occurs: Get medical advice/ attention. If eye irritation persists: Get medical advice/ attention. Take off contaminated clothing and wash it before reuse.

Hazardous components which must be listed on the label:

- 202-327-6 dibenzoyl peroxide

2.3 Other hazards

This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher.

SECTION 3: Composition/information on ingredients

3.2 Mixtures

Hazardous components

Chemical name CAS-No. EC-No. Registration number	Classification (REGULATION (EC) No 1272/2008)	Concentration [%]
dibenzoyl peroxide 94-36-0 202-327-6 01-2119511472-50-XXXX	Org. Perox.B; H241 Eye Irrit.2; H319 Skin Sens.1; H317 Aquatic Acute1; H400 Aquatic Acute1; H400 Aquatic Chronic1; H410	>= 40 - < 60

For the full text of the H-Statements mentioned in this Section, see Section 16.

SECTION 4: First aid measures

4.1 Description of first aid measures

General advice : Move out of dangerous area.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

EVERBUILD Wood Filler 2-Part High Performance (A)

Revision Date 27.07.2017

Version 2.1



BUILDING TRUST



Print Date 27.07.2017

- Consult a physician.
Show this safety data sheet to the doctor in attendance.
- If inhaled : Move to fresh air.
Consult a physician after significant exposure.
- In case of skin contact : Take off contaminated clothing and shoes immediately.
Wash off with soap and plenty of water.
If symptoms persist, call a physician.
- In case of eye contact : Immediately flush eye(s) with plenty of water.
Remove contact lenses.
Keep eye wide open while rinsing.
If eye irritation persists, consult a specialist.
- If swallowed : Do not induce vomiting without medical advice.
Rinse mouth with water.
Do not give milk or alcoholic beverages.
Never give anything by mouth to an unconscious person.

4.2 Most important symptoms and effects, both acute and delayed

- Symptoms : Allergic reactions
Excessive lachrymation
See Section 11 for more detailed information on health effects and symptoms.
- Risks : irritant effects
sensitising effects
- May cause an allergic skin reaction.
Causes serious eye irritation.

4.3 Indication of any immediate medical attention and special treatment needed

- Treatment : Treat symptomatically.

SECTION 5: Firefighting measures

5.1 Extinguishing media

- Suitable extinguishing media : Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

5.2 Special hazards arising from the substance or mixture

- Specific hazards during fire-fighting : Do not allow run-off from fire fighting to enter drains or water courses.
- Hazardous combustion products : No hazardous combustion products are known

5.3 Advice for firefighters

- Special protective equipment : In the event of fire, wear self-contained breathing apparatus.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

EVERBUILD Wood Filler 2-Part High Performance (A)

Revision Date 27.07.2017

Version 2.1



BUILDING TRUST



Print Date 27.07.2017

for firefighters

Further information : Collect contaminated fire extinguishing water separately. This must not be discharged into drains. Fire residues and contaminated fire extinguishing water must be disposed of in accordance with local regulations.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

Personal precautions : Use personal protective equipment.
Deny access to unprotected persons.

6.2 Environmental precautions

Environmental precautions : Do not flush into surface water or sanitary sewer system. If the product contaminates rivers and lakes or drains inform respective authorities.

6.3 Methods and materials for containment and cleaning up

Methods for cleaning up : Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust).
Keep in suitable, closed containers for disposal.

6.4 Reference to other sections

For personal protection see section 8.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Advice on safe handling : Do not breathe vapours or spray mist. Avoid exceeding the given occupational exposure limits (see section 8). Do not get in eyes, on skin, or on clothing. For personal protection see section 8. Persons with a history of skin sensitisation problems or asthma, allergies, chronic or recurrent respiratory disease should not be employed in any process in which this mixture is being used. Smoking, eating and drinking should be prohibited in the application area. Follow standard hygiene measures when handling chemical products

Advice on protection against fire and explosion : Normal measures for preventive fire protection.

Hygiene measures : Handle in accordance with good industrial hygiene and safety practice. When using do not eat or drink. When using do not smoke. Wash hands before breaks and at the end of workday.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

EVERBUILD Wood Filler 2-Part High Performance (A)

Revision Date 27.07.2017

Version 2.1



BUILDING TRUST



Print Date 27.07.2017

7.2 Conditions for safe storage, including any incompatibilities

Requirements for storage areas and containers : Keep container tightly closed in a dry and well-ventilated place. Containers which are opened must be carefully re-sealed and kept upright to prevent leakage. Store in accordance with local regulations.

Other data : No decomposition if stored and applied as directed.

7.3 Specific end use(s)

Specific use(s) : No data available

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Components with workplace control parameters

Components	CAS-No.	Value	Control parameters *	Basis *
dibenzoyl peroxide	94-36-0	TWA	5 mg/m3	GB EH40

8.2 Exposure controls

Personal protective equipment

Eye protection : Safety glasses with side-shields conforming to EN166
Eye wash bottle with pure water

Hand protection : Chemical-resistant, impervious gloves complying with an approved standard must be worn at all times when handling chemical products. Reference number EN 374. Follow manufacturer specifications.

Suitable for short time use or protection against splashes:
Butyl rubber/nitrile rubber gloves (0,4 mm),
Contaminated gloves should be removed.
Suitable for permanent exposure:
Viton gloves (0.4 mm),
breakthrough time >30 min.

Skin and body protection : Protective clothing (e.g. Safety shoes acc. to EN ISO 20345, long-sleeved working clothing, long trousers). Rubber aprons and protective boots are additionally recommended for mixing and stirring work.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

EVERBUILD Wood Filler 2-Part High Performance (A)

Revision Date 27.07.2017

Version 2.1



BUILDING TRUST



Print Date 27.07.2017

Respiratory protection : Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.
organic vapor filter (Type A)
A1: < 1000 ppm; A2: < 5000 ppm; A3: < 10000 ppm
Ensure adequate ventilation. This can be achieved by local exhaust extraction or by general ventilation. (EN 689 - Methods for determining inhalation exposure). This applies in particular to the mixing / stirring area. In case this is not sufficient to keep the concentrations under the occupational exposure limits then respiration protection measures must be used.

Environmental exposure controls

General advice : Do not flush into surface water or sanitary sewer system.
If the product contaminates rivers and lakes or drains inform respective authorities.

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Appearance : liquid
Colour : white
Odour : pleasant
Odour Threshold : No data available
Flash point : Not applicable
Autoignition temperature : No data available
Decomposition temperature : No data available
Lower explosion limit (Vol-%) : No data available
Upper explosion limit (Vol-%) : No data available
Flammability : No data available
Explosive properties : No data available
Oxidizing properties : No data available
pH : No data available
Melting point/range / Freezing point : No data available
Boiling point/boiling range : No data available

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

EVERBUILD Wood Filler 2-Part High Performance (A)

Revision Date 27.07.2017

Version 2.1



BUILDING TRUST



Print Date 27.07.2017

Vapour pressure	: 0,01 hPa
Density	: ca. 1,14 g/cm ³ at 20 °C
Water solubility	: No data available
Partition coefficient: n-octanol/water	: No data available
Viscosity, dynamic	: No data available
Viscosity, kinematic	: > 20,5 mm ² /s at 40 °C
Relative vapour density	: No data available
Evaporation rate	: No data available

9.2 Other information

No data available

SECTION 10: Stability and reactivity

10.1 Reactivity

No dangerous reaction known under conditions of normal use.

10.2 Chemical stability

The product is chemically stable.

10.3 Possibility of hazardous reactions

Hazardous reactions : Stable under recommended storage conditions.

10.4 Conditions to avoid

Conditions to avoid : No data available

10.5 Incompatible materials

Materials to avoid : No data available

10.6 Hazardous decomposition products

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute toxicity

Not classified based on available information.

Components:

dibenzoyl peroxide:

Acute oral toxicity : LD50 Oral (Rat): > 5.000 mg/kg

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

EVERBUILD Wood Filler 2-Part High Performance (A)

Revision Date 27.07.2017

Version 2.1



BUILDING TRUST



Print Date 27.07.2017

Acute inhalation toxicity : LC50 (Rat): > 24,3 mg/l
Exposure time: 4 h
Test atmosphere: dust/mist

Skin corrosion/irritation

Not classified based on available information.

Serious eye damage/eye irritation

Causes serious eye irritation.

Respiratory or skin sensitisation

Skin sensitisation: May cause an allergic skin reaction.

Respiratory sensitisation: Not classified based on available information.

Germ cell mutagenicity

Not classified based on available information.

Carcinogenicity

Not classified based on available information.

Reproductive toxicity

Not classified based on available information.

STOT - single exposure

Not classified based on available information.

STOT - repeated exposure

Not classified based on available information.

Aspiration toxicity

Not classified based on available information.

SECTION 12: Ecological information

12.1 Toxicity

Components:

dibenzoyl peroxide :

M-Factor (Acute aquatic toxicity) : 10

M-Factor (Chronic aquatic toxicity) : 10

12.2 Persistence and degradability

No data available

12.3 Bioaccumulative potential

No data available

12.4 Mobility in soil

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

EVERBUILD Wood Filler 2-Part High Performance (A)

Revision Date 27.07.2017

Version 2.1



BUILDING TRUST



Print Date 27.07.2017

No data available

12.5 Results of PBT and vPvB assessment

Product:

Assessment : This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher.

12.6 Other adverse effects

Product:

Additional ecological information : An environmental hazard cannot be excluded in the event of unprofessional handling or disposal.
Very toxic to aquatic life with long lasting effects.

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Product : The generation of waste should be avoided or minimized wherever possible.
Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe way.
Dispose of surplus and non-recyclable products via a licensed waste disposal contractor.
Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements.
Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers.

Contaminated packaging : 15 01 10* packaging containing residues of or contaminated by dangerous substances

SECTION 14: Transport information

ADR

14.1 UN number : 3108
14.2 UN proper shipping name : ORGANIC PEROXIDE TYPE E, SOLID (dibenzoyl peroxide)
14.3 Transport hazard class(es) : 5.2
Classification Code : P1
Labels : 5.2

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

EVERBUILD Wood Filler 2-Part High Performance (A)

Revision Date 27.07.2017

Version 2.1



BUILDING TRUST



Tunnel restriction code : (D)
14.5 Environmental hazards : yes

IATA

14.1 UN number : 3108
14.2 UN proper shipping name : Organic peroxide type E, solid
(dibenzoyl peroxide)
14.3 Transport hazard class(es) : 5.2
Labels : 5.2 (HEAT)
14.5 Environmental hazards : yes

IMDG

14.1 UN number : 3108
14.2 UN proper shipping name : ORGANIC PEROXIDE TYPE E, SOLID
(dibenzoyl peroxide)
14.3 Class : 5.2
Labels : 5.2
EmS Number 1 : F-J
EmS Number 2 : S-R
14.5 Marine pollutant : yes
dibenzoyl peroxide

14.6 Special precautions for user

No data available

14.7 Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

Prohibition/Restriction

REACH - Restrictions on the manufacture, placing on the market and use of certain dangerous substances, preparations and articles (Annex XVII) : Not applicable

REACH - Candidate List of Substances of Very High Concern for Authorisation (Article 59). : None of the components are listed
(=> 0.1 %).

REACH - List of substances subject to authorisation (Annex XIV) : Not applicable

REACH Information: All substances contained in our Products are
- preregistered or registered by our upstream suppliers, and/or
- preregistered or registered by us, and/or
- excluded from the regulation, and/or
- exempted from the registration.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

EVERBUILD Wood Filler 2-Part High Performance (A)

Revision Date 27.07.2017

Version 2.1

Print Date 27.07.2017



BUILDING TRUST



Seveso III: Directive 2012/18/EU of the European Parliament and of the Council on the control of major-accident hazards involving dangerous substances.

E1	ENVIRONMENTAL HAZARDS	Quantity 1 100 t	Quantity 2 200 t
----	--------------------------	---------------------	---------------------

VOC-CH (VOCV) : no VOC duties

VOC-EU (solvent) : Not applicable

If other regulatory information applies that is not already provided elsewhere in the Safety Data Sheet, then it is described in this subsection.

Health, safety and environmental regulation/legislation specific for the substance or mixture: : Environmental Protection Act 1990 & Subsidiary Regulations
Health and Safety at Work Act 1974 & Subsidiary Regulations
Control of Substances Hazardous to Health Regulations (COSHH)
May be subject to the Control of Major Accident Hazards Regulations (COMAH), and amendments.

15.2 Chemical safety assessment

This product contains substances for which Chemical Safety Assessments are still required.

SECTION 16: Other information

Full text of H-Statements

H241	Heating may cause a fire or explosion.
H317	May cause an allergic skin reaction.
H319	Causes serious eye irritation.
H400	Very toxic to aquatic life.
H410	Very toxic to aquatic life with long lasting effects.

Full text of other abbreviations

Aquatic Acute	Acute aquatic toxicity
Aquatic Chronic	Chronic aquatic toxicity
Eye Irrit.	Eye irritation
Org. Perox.	Organic peroxides
Skin Sens.	Skin sensitisation
ADR	Accord européen relatif au transport international des marchandises Dangereuses par Route
CAS	Chemical Abstracts Service
DNEL	Derived no-effect level
EC50	Half maximal effective concentration
GHS	Globally Harmonized System
IATA	International Air Transport Association
IMDG	International Maritime Code for Dangerous Goods
LD50	Median lethal dosis (the amount of a material, given all at once, which causes the death of 50% (one half) of a group of test animals)
LC50	Median lethal concentration (concentrations of the chemical in air that

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

EVERBUILD Wood Filler 2-Part High Performance (A)

Revision Date 27.07.2017

Version 2.1

Print Date 27.07.2017



BUILDING TRUST



MARPOL	kills 50% of the test animals during the observation period) International Convention for the Prevention of Pollution from Ships, 1973 as modified by the Protocol of 1978
OEL	Occupational Exposure Limit
PBT	Persistent, bioaccumulative and toxic
PNEC	Predicted no effect concentration
REACH	Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency
SVHC	Substances of Very High Concern
vPvB	Very persistent and very bioaccumulative

The information contained in this Safety Data Sheet corresponds to our level of knowledge at the time of publication. All warranties are excluded. Our most current General Sales Conditions shall apply. Please consult the product data sheet prior to any use and processing.

Changes as compared to previous version !