



RM45N

miniature relays



- DC coils - of up to 24 V DC, low coil power 0,20 W (sensitive version) or 0,45 W (standard version)
- For PCB • Very small dimensions, light weight
- High load up to 10 A / 125 V AC ❶
- Applications: for household electrical appliance, automation systems, electrical equipment, instrument and meter, telecommunication devices, remote control facilities, light controllers, etc.
- Recognitions, certifications, directives: RoHS,  

Contact data

Number and type of contacts	1 CO, 1 NO		
Contact material	AgSnO₂		
Rated / max. switching voltage	AC	250 V / 277 V	
Min. switching voltage	5 V		
Rated load	AC1	1 CO: 5 A / 5 A (NO/NC) / 250 V AC 1 CO: 10 A / 125 V AC ❶	1 NO: 5 A / 250 V AC 1 NO: 10 A / 125 V AC
	DC1	1 CO: 5 A / 5 A (NO/NC) / 28 V DC	1 NO: 5 A / 28 V DC
Rated current	5 A		
Max. breaking capacity	AC1	1 250 VA	
	AC3	186 W	0,25 HP UL 508 (single-phase motor)
Contact resistance	≤ 100 mΩ		
Coil data			
Rated voltage	DC	5 ... 24 V	
Must release voltage	DC: ≥ 0,05 U _n		
Operating range of supply voltage	see Tables 1, 2		
Rated power consumption	DC	0,20 W sensitive version ❶	0,45 W standard version
Insulation according to PN-EN 60664-1			
Insulation resistance	100 MΩ 500 V DC, 60 s		
Dielectric strength	• between coil and contacts	4 000 V AC	type of insulation: reinforced
	• contact clearance	1 000 V AC	type of clearance: micro-disconnection
General data			
Operating / release time (typical values)	8 ms / 5 ms		
Electrical life (number of cycles)	• resistive AC1 1 800 cycles/hour	10 ⁵ 1 CO: 5 A / 5 A (NO/NC), 250 V AC	1 NO: 5 A, 250 V AC
	• resistive DC1 1 800 cycles/hour	10 ⁵ 1 CO: 5 A / 5 A (NO/NC), 28 V DC	1 NO: 5 A, 28 V DC
Mechanical life 18 000 cycles/hour	10 ⁷		
Dimensions (L x W x H)	20,5 x 10,6 x 15,6 mm		
Weight	7 g		
Ambient temperature • operating	-40...+70 °C		
Cover protection category	IP 64	PN-EN 60529	
Shock resistance	10 g		
Vibration resistance	1,5 mm DA (constant amplitude) 10...55 Hz		
Solder bath temperature	max. 235 °C		
Soldering time	max. 3 s		


The data in bold type relate to the standard versions of the relays.

❶ Only for contacts 1 NO


RM45N

miniature relays


Dimensions



Connection diagrams (pin side view)



Pinout (solder side view)



Mounting

Relays **RM45N** are designed for direct PCB mounting.

PRECAUTIONS:

1. Ensure that the parameters of the product described in its specification provide a safety margin for the appropriate operation of the device or system and never use the product in circumstances which exceed the parameters of the product. 2. Never touch any live parts of the device. 3. Ensure that the product has been connected correctly. An incorrect connection may cause malfunction, excessive heating or risk of fire. 4. In case of any risk of any serious material loss or death or injuries of humans or animals, the devices or systems shall be designed so to equip them with double safety system to guarantee their reliable operation.

RM45N

miniature relays

Coil data - DC voltage version, sensitive

Table 1

Coil code ❶	Rated voltage V DC	Coil resistance at 20 °C Ω	Acceptable resistance	Coil operating range V DC	
				min. (at 20 °C)	max. (at 20 °C)
S005	5	125	± 10%	3,75	5,5
S009	9	405	± 10%	6,75	9,9
S012	12	720	± 10%	9,00	13,2
S024	24	2 880	± 10%	18,00	26,4


❶ Only for contacts 1 NO

Coil data - DC voltage version, standard

Table 2

Coil code	Rated voltage V DC	Coil resistance at 20 °C Ω	Acceptable resistance	Coil operating range V DC	
				min. (at 20 °C)	max. (at 20 °C)
1005	5	56	± 10%	3,75	5,5
1009	9	180	± 10%	6,75	9,9
1012	12	320	± 10%	9,00	13,2
1024	24	1 280	± 10%	18,00	26,4

Ordering codes



Examples of ordering codes:

RM45N-3021-85-S012

relay **RM45N**, for PCB, one normally open contact, contact material AgSnO₂, sensitive coil voltage 12 V DC, in cover IP 64

RM45N-3011-85-1024

relay **RM45N**, for PCB, one changeover contact, contact material AgSnO₂, standard coil voltage 24 V DC, in cover IP 64