

FOR CHEMICAL EMERGENCY:

During Business Hours: (800) 966-3458 | Outside Business Hours: (800) 420-7186



ACCORDING TO EC-REGULATIONS 1907/2006 (REACH), 1272/2008 (CLP) & 2015/830

1. SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1 Product identifier

Product Name Gorilla Sealant Clear (100% Silicone Sealant)
CAS No. Mixture.
EC No. Mixture.
REACH Registration No. Mixture.

1.2 Relevant identified uses of the substance or mixture and uses advised against

Identified Use(s) Sealant.
Uses Advised Against None known.

1.3 Details of the supplier of the safety data sheet

Company Identification Gorilla Glue Europe Ltd.
Address of Manufacturer Chorley Business & Technology Centre
East Terrace
Euxton Lane
Chorley, United Kingdom.

Postal code PR7 6TE
Telephone: 01257 241319
Fax 01257 273820
E-mail eusales@gorillaglu.com

1.4 Emergency telephone number

Emergency Phone No. +44 (0) 1257 241319 (During Business Hours)
+1 651-603-3429 (Outside Business Hours)

National response center
Address National Poisons Information Service (Birmingham Centre)
City Hospital
Dudley Road,
Birmingham,
United Kingdom

Emergency Phone No. +00 448 706 006 266 NHS Direct - 0845 4647 / 111

2. SECTION 2: HAZARDS IDENTIFICATION

2.1 Classification of the substance or mixture

Regulation (EC) No. 1272/2008 (CLP) Eye Irrit. 2: Causes serious eye irritation.
Skin Irrit. 2: Causes skin irritation.

FOR CHEMICAL EMERGENCY:

During Business Hours: (800) 966-3458 | Outside Business Hours: (800) 420-7186



2.2 Label elements

Product Name

According to Regulation (EC) No. 1272/2008 (CLP)
Gorilla Sealant Clear (100% Silicone Sealant)

Hazard Pictogram(s)



GHS07

Signal Word(s)

Warning.

Hazard Statement(s)

H315: Causes skin irritation.
H319: Causes serious eye irritation.

Precautionary Statement(s)

P102: Keep out of reach of children.
P280: Wear protective gloves/protective clothing/eye protection/face protection.
P302+P352: IF ON SKIN: Wash with plenty of water.
P305+P351+P338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P332+P313: If skin irritation occurs: Get medical advice/attention.
P337+P31: If eye irritation persists: Get medical advice/attention.
P362+P364: Take off contaminated clothing and wash it before reuse.

2.3 Other hazards

None known.

2.4 Additional Information

For full text of H/P Statements see section 16.

3. SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

3.1 Substances

Not applicable.

3.2 Mixtures

HAZARDOUS INGREDIENT(S)	CAS No.	EC No. / REACH Registration No.	%W/W	Hazard Statement(s)	Hazard Pictogram(s)
Silicon dioxide	7631-86-9	231-545-4 / 01-2119379499-16-0000	7-13	Not classified	

FOR CHEMICAL EMERGENCY:

During Business Hours: (800) 966-3458 | Outside Business Hours: (800) 420-7186



Distillates (petroleum), hydrotreated middle Gasoil - unspecified	64742-46-7	265-148-2 / 01-2119489867-12-0000	7-13	Not classified	
Triacetoxysilane	17689-77-9	241-677-4 / 01-2119881778-15-0000	0,1-1	Acute Tox. 4 H302 Skin Corr. 1B H314 Eye Dam. 1 H318	GHS07 GHS05
Methylsilanetriyl triacetate	4253-34-3	224-221-9 / 01-2119962266-32-0000	0,1-1	Acute Tox. 4 H302 Skin Corr. 1C H314	GHS07 GHS05
Acetic acid	64-19-7	200-580-7 / 01-2119475328-30-0000	< 0,1	Flam. Liq. 3 H226 Skin Corr. 1A H314	GHS02 GHS05
Acetic anhydride	108-24-7	203-564-8 / 01-2119486470-36-0000	< 0,1	Flam. Liq. 3 H226 Acute Tox. 4 H302 Skin Corr. 1B H314 Acute Tox. 4 H332	GHS02 GHS07 GHS05
p-[(diiodomethyl)sulphonyl]toluene	20018-09-1	243-468-3	< 0,1	Eye Dam. 1 H318 Acute Tox. 3 H331 Aquatic Acute 1 H400	GHS05 GHS06 GHS09

4. SECTION 4: FIRST AID MEASURES

4.1 Description of first aid measures

Inhalation If breathing is difficult, remove victim to fresh air and keep at rest in a position comfortable for breathing.

Skin Contact IF ON SKIN: Wash with plenty of water. If skin irritation occurs: Get medical advice/attention.

Eye Contact IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.

Ingestion Wash out mouth with water.

4.2 Most important symptoms and effects, both acute and delayed

None anticipated.

4.3 Indication of any immediate medical attention and special treatment needed

Unlikely to be required but if necessary treat symptomatically.

5. SECTION 5: FIREFIGHTING MEASURES

Non-flammable.

FOR CHEMICAL EMERGENCY:

During Business Hours: (800) 966-3458 | Outside Business Hours: (800) 420-7186



5.1 Extinguishing media

Suitable Extinguishing media As appropriate for surrounding fire.
 Unsuitable extinguishing media None known.

5.2 Special hazards arising from the substance or mixture

Decomposes in a fire giving off toxic fumes: Formaldehyde. Acetic acid is formed upon contact with water or humid air.

5.3 Advice for firefighters

Fire fighters should wear complete protective clothing including self-contained breathing apparatus.

6. SECTION 6: ACCIDENTAL RELEASE MEASURES

6.1 Personal precautions, protective equipment and emergency procedures

Provide adequate ventilation. Wear protective gloves/protective clothing/eye protection/face protection. Take off contaminated clothing and wash it before reuse.

6.2 Environmental precautions

Do not release large quantities into the surface water or into drains.

6.3 Methods and material for containment and cleaning up

Adsorb spillages onto sand, earth or any suitable adsorbent material. Transfer to a container for disposal.

6.4 Reference to other sections

See Also Section 8, 13.

7. SECTION 7: HANDLING AND STORAGE

7.1 Precautions for safe handling

Ensure adequate ventilation. Wash hands thoroughly after handling. Wear protective gloves/protective clothing/eye protection/face protection. Do not eat, drink or smoke at the work place.

7.2 Conditions for safe storage, including any incompatibilities

Keep container in a well-ventilated place.

Storage temperature

Ambient.

Storage life

Stable under normal conditions.

Incompatible materials

Strong oxidising agents.

7.3 Specific end use(s)

Sealant.

8. SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1 Control parameters

8.1.1 Occupational Exposure Limits

Substances	CAS No.	LTEL (8 hr TWA ppm)	LTEL (8 hr TWA mg/m ³)	STEL (ppm)	STEL (mg/m ³)	Note
Silicon dioxide (Inhalable Dust)	7631-86-9	0	6	0	0	
Silicon dioxide (Respirable Dust)	7631-86-9	0	2.4	0	0	

FOR CHEMICAL EMERGENCY:

During Business Hours: (800) 966-3458 | Outside Business Hours: (800) 420-7186



Acetic anhydride	108-24-7	0.5	2.5	2	10	
------------------	----------	-----	-----	---	----	--

Source: WEL: Workplace Exposure Limit (UK HSE EH40)

8.2 Exposure controls

8.2.1. Appropriate engineering controls Use with ventilation, local exhaust ventilation or breathing protection. A washing facility/water for eye and skin cleaning purposes should be present.

8.2.2. Personal protection equipment



Eye Protection

Wear eye protection with side protection (EN166).



Skin protection

Wear protective clothing and gloves: Impervious gloves (EN 374).



Respiratory protection

Wear suitable respiratory protective equipment if exposure to levels above the occupational exposure limit is likely.



Thermal hazards

Not applicable.

8.2.3. Environmental Exposure Controls

Do not release large quantities into the surface water or into drains.

9. SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

9.1 Information on basic physical and chemical properties

Appearance	Paste.
Colour	Colourless/Clear/Slightly hazy.
Odour	Smells of acetic acid.
Odour threshold	Not established.
pH	Not available.
Melting point/freezing point	Not available.
Initial boiling point and boiling range	Not available.
Flash Point	>100 °C [Closed cup]
Evaporation rate	Not available.
Flammability (solid, gas)	Not applicable.
Upper/lower flammability or explosive limits	Not applicable.
Vapour pressure	Not available.
Vapour density	Not available.
Density (g/ml)	Not available.
Relative density	1.007

FOR CHEMICAL EMERGENCY:

During Business Hours: (800) 966-3458 | Outside Business Hours: (800) 420-7186



Solubility(ies)	Solubility (Water) : Not known.
	Solubility (Other) : Not known.
Partition coefficient: n-octanol/water	Not available.
Auto-ignition temperature	Not available.
Decomposition Temperature (°C)	Not available.
Viscosity	Not applicable.
Explosive properties	Not explosive.
Oxidising properties	Not oxidising.
9.2 Other information	
	None.

10. SECTION 10: STABILITY AND REACTIVITY

10.1 Reactivity

Stable under normal conditions.

10.2 Chemical Stability

Stable under normal conditions.

10.3 Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose.

10.4 Conditions to avoid

Heat and direct sunlight.

10.5 Incompatible materials

Strong oxidising agents.

10.6 Hazardous decomposition products

No hazardous decomposition products known.

11. SECTION 11: TOXICOLOGICAL INFORMATION

11.1 Information on toxicological effects

Acute toxicity	Low acute toxicity.
Skin corrosion/irritation	Causes skin irritation. No data.
Serious eye damage/irritation	Causes serious eye irritation. No data.
Skin sensitisation data	Not classified.
Respiratory sensitisation data	Not classified.
Germ cell mutagenicity	There is no evidence of mutagenic potential.
Carcinogenicity	No evidence of carcinogenicity. Classified based on the conditions cited in Nota N (Regulation (EC) 1272/2008, Annex VI, Part 3, Note N)
Reproductive toxicity	Not classified.
Lactation	Not classified.

FOR CHEMICAL EMERGENCY:

During Business Hours: (800) 966-3458 | Outside Business Hours: (800) 420-7186



STOT - single exposure
STOT - repeated exposure
Aspiration hazard

None anticipated.
None anticipated.
Not classified.

11.2 Other information

Not known.

12. SECTION 12: ECOLOGICAL INFORMATION

12.1 Toxicity

Low toxicity to aquatic organisms.

12.2 Persistence and Degradation

No information available.

12.3 Bioaccumulative potential

No information available.

12.4 Mobility in soil

No information available.

12.5 Results of PBT and vPvB assessment

Not classified as PBT or vPvB.

12.6 Other adverse effects

Not known.

13. SECTION 13: DISPOSAL CONSIDERATIONS

13.1 Waste treatment methods

This product has been evaluated for RCRA characteristics and does not meet the criteria of hazardous waste if discarded in its purchased form.

13.2 Additional Information

Disposal should be in accordance with local, state or national legislation.

14. SECTION 14: TRANSPORT INFORMATION

Not classified as hazardous for transport.

15. SECTION 15: REGULATORY INFORMATION

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

European Regulations - Authorisations and/or Restrictions On Use

Candidate List of Substances of Very Not listed.

High Concern for Authorisation

FOR CHEMICAL EMERGENCY:

During Business Hours: (800) 966-3458 | Outside Business Hours: (800) 420-7186



REACH: ANNEX XIV list of substances Not listed.
subject to authorisation

REACH: Annex XVII Restrictions on the manufacture, placing on the market and use of certain dangerous substances, mixtures and articles
Listed: Distillates (petroleum), hydrotreated middle Gasoil – unspecified (CAS No.: 64742-46-7)

Community Rolling Action Plan (CoRAP)
Listed: Silicon dioxide (CAS No.: 7631-86-9)

Regulation (EC) N° 850/2004 of the European Parliament and of the Council on persistent organic pollutants
Not listed.

Regulation (EC) N° 2037/2000 on substances that deplete the ozone layer
Not listed.

Regulation (EU) N° 649/2012 of the European Parliament and of the Council concerning the export and import of hazardous chemicals
Not listed.

National regulations

Other
Not known.

15.2 Chemical Safety Assessment

A REACH chemical safety assessment has not been carried out.

16. SECTION 16: OTHER INFORMATION

The following sections contain revisions or new statements: 1-16

LEGEND

Hazard Pictogram(s)



GHS07

- GHS05: GHS: corrosive
- GHS02: GHS: flame
- GHS06: GHS: skull and crossbones
- GHS09: GHS: fish and tree

Hazard Statement(s)

- H226: Flammable liquid and vapour.
- H302: Harmful if swallowed.
- H314: Causes severe skin burns and eye damage.
- H315: Causes skin irritation.
- H318: Causes serious eye damage.
- H319: Causes serious eye irritation.
- H331: Toxic if inhaled.
- H332: Harmful if inhaled.

FOR CHEMICAL EMERGENCY:

During Business Hours: (800) 966-3458 | Outside Business Hours: (800) 420-7186



H400: Very toxic to aquatic life.

Precautionary Statement(s)

P264: Wash hands thoroughly after handling.

Acronyms

CAS: Chemical Abstracts Service
CLP: Regulation (EC) No 1272/2008 on classification, labelling and packaging of substances and mixtures
EC: European Community
EINECS: European Inventory of Existing Commercial Chemical Substances
LTEL: Long Term Exposure Limit
PBT: Persistent, Bioaccumulative and Toxic
REACH: Registration, Evaluation, Authorisation and Restriction of Chemicals
STEL: Short Term Exposure Limit
STOT: Specific Target Organ Toxicity
vPvB: very Persistent and very Bioaccumulative
RCRA: Resource Conservation and Recovery Act

Disclaimers

The information presented in this Safety Data Sheet was prepared by qualified personnel and to the best of our knowledge is true and accurate. The information and recommendations are furnished for this product with the understanding that the purchaser will independently determine the suitability of the product for this purpose. This data does not constitute a warranty, expressed or implied, statutory or otherwise, nor is it representation for which The Gorilla Glue Company assumes legal responsibility. The data is submitted for the user's information and consideration only. Any use of this product must be determined by the user to be in accordance with applicable federal, state, provincial and local laws and regulations.

Annex to the extended Safety Data Sheet (eSDS)

Not available.