

## Product information

# 97 52 63 DG

## Four-Mandrel Crimping Pliers for turned contacts




- Crimping capacity can be adjusted in increments of 0.01 mm
- With digital display of the preset crimping capacities and possibility of re-calibration via RESET function with electronic wear monitoring
- Adjustment in mm, inches or comparable selection positions according to MIL
- Pliers in a plastic case with foam insert and standard locator for precise positioning of the contacts
- For crimping turned contacts
- Four-mandrel crimping for top-quality crimping connections
- Mandrel gauge to check the basic setting
- Repetitive, high crimping quality due to integral lock (self-releasing mechanism)
- Optimum transmission of force due to highly effective lever action for fatigue-reduced operation
- High operation comfort thanks to handy shape
- Chrome vanadium electric steel in special quality, oil-hardened

### General

|             |                            |
|-------------|----------------------------|
| Article No. | 97 52 63 DG                |
| EAN         | 4003773063209              |
| Pliers      | chrome plated              |
| Head        | chrome plated              |
| Handles     | with multi-component grips |
| weight      | 388 g                      |
| Dimensions  | 195 x 82 x 19 mm           |
| Reach       | yes                        |
| RohS        | no                         |

### Technical details



|                                |                            |
|--------------------------------|----------------------------|
| Applications                   | turned contacts            |
| Capacity in square millimetres | 0.08 — 2.5 mm <sup>2</sup> |
| AWG                            | 28 — 14                    |
| Number of crimping positions   | 1                          |
| Max. contact diameter          | 5 mm                       |

### Classification

|                |            |
|----------------|------------|
| eCl@ss 5.1.4   | 21040301   |
| ETIM 5.0       | EC000168   |
| ETIM 6.0       | EC000168   |
| proficl@ss 6.0 | AAA946c003 |
| UNSPSC 13.1    | 27112147   |

technical change and errors excepted



Standard locator