

Product information

97 52 65 DG A

Four-Mandrel Crimping Pliers for turned contacts



- Crimping capacity can be adjusted in increments of 0.01 mm
- With digital display of the preset crimping capacities and possibility of re-calibration via RESET function with electronic wear monitoring
- Adjustment in mm, inches or comparable selection positions according to MIL
- With table for calculating the settings
- Pliers in a plastic case with foam insert
- Without locator
- For crimping turned contacts
- Four-mandrel crimping for top-quality crimping connections
- Mandrel gauge to check the basic setting
- Repetitive, high crimping quality due to integral lock (self-releasing mechanism)
- Optimum transmission of force due to highly effective lever action for fatigue-reduced operation
- High operation comfort thanks to handy shape
- Chrome vanadium electric steel in special quality, oil-hardened

General

Article No.	97 52 65 DG A
EAN	4003773071990
Pliers	chrome plated
Head	chrome plated
Handles	with multi-component grips
weight	633 g
Dimensions	250 x 86 x 19 mm
Reach	yes
RohS	no

Technical details



Applications	turned contacts (Harting; Ilme; Phoenix; Amphenol; Walther; HTS; Contact; Weidmüller)
Capacity in square millimetres	0.14 — 6 mm ²
AWG	26 — 10
Number of crimping positions	1
Max. contact diameter	7.5 mm

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC000168
ETIM 6.0	EC000168
proficl@ss 6.0	AAA946c003
UNSPSC 13.1	27112147

Accessories

97 59 65 2	Universal Locator for 97 52 65 / 97 52 65 A / 97 52 65 DG / 97 52 65 DG A
------------	---

technical change and errors excepted