


5.08mm low profile 90° rising clamp terminal blocks

Product overview


- 2 and 3 pole double interlocking mechanism for increased strength
- 4-12 solid block end stackable
- Moulded in green UL94-V0 flame retardant PA66
- Professional rising clamp terminals
- Cable acceptance - 0.1-2.8mm² (26-14AWG)
- Guided pin alignment
- Captive screw
-  approved

CTBP0558



SPECIFICATION	
Rating	UL=12A/300V
Impulse withstand voltage	1.6kV
Working temperature	-40°C to +105°C
Moulding	UL94-V0 flame retardant PA66
Pin/terminal	Tinned, nickel plated brass
Rising clamp	Tinned, nickel plated brass
Screw/torque	M2.5 steel zinc plated, 0.4Nm
Recommended PCB hole size	ø1.3mm

PART NO.	POLES	LENGTH
CTBP0558/2	2	10.16mm
CTBP0558/3	3	15.24mm
CTBP0558/4	4	20.32mm
CTBP0558/5	5	25.4mm
CTBP0558/6	6	30.48mm
CTBP0558/7	7	35.56mm
CTBP0558/8	8	40.64mm
CTBP0558/9	9	45.72mm
CTBP0558/10	10	50.8mm
CTBP0558/11	11	55.88mm
CTBP0558/12	12	60.96mm



KEY FEATURES

Low profile | Double interlock mechanism | Professional rising clamp



081

TERMINAL STRIPS

095

WIRE TO BOARD
CONNECTORS

100

CIRCULAR
CONNECTORS

151

IP68 CONNECTORS

158

INTERFACE
MODULES AND
RELAY BASES