




10mm pitch standard profile terminal blocks

Product overview


- 2 to 12 pole interlocking
- Wire protector terminals
- Standard profile
- Moulded in green UL94-V0 PA66
- Cable acceptance - 0.4-1.3mm² (26-16 AWG)
- Guided pin alignment
-   approved

CTBP2000



SPECIFICATION	
Rating	16A 250V
Insulation resistance	5000M Ω /1000V
Dielectric strength	AC1500V/1min
Contact resistance	20m Ω
Working temperature	-33°C to +120°C
Moulding	UL94-V0 flame retardant PA66
Pin/terminal	Stainless steel
Screw/torque	M3 steel, nickel plated 0.4Nm
Recommended PCB hole size	ϕ 1.1mm

PART NO.	POLES	LENGTH
CTBP2000/2	2	15mm
CTBP2000/3	3	25mm
CTBP2000/4	4	35mm
CTBP2000/5	5	45mm
CTBP2000/6	6	55mm
CTBP2000/7	7	65mm
CTBP2000/8	8	75mm
CTBP2000/9	9	85mm
CTBP2000/10	10	95mm
CTBP2000/11	11	105mm
CTBP2000/12	12	115mm



KEY FEATURES

Green UL94-V0 moulding | Interlock mechanism | Wire protector terminals

