

SAFETY DATA SHEET

In accordance with 453/2010 and 1272/2008

(All references to EU regulations and directives are abbreviated into only the numeric term)

Issued 2015-06-01

Replaces issued SDS 2015-02-26

SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1. Product identifier

Trade name

Ultragas

Supplier's product number

2202, 60g, 110ml - 2205, 210g, 300ml

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses

Propellants

1.3. Details of the supplier of the safety data sheet

Company

Sievert AB

Box 1366

SE-17126 SOLNA

Sweden

Telephone

+46 8-629 22 00

E-Mail

info@sievert.se

1.4. Emergency telephone number

In case of emergency contact toxicological information, emergency tel 112 (within Europe) or 1-800-222-1222 (for USA). For other countries, use the built-in emergency number in your cell phone

For non-emergency poison information, see http://www.who.int/gho/phe/chemical_safety/poisons_centres/en/

SECTION 2: HAZARDS IDENTIFICATION

2.1. Classification of the substance or mixture

Classification in accordance with 1272/2008

Extremely flammable gas (Category 1)

Liquefied pressurized gas

2.2. Label elements

Label information in accordance with 1272/2008



Hazard pictograms

Signal words

Danger

Hazard statements

H220

Extremely flammable gas

H280

Contains gas under pressure; may explode if heated

Precautionary statements

P210

Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking

P377

Leaking gas fire: Do not extinguish, unless leak can be stopped safely

P381

Eliminate all ignition sources if safe to do so

P410+P403

Protect from sunlight. Store in a well-ventilated place

2.3. Other hazards

Not relevant.

SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

This product is composed of a liquefied gas mixture.

3.2. Mixtures

Note that the table shows known hazards of the ingredients in a pure form. These hazards are reduced or eliminated when mixed or diluted, see Section 16d.

Constituent	Classification	Concentration
BUTANE < 0.1% BUTADIENE		
CAS No 106-97-8 EC No 203-448-7 Index No 601-004-00-0	Flam Gas 1, Press Gas <i>P</i> ; H220, H280	55 - 60%
PROPENE		
CAS No 115-07-1 EC No 204-062-1 Index No 601-011-00-9	Flam Gas 1, Press Gas <i>P</i> ; H220, H280	25 - 30%
PROPANE		
CAS No 74-98-6 EC No 200-827-9 Index No 601-003-00-5	Flam Gas 1, Press Gas <i>P</i> ; H220, H280	10 - 15%

Explanations to the classification and labelling of the ingredients are given in Section 16e. Official abbreviations are printed in normal font. Text in italics are specifications and/or complement used in the calculation of the hazards of this mixture, see Section 16b

SECTION 4: FIRST AID MEASURES

4.1. Description of first aid measures

Generally

Never attempt to administer liquid, or anything else, to an unconscious person via the mouth.

In case of concern, or if symptoms persist, call doctor/physician.

Case of respiratory arrest give artificial respiration.

Upon breathing in

Allow the injured person to rest in a warm place with fresh air, if symptoms persist seek medical advice.

Upon contact with the eyes

Rinse the eye for several minutes with lukewarm water. If irritation persists call a doctor/ophthalmologist.

Upon skin contact

Remove contaminated clothes.

Warm up affected parts of the body if frostbite is apparent.

In case of major frost injuries, please contact your doctor.

Upon ingestion

If symptoms persist contact a doctor.

4.2. Most important symptoms and effects, both acute and delayed

No further relevant information available.

4.3. Indication of any immediate medical attention and special treatment needed

Symptomatic treatment.

SECTION 5: FIRE-FIGHTING MEASURES

5.1. Extinguishing media Recommended

extinguishing agents Extinguish with powder or carbon dioxide. **Unsuitable**

extinguishing agents Should not be extinguished with water.

5.2. Special hazards arising from the substance or mixture

Gases detrimental to health (carbon monoxide and carbon dioxide) can be spread in case of fire.

Emits flammable vapours which may form an explosive mixture with air.

In case of fire, high pressure may build up causing the packaging to explode.

Flammable gas.

5.3. Advice for fire-fighters

Due to the risk of explosion, any extinguishing must be executed from a good distance.

In case of fire use a respirator mask.

If the gas cylinder cannot be removed, cool it with water as long as the fire persists and then at least 10 minutes.

SECTION 6: ACCIDENTAL RELEASE MEASURES

6.1. Personal precautions, protective equipment and emergency procedures

Use recommended safety equipment, see section 8.

Ensure good ventilation.

Do not inhale the gas.

Note, risk of ignition and explosion.

Switch off equipment which has an exposed flame, glows, or has a heat source of some other kind.

Switch off power at the main switch. Do not use the power switch in the room where the spillage has occurred.

Note, risk for formation of sparks due to static electricity. Do not remove clothing in a room where spillage has occurred.

Prevent from entering sewers, basements and pits, or any place where gas accumulation could be dangerous.

6.2. Environmental precautions

Avoid discharge into soil, water or air.

Avoid discharge into sewers.

6.3. Methods and material for containment and cleaning up

Evacuate the area and ventilate the gas.

For larger spills: Stop leak if possible. Keep public away. Contact emergency services.

Do not try to clean up yourself, unless you are properly trained for decontaminating this product.

Take the risk for violent reaction into account.

6.4. Reference to other sections

Not applicable

SECTION 7: HANDLING AND STORAGE

7.1. Precautions for safe handling

Check pipes and shut-off valves regularly for gas leakages.

Do not inhale the product and avoid exposure to skin, eyes and clothing.

Note also information about exposure control/personal protection and disposal considerations (Safety data sheet Sections 8 and 13).

The product should be stored in a manner which prevents hazards to health and the environment. Avoid exposure to humans and animals and do not discharge the product in a sensitive environment.

Store this product separately from food items and keep it out of the reach of children and pets.

Do not eat, drink or smoke in premises where this product is stored.

Work in order to avoid spillage. If spillage does occur, address it immediately in accordance with the directions specified in Section 6 of this safety data sheet.

Open fire, hot items, sparks or other ignition sources must not be present in the environment used for handling this product.

The product may be electrostatically charged. Always ground the containers while transferring the contents from one container to another. Do not use tools that may cause sparks.

Wash your hands after using the product.

7.2. Conditions for safe storage, including any incompatibilities

Do not store above normal room temperature or in direct sun light.

Handle in a premises which is well ventilated.

Store in a well-ventilated space.

An evacuation plan should be available and evacuation routes must not be blocked.

Emergency showers and eye-rinsing facilities must be available at the workplace.

Store only in the original package.

7.3. Specific end uses

Not relevant.

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1. Control parameters

8.1.1. National limit values, United Kingdom

BUTANE < 0.1% BUTADIENE

**Time-weighted-average exposure limit (TWA) 600 ppm / 1450 mg/m³ Short term exposure limit (STEL)
750 ppm / 1810 mg/m³**

Other ingredients (cf. Section 3) have no occupational exposure limit values.

8.2. Exposure controls

In terms of minimizing risks, attention must be paid to the physical hazards (see Sections 2 and 10) of this product according to EU directives 89/391 and 98/24 and national occupational legislation.

Protective gloves are normally not needed due to the properties of this product, but may be necessary for other reasons, e.g. mechanical risks, temperature conditions or microbiological risks.

A respiratory mask may be required.

For limitation of environmental exposure, see Section 12.

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

9.1. Information on basic physical and chemical properties

a) Appearance	Form: Liquefied gas Colour: colourless
b) Odour	Characteristic
c) Odour threshold	Not applicable
d) pH	Not applicable
e) Melting point/freezing point	-180 °C
f) Initial boiling point and boiling range	-44 °C at atmospheric pressure (101325 Pa)
g) Flash point	-107 °C
h) Evaporation rate	Not applicable
i) Flammability (solid, gas)	Extremely flammable gas
j) Upper/lower flammability or explosive limits	Lower explosion limit 1.5% Upper explosion limit 10.9%
k) Vapour pressure	450 kPa (15 °C)
l) Vapour density	Not applicable
m) Relative density	0,55 kg/L
n) Solubility	Solubility in water: Partially soluble
o) Partition coefficient: n-octanol/water	Not applicable
p) Auto-ignition temperature	365 °C
q) Decomposition temperature	Not applicable
r) Viscosity	Not applicable
s) Explosive properties	Not applicable
t) Oxidising properties	Not applicable

9.2. Other information

No data available

SECTION 10: STABILITY AND REACTIVITY

10.1. Reactivity

The product contains no substances which can lead to hazardous reactions at normal use.

10.2. Chemical stability

The product is stable at normal storage and handling conditions.

10.3. Possibility of hazardous reactions

May emit volatile, flammable vapours. Avoid handling close to heat or ignition sources.

The gas forms an explosive mixture with air.

10.4. Conditions to avoid

Avoid heat, sparks and open flames.

10.5. Incompatible materials

Avoid contact with oxidizers.

10.6. Hazardous decomposition products

Carbon monoxide (CO), carbon dioxide (CO₂) and harmful and irritating substances.

SECTION 11: TOXICOLOGICAL INFORMATION

11.1. Information on toxicological effects

General or unspecific toxicity

This product's main risk is its flammability.

Acute effects

Not classified as an acutely toxic substance.

Harmfulness

The product is not classified as harmful to health.

Effect on judgement and other psychological effects

At high concentrations there is an anaesthetic or narcotic effect.

Effect on human microflora

Effects on human micro flora have not been proven, or are negligible.

Relevant toxicological properties

BUTANE < 0.1% BUTADIENE

LC50 rat (Inhalation) 4h = 658 mg/L inhalation

PROPANE

LC50 rat (Inhalation) 4h = 658 mg/L inhalation

SECTION 12: ECOLOGICAL INFORMATION

12.1. Toxicity

PROPANE

LC50 Freshwater water flea (Daphnia magna) 48h = 16,3 mg/L

LC50 Fish 96h = 16,1 mg/L

IC50 Algae 72h = 11,3 mg/L

Avoid all discharge into the air.

12.2. Persistence and degradability

There is no information regarding persistence or degradability.

12.3. Bioaccumulative potential

There is no information regarding bioaccumulation.

12.4. Mobility in soil

Information about mobility in nature is not available.

12.5. Results of PBT and vPvB assessment

No chemical safety report has been executed.

12.6. Other adverse effects

Not indicated

SECTION 13: DISPOSAL CONSIDERATIONS

13.1. Waste treatment methods

Waste handling for the product

Also take local regulations for dealing with waste into account.

Pressurized can; The container must not be heated or disposed as conventional waste.

Product as well as packaging must be disposed as hazardous waste.

Cf. also national waste regulations.

Special advises for waste handling

16 05 04.

Recycling of the product

This product is not usually recycled.

Transportation of waste

Not indicated

SECTION 14: TRANSPORT INFORMATION

This product is only supposed to be transported by road or railway and just the transport regulations ADR/RID thus apply.

14.1. UN number

2037

14.2. UN proper shipping name

RECEPTACLES, SMALL, CONTAINING GAS (GAS CARTRIDGES)

14.3. Transport hazard class(es)

Class

2: Gases

Classification code (ADR/RID)

5F:

Subsidiary risk (IMDG)

Labels



14.4. Packing group

Packing group: Not applicable

14.5. Environmental hazards

Not applicable

14.6. Special precautions for user

Tunnel restrictions

Tunnel category: D.

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Not applicable

14.8 Other transport information

Transport category: 2; Highest total quantity per transported unit 333 kg or liters.

SECTION 15: REGULATORY INFORMATION

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Not applicable.

15.2. Chemical safety assessment

Chemical safety report according to 1907/2006 Annex I is not required for this product.

SECTION 16: OTHER INFORMATION

16a. Indication of where changes have been made to the previous version of the safety data sheet

Revisions of this document

Earlier versions

2015-02-26 Revisions of this document has, where not otherwise stated, been caused by changes in the regulations

16b. Legend to abbreviations and acronyms used in the safety data sheet

Full texts for Hazard Class and Category Code mentioned in section 3

Flam Gas 1 Extremely flammable gas (Category 1)

Press Gas *P* Compressed gas

No tox haz Not classified as toxic

Comprehensive definition of the hazards mentioned in Section 2

Flam Gas 1

Gases, which at 20 °C and a standard pressure of 101,3 kPa:

(a) are ignitable when in a mixture of 13 % or less by volume in air; or

(b) have a flammable range with air of at least 12 percentage points regardless of the lower flammable limit.

Liq Press gas

Pressurized liquefied gas: A gas which when packaged under pressure, is partially liquid at temperatures above -50 °C without specification of critical temperature

Explanations of the abbreviations in Section 14

ADR European Agreement concerning the International Transport of Dangerous Goods by Road

RID Regulations concerning the International Transport of Dangerous Goods by Rail

Tunnel restriction code: D; Passage forbidden through tunnels of category D and E type.

Transport category: 2; Highest total quantity per transported unit 333 kg or liters.

16c. Key literature references and sources for data

Sources for data

Primary data for the calculation of the hazards has preferentially been taken from the official European classification list, 1272/2008 Annex I, as updated to 2015-06-01.

Where such data was lacking, on the second hand the documentation on which this official classification is based was used, e.g. IUCLID (International Uniform Chemical Information Database). On the third hand, information was used from reputable international chemical suppliers, and on the fourth hand from other available information, e.g. safety data sheets from other suppliers or information from non-profit associations, whereby the reliability of the source was judged by an expert. If, in spite of this, reliable information was not found, the hazards were judged by expert opinions based on the known properties of similar substances, and according to the principles in 1907/2006 and 1272/2008.

Full texts for Regulations mentioned in this Safety Data Sheet

- 453/2010 COMMISSION REGULATION (EU) No 453/2010 of 20 May 2010 amending Regulation (EC) No 1907/2006 of the European Parliament and of the Council on the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH)
- 1272/2008 REGULATION (EC) No 1272/2008 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006
- 89/391 COUNCIL DIRECTIVE (89/391/EEC of 12 June 1989 on the introduction of measures to encourage improvements in the safety and health of workers at work
- 98/24 COUNCIL DIRECTIVE 98/24/EC of 7 April 1998 on the protection of the health and safety of workers from the risks related to chemical agents at work (fourteenth individual Directive within the meaning of Article 16(1) of Directive 89/391/EEC)
- 1907/2006 REGULATION (EC) No 1907/2006 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC Annex I

16d. Methods of evaluating information referred to in 1272/2008 Article 9 which was used for the purpose of classification

The calculation of the hazards of this mixture has been performed as an evaluation by applying a weight of evidence determination using expert judgement in accordance with 1272/2008 Annex I, weighing all available information having a bearing on the determination of the hazards of the mixture, and in accordance with 1907/2006 Annex XI.

16e. List of relevant hazard statements and/or precautionary statements

Full texts for hazard statements mentioned in section 3

H220 Extremely flammable gas

H280 Contains gas under pressure; may explode if heated

16f. Advice on any training appropriate for workers to ensure protection of human health and the environment

Warning for misuse

This product can cause severe injuries if used improperly. Read and follow carefully the instructions in this safety sheet and other appropriate risk information. At professional use the employer is responsible for the staff being well aware of the risks.

Other relevant information

Editorial information

This safety data sheet has been generated by the program KemRisk®, KemRisk Sweden AB, Teknikringen 10, SE-583 30 Linköping, Sweden.