




10mm pitch standard profile 90° wire protector terminal blocks


Product overview

- 1 and 2 pole interlocking mechanism
- 3-6 pole solid block end stackable
- 90° mounting
- Moulded in green UL94-V0 flame retardant PA
- Cable acceptance - 0.33-2mm² (22-14 AWG)
- Wire protector terminals
- Guided pin alignment
- Captive screws
- Anti solder wicking terminals
- approved

CTBP2050




CTBP2050/1/15



SPECIFICATION	
Rating	16A / 250V
Withstand voltage	AC 1500V / 1Min
Working temperature	-40°C to +105°C
Moulding	UL94-V0 flame retardant PA
Pin/terminal	Tinned, nickel plated brass
Wire protector	Tin plated, phosphor bronze
Screw/torque	M3 steel, zinc plated / 0.5Nm
Recommended PCB hole size	Ø1.2mm

PART NO.	POLES	LENGTH
CTBP2050/1	1	10mm
CTBP2050/1/15	1	15mm
CTBP2050/2	2	15mm
CTBP2050/3	3	25mm
CTBP2050/4	4	35mm
CTBP2050/5	5	45mm
CTBP2050/6	6	55mm
CTBP2050/7	7	65mm
CTBP2050/8	8	75mm
CTBP2050/9	9	85mm
CTBP2050/10	10	95mm
CTBP2050/11	11	105mm
CTBP2050/12	12	115mm



KEY FEATURES

Standard profile | Interlocking mechanism | Wire protector terminals

