



SAFETY DATA SHEET

Zinsser Gardz®

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Product name : Zinsser Gardz®
Product description : Paint.
Product type : Liquid.

1.2 Relevant identified uses of the substance or mixture and uses advised against

Not applicable.

1.3 Details of the supplier of the safety data sheet

Manufactured under license in the UK by
Tor Coatings Limited
Portobello Industrial Estate
Birtley
County Durham
United Kingdom
DH3 2RE
Telephone no.: +44 (0) 191 4106611
Fax no.: +44 (0) 191 4920125
enquiries@tor-coatings.com

e-mail address of person responsible for this SDS : rpmeurohas@ro-m.com

1.4 Emergency telephone number

Telephone number : +44 (0) 207 858 1228
Hours of operation : 24 / 7

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Product definition : Mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP/GHS]

Not classified.

See Section 16 for the full text of the R phrases or H statements declared above.

See Section 11 for more detailed information on health effects and symptoms.

2.2 Label elements

Signal word : No signal word.

Hazard statements : No known significant effects or critical hazards.

Precautionary statements

General : Keep out of reach of children. Read label before use. If medical advice is needed, have product container or label at hand.

Prevention : Not applicable.

Response : Not applicable.

Storage : Not applicable.

SECTION 2: Hazards identification

- Disposal** : Dispose of contents and container in accordance with all local, regional, national and international regulations.
- Supplemental label elements** : Not applicable.
- Annex XVII - Restrictions on the manufacture, placing on the market and use of certain dangerous substances, mixtures and articles** : Not applicable.
- Special packaging requirements**
- Containers to be fitted with child-resistant fastenings** : Not applicable.
- Tactile warning of danger** : Not applicable.

2.3 Other hazards

- Substance meets the criteria for PBT according to Regulation (EC) No. 1907/2006, Annex XIII** : Not applicable.
- Substance meets the criteria for vPvB according to Regulation (EC) No. 1907/2006, Annex XIII** : Not applicable.
- Other hazards which do not result in classification** : Not available.

SECTION 3: Composition/information on ingredients

Substance/mixture : Mixture

There are no ingredients present which, within the current knowledge of the supplier and in the concentrations applicable, are classified as hazardous to health or the environment, are PBTs or vPvBs or have been assigned a workplace exposure limit and hence require reporting in this section.

SECTION 4: First aid measures

4.1 Description of first aid measures

- General** : In all cases of doubt, or when symptoms persist, seek medical attention. Never give anything by mouth to an unconscious person. If unconscious, place in recovery position and seek medical advice.
- Eye contact** : Check for and remove any contact lenses. Immediately flush eyes with running water for at least 15 minutes, keeping eyelids open. Seek immediate medical attention.
- Inhalation** : Remove to fresh air. Keep person warm and at rest. If not breathing, if breathing is irregular or if respiratory arrest occurs, provide artificial respiration or oxygen by trained personnel.
- Skin contact** : Remove contaminated clothing and shoes. Wash skin thoroughly with soap and water or use recognised skin cleanser. Do NOT use solvents or thinners.
- Ingestion** : If swallowed, seek medical advice immediately and show the container or label. Keep person warm and at rest. Do NOT induce vomiting.
- Protection of first-aiders** : No action shall be taken involving any personal risk or without suitable training.

4.2 Most important symptoms and effects, both acute and delayed

SECTION 4: First aid measures

There are no data available on the mixture itself. The mixture has been assessed following the conventional method of the Dangerous Preparations Directive 1999/45/EC and classified for toxicological hazards accordingly. See Sections 3 and 15 for details.

Repeated or prolonged contact with the mixture may cause removal of natural fat from the skin, resulting in non-allergic contact dermatitis and absorption through the skin.

If splashed in the eyes, the liquid may cause irritation and reversible damage.

This takes into account, where known, delayed and immediate effects and also chronic effects of components from short-term and long-term exposure by oral, inhalation and dermal routes of exposure and eye contact.

4.3 Indication of any immediate medical attention and special treatment needed

Notes to physician : Treat symptomatically. Contact poison treatment specialist immediately if large quantities have been ingested or inhaled.

Specific treatments : No specific treatment.

See toxicological information (Section 11)

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media : Recommended: alcohol-resistant foam, CO₂, powders, water spray.

Unsuitable extinguishing media : Do not use water jet.

5.2 Special hazards arising from the substance or mixture

Hazards from the substance or mixture : Fire will produce dense black smoke. Exposure to decomposition products may cause a health hazard.

Hazardous thermal decomposition products : Decomposition products may include the following materials: carbon monoxide, carbon dioxide, smoke, oxides of nitrogen.

5.3 Advice for firefighters

Special protective actions for fire-fighters : Cool closed containers exposed to fire with water. Do not release runoff from fire to drains or watercourses.

Special protective equipment for fire-fighters : Appropriate breathing apparatus may be required.

Additional information : No unusual hazard if involved in a fire.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

For non-emergency personnel : Exclude sources of ignition and ventilate the area. Avoid breathing vapour or mist. Refer to protective measures listed in sections 7 and 8.

For emergency responders : If specialised clothing is required to deal with the spillage, take note of any information in Section 8 on suitable and unsuitable materials. See also the information in "For non-emergency personnel".

6.2 Environmental precautions : Do not allow to enter drains or watercourses. If the product contaminates lakes, rivers, or sewers, inform the appropriate authorities in accordance with local regulations.

6.3 Methods and materials for containment and cleaning up : Contain and collect spillage with non-combustible, absorbent material e.g. sand, earth, vermiculite or diatomaceous earth and place in container for disposal according to local regulations (see Section 13). Preferably clean with a detergent. Avoid using solvents.

SECTION 6: Accidental release measures

- 6.4 Reference to other sections** : See Section 1 for emergency contact information.
See Section 8 for information on appropriate personal protective equipment.
See Section 13 for additional waste treatment information.

SECTION 7: Handling and storage

- 7.1 Precautions for safe handling** : Keep away from heat, sparks and flame. No sparking tools should be used. Avoid contact with skin and eyes. Avoid the inhalation of dust, particulates, spray or mist arising from the application of this mixture. Avoid inhalation of dust from sanding.
Eating, drinking and smoking should be prohibited in areas where this material is handled, stored and processed.
Put on appropriate personal protective equipment (see Section 8).
Never use pressure to empty. Container is not a pressure vessel.
Always keep in containers made from the same material as the original one.
Comply with the health and safety at work laws. Do not allow to enter drains or watercourses.

When operators, whether spraying or not, have to work inside the spray booth, ventilation is unlikely to be sufficient to control particulates and solvent vapour in all cases. In such circumstances they should wear a compressed air-fed respirator during the spraying process and until such time as the particulates and solvent vapour concentration has fallen below the exposure limits.

- 7.2 Conditions for safe storage, including any incompatibilities** : Store in accordance with local regulations.
Notes on joint storage
Keep away from: oxidising agents, strong alkalis, strong acids.
Additional information on storage conditions
Observe label precautions. Do not store below the following temperature: 0°C (32°F). Store in a dry, cool and well-ventilated area. Keep container tightly closed.
No smoking. Prevent unauthorised access. Containers that have been opened must be carefully resealed and kept upright to prevent leakage.

7.3 Specific end use(s)

- Recommendations** : Not available.
Industrial sector specific solutions : Not available.

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Occupational exposure limits

No exposure limit value known.

- Recommended monitoring procedures** : If this product contains ingredients with exposure limits, personal, workplace atmosphere or biological monitoring may be required to determine the effectiveness of the ventilation or other control measures and/or the necessity to use respiratory protective equipment. Reference should be made to European Standard EN 689 for methods for the assessment of exposure by inhalation to chemical agents and national guidance documents for methods for the determination of hazardous substances.

DNELs/DMELs

No DNELs/DMELs available.

PNECs

No PNECs available

SECTION 8: Exposure controls/personal protection

8.2 Exposure controls

Appropriate engineering controls : Provide adequate ventilation. Where reasonably practicable, this should be achieved by the use of local exhaust ventilation and good general extraction.

Individual protection measures

Hygiene measures : Wash hands, forearms and face thoroughly after handling chemical products, before eating, smoking and using the lavatory and at the end of the working period. Appropriate techniques should be used to remove potentially contaminated clothing. Wash contaminated clothing before reusing. Ensure that eyewash stations and safety showers are close to the workstation location.

Eye/face protection : Safety glasses with side shields. (EN166)

Skin protection

Hand protection

There is no one glove material or combination of materials that will give unlimited resistance to any individual or combination of chemicals.

The breakthrough time must be greater than the end use time of the product.

The instructions and information provided by the glove manufacturer on use, storage, maintenance and replacement must be followed.

Gloves should be replaced regularly and if there is any sign of damage to the glove material.

Always ensure that gloves are free from defects and that they are stored and used correctly.

The performance or effectiveness of the glove may be reduced by physical/chemical damage and poor maintenance.

Barrier creams may help to protect the exposed areas of the skin but should not be applied once exposure has occurred.

Gloves : For prolonged or repeated handling, use the following type of gloves:

Recommended: > 8 hours (breakthrough time): nitrile rubber

The recommendation for the type or types of glove to use when handling this product is based on information from the following source:

EN 374-3 : 2003

The user must check that the final choice of type of glove selected for handling this product is the most appropriate and takes into account the particular conditions of use, as included in the user's risk assessment.

Body protection : Wear overalls or long sleeved shirt. (EN 467)

Other skin protection : Appropriate footwear and any additional skin protection measures should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.

Respiratory protection : Not applicable.

Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

Recommended: organic vapour (Type A) and particulate filter (EN 140) .

Environmental exposure controls : Do not allow to enter drains or watercourses.

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Appearance

Physical state : Liquid.

Colour : Colourless.

Odour : Faint odour

pH : 8 to 9 [Alcaline.]

Melting point/freezing point : 0°C

Initial boiling point and boiling range : >100°C

SECTION 9: Physical and chemical properties

Flash point	: Closed cup: >100°C [Product does not sustain combustion.]
Evaporation rate	: <1 (butyl acetate = 1)
Flammability (solid, gas)	: Non-flammable in the presence of the following materials or conditions: open flames, sparks and static discharge, heat and shocks and mechanical impacts. Nonflammable, but will burn on prolonged exposure to flame or high temperature.
Burning time	: Not applicable.
Burning rate	: Not applicable.
Upper/lower flammability or explosive limits	: Not applicable.
Vapour pressure	: Not available.
Vapour density	: >1 [Air = 1]
Relative density	: 1.01
Solubility(ies)	: Not available.
Solubility in water	:
Partition coefficient: n-octanol/ water	: Not available.
Auto-ignition temperature	: Not available.
Decomposition temperature	: Not available.
Viscosity	: Dynamic: 100 to 500 mPa·s
Explosive properties	: Not applicable.
Oxidising properties	: Not available.

9.2 Other information

No additional information.

SECTION 10: Stability and reactivity

10.1 Reactivity	: No specific test data related to reactivity available for this product or its ingredients.
10.2 Chemical stability	: Stable under recommended storage and handling conditions (see Section 7).
10.3 Possibility of hazardous reactions	: Under normal conditions of storage and use, hazardous reactions will not occur.
10.4 Conditions to avoid	: When exposed to high temperatures may produce hazardous decomposition products.
10.5 Incompatible materials	: Keep away from the following materials to prevent strong exothermic reactions: oxidising agents, strong alkalis, strong acids.
10.6 Hazardous decomposition products	: Under normal conditions of storage and use, hazardous decomposition products should not be produced. If involved in a fire, toxic gases including CO, CO ₂ and smoke can be generated.

SECTION 11: Toxicological information

11.1 Information on toxicological effects

SECTION 11: Toxicological information

There are no data available on the mixture itself. The mixture has been assessed following the conventional method of the Dangerous Preparations Directive 1999/45/EC and classified for toxicological hazards accordingly. See Sections 3 and 15 for details.

Repeated or prolonged contact with the mixture may cause removal of natural fat from the skin, resulting in non-allergic contact dermatitis and absorption through the skin.

If splashed in the eyes, the liquid may cause irritation and reversible damage.

This takes into account, where known, delayed and immediate effects and also chronic effects of components from short-term and long-term exposure by oral, inhalation and dermal routes of exposure and eye contact.

Acute toxicity

Conclusion/Summary : Not available.

Irritation/Corrosion

Conclusion/Summary : Not available.

Sensitisation

Conclusion/Summary : Not available.

Mutagenicity

Conclusion/Summary : Not available.

Carcinogenicity

Conclusion/Summary : Not available.

Reproductive toxicity

Conclusion/Summary : Not available.

Teratogenicity

Conclusion/Summary : Not available.

Specific target organ toxicity (single exposure)

Not available.

Specific target organ toxicity (repeated exposure)

Not available.

Aspiration hazard

Not available.

Other information : Not available.

SECTION 12: Ecological information

12.1 Toxicity

There are no data available on the mixture itself.

Do not allow to enter drains or watercourses.

Conclusion/Summary : Not available.

12.2 Persistence and degradability

Conclusion/Summary : According to EC criteria: Expected to be inherently biodegradable

12.3 Bioaccumulative potential

Not available.

12.4 Mobility in soil

Soil/water partition coefficient (K_{oc}) : Not available.

Mobility : This product is not likely to volatilise rapidly into the air because of its low vapour pressure.

SECTION 12: Ecological information

12.5 Results of PBT and vPvB assessment

- PBT** : Not applicable.
P: Not available. B: Not available. T: Not available.
- vPvB** : Not applicable.
vP: Not available. vB: Not available.

12.6 Other adverse effects : No known significant effects or critical hazards.

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Product

Methods of disposal : The generation of waste should be avoided or minimised wherever possible. Significant quantities of waste product residues should not be disposed of via the foul sewer but processed in a suitable effluent treatment plant. Dispose of surplus and non-recyclable products via a licensed waste disposal contractor. Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements.

Hazardous waste : Within the present knowledge of the supplier, this product is not regarded as hazardous waste, as defined by EU Directive 91/689/EEC.

Disposal considerations : Do not allow to enter drains or watercourses.
Dispose of according to all federal, state and local applicable regulations.

European waste catalogue (EWC)

The European Waste Catalogue classification of this product, when disposed of as waste, is:

Waste code	Waste designation
08 01 12	waste paint and varnish other than those mentioned in 08 01 11

Packaging

Methods of disposal : The generation of waste should be avoided or minimised wherever possible. Waste packaging should be recycled. Incineration or landfill should only be considered when recycling is not feasible.

Disposal considerations : Using information provided in this safety data sheet, advice should be obtained from the relevant waste authority on the classification of empty containers.
Empty containers must be scrapped or reconditioned.
Not emptied containers are hazardous waste.

Special precautions : This material and its container must be disposed of in a safe way. Empty containers or liners may retain some product residues. Avoid dispersal of spilt material and runoff and contact with soil, waterways, drains and sewers.

SECTION 14: Transport information

	ADR/RID	IMDG	IATA
14.1 UN number	Not regulated.	Not regulated.	Not regulated.
14.2 UN proper shipping name	-	-	-
14.3 Transport hazard class(es)	-	-	-

Zinsser Gardz®

SECTION 14: Transport information

14.4 Packing group	-	-	-
14.5 Environmental hazards	No.	No.	No.
Additional information	-	-	-

14.6 Special precautions for user : **Transport within user's premises:** always transport in closed containers that are upright and secure. Ensure that persons transporting the product know what to do in the event of an accident or spillage.

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

The information contained in this safety data sheet does not constitute the user's own assessment of workplace risks, as required by other health and safety legislation. The provisions of the national health and safety at work regulations apply to the use of this product at work.

CN code : 3209 10 00

EU Regulation (EC) No. 1907/2006 (REACH)

Annex XIV - List of substances subject to authorisation

Annex XIV

None of the components are listed.

Substances of very high concern

None of the components are listed.

Annex XVII - Restrictions : Not applicable.

on the manufacture, placing on the market and use of certain dangerous substances, mixtures and articles

Other EU regulations

VOC for Ready-for-Use Mixture : IIA/g. Primers. EU limit value for this product : 50g/l (2007) 30g/l (2010.)
This product contains a maximum of 30 g/l VOC.

Europe inventory : All components are listed or exempted.

National regulations

15.2 Chemical Safety Assessment : This product contains substances for which Chemical Safety Assessments are still required.

SECTION 16: Other information

✔ Indicates information that has changed from previously issued version.

Abbreviations and acronyms :

- ATE = Acute Toxicity Estimate
- CLP = Classification, Labelling and Packaging Regulation [Regulation (EC) No. 1272/2008]
- DMEL = Derived Minimal Effect Level
- DNEL = Derived No Effect Level
- EUH statement = CLP-specific Hazard statement
- PBT = Persistent, Bioaccumulative and Toxic
- PNEC = Predicted No Effect Concentration
- RRN = REACH Registration Number
- vPvB = Very Persistent and Very Bioaccumulative

Zinsser Gardz®

SECTION 16: Other information

Procedure used to derive the classification according to Regulation (EC) No. 1272/2008 [CLP/GHS]

Classification	Justification
Not classified.	

Full text of abbreviated H statements : Not applicable.

Full text of classifications [CLP/GHS] : Not applicable.

Full text of abbreviated R phrases : Not applicable.

Full text of classifications [DSD/DPD] : Not applicable.

Date of printing : 19-11-2014.

Date of issue/ Date of revision : 10-09-2013.

Date of previous issue : 10-09-2013.

Version : 1

Notice to reader

The information in this SDS is based on the present state of our knowledge and on current laws. The product is not to be used for purposes other than those specified under section 1 without first obtaining written handling instructions. It is always the responsibility of the user to take all necessary steps to fulfil the demands set out in the local rules and legislation. The information in this SDS is meant to be a description of the safety requirements for our product. It is not to be considered a guarantee of the product's properties.