


Specifications

Pitch:	2.54mm
Type:	Rising Clamp
Poles:	2 to 12
Rated Voltage:	See Table
Rated Current:	See Table
Operational Temperature:	-40°C to +105°C
Withstand Voltage:	1250V AC for 60s
Insulation Resistance:	500MΩ at 500V DC
Wire Range:	See Table
Wire Stripping Length:	4.5mm ± 0.5mm
Screw Size:	M1.6
Max. Torque Value:	0.1Nm
Wave Soldering:	260°C for 5s
Hand Soldering:	350°C for 10s






Colour and Materials

Housing Colour:	Green
Housing Material:	PA66
Flame Retardancy:	UL94-V0
Screw:	Zinc-plated steel (A3)
Wire Cage:	Nickel-plated brass
Pin Header:	Tin-plated brass

Order Code	Poles	Order Code	Poles
21-3900	2	21-3905	8
21-3901	3	21-3909	9
21-3902	4	21-3906	10
21-3903	5	21-3912	11
21-3904	6	21-3907	12
21-3908	7		

Standard	Rated Voltage	Rated Current	Wire Range
UL	150V	6A	26-18AWG
IEC	130V	8A	1mm ²



Measurements are in mm unless stated otherwise.

For further information on pricing, delivery, and long-term stock agreements please get in touch with your local business development contact. Telephone our main office on **01206 838000** or email Sales@Rapidonline.com.

The information contained in this datasheet is subject to change without notice and replaces all data sheets previously supplied.

