


Type: **DILA–XHIV11**

Article No.: **276423**

Sales text **Contactor relays,aux.cont.mod.,2–pole**




With interlocked opposing contacts (exception: ...XHI(C)V...)

Ordering information

Connection technique			Screw terminals
Description			2 pole
Contacts			
N/O = Normally open			1 N/O _E
N/C = Normally closed			1 N/C _L
Rated operational current			
AC–15 220 V 230 V 240 V	I_e	A	4
AC–15 380 V 400 V 415 V	I_e	A	4
Conventional thermal current	I_{th}	A	16
Code number and version of combination			
DILA(C)–40			51
DILA(C)–31			42
DILA(C)–22			33

Contact sequence



Notes concerning the product group

Version E combinations correspond to EN 50011 and are to be preferred; other combinations correspond to EN 50005

The DC operated contactor DILA(C)–22 must only be combined with 2 pole auxiliary contacts.


NO_E: early–make NO contact

NC_L: late break NC contact

Auxiliary contacts			
Interlocked opposing contacts within an auxiliary contact module (to IEC 60947–5–1 Annex L)			Yes
N/C contact (not late–break contact) suitable as a mirror contact (to IEC/EN 60947–4–1 Annex F)			DILM7 – DILM32
Rated impulse withstand voltage	U_{imp}	V AC	6000
Overtoltage category/pollution degree			III/3
Rated insulation voltage	U_i	V AC	690
Rated operational voltage	U_e	V AC	500
Safe isolation to VDE 0106 Part 101 and Part 101/A1			
between coil and auxiliary contacts		V AC	400
between the auxiliary contacts		V AC	400
Rated operational current			
AC–15			
230 V	I_e	A	4
380/415 V	I_e	A	4
DC–13 L/R – 15 ms			
24 V	I_e	A	10
60 V	I_e	A	6
110 V	I_e	A	3
220 V	I_e	A	1
Conv. thermal current	I_{th}	A	16
Control circuit reliability (at $U_e = 24$ V DC, $U_{min} = 17$ V, $I_{min} = 5.4$ mA)	Failure rate		–8, < 1 one failure at 100 million operations
Component lifespan			
at $U_e = 230$ V, AC–15, 3 A	Operations	$\times 10^6$	1.3
Short–circuit rating without welding			
max. fuse		A gG/gL	10
Notes			
Notes			See transparent overlay "Fuses" for time/current characteristics (please inquire) not with DIL...–XHIV and

DIL...-XHICV
Making and breaking
conditions to DC-13, time
L/R constant as stated

Dimensions



Moeller GmbH, Hein-Moeller-Str. 7-11, D-53115 Bonn
E-Mail: catalog@moeller.net, Internet: www.moeller.net, <http://catalog.moeller.net>
HPL-C2007G V2.1 © 2007 by Moeller GmbH