

Printview: Female connector; with integrated push-buttons; 10-pole; Pin spacing 7.5 mm / 0.295 in; codable; with 2 latches - Item No.: 2231-210/026-000



Female connector; with integrated push-buttons; 10-pole; Pin spacing 7.5 mm / 0.295 in; codable; with 2 latches

Item No.: 2231-210/026-000



Marking

RoHS ✓
Compliant

Business data

Supplier	WAGO
Item no.	2231-210/026-000
GTIN / EAN	4045454722760
Content	1

Notes

Item description: Universal connection for all conductor types Easy-to-use design does not require special tools Ability to wire while mated Simple, push-in termination of solid and ferruled stranded conductors Integrated test ports for testing parallel to conductor entry Coding option available Safety information 1: The MULTI CONNECTION SYSTEM (MCS) is designed without breaking capacity for compliance with DIN EN 61984. When used as intended, MCS Connectors shall not be connected/disconnected when live or under load. The circuit design should ensure header pins, which can be touched, are not live when unmated.

Technical data

Miscellaneous

Printview: Female connector; with integrated push-buttons; 10-pole; Pin spacing 7.5 mm / 0.295 in; codable; with 2 latches - Item No.: 2231-210/026-000



Technical data	
<i>Other versions (or variants) can be requested</i>	<i>Gold-plated or partially gold-plated contact surfaces</i>
<i>Ratings per</i>	<i>IEC/EN 60664-1</i>
<i>Rated voltage (III / 3) [V]</i>	<i>500 [V]</i>
<i>Rated impulse voltage (III / 3) [kV]</i>	<i>6 [kV]</i>
<i>Rated voltage (III/2) [V]</i>	<i>630 [V]</i>
<i>Rated impulse voltage (III / 2) [kV]</i>	<i>6 [kV]</i>
<i>Rated voltage (II / 2) [V]</i>	<i>1000 [V]</i>
<i>Rated impulse voltage (II / 2) [kV]</i>	<i>6 [kV]</i>
<i>Rated current [A]</i>	<i>16 [A]</i>
<i>Legend (ratings)</i>	<i>(III / 2) Overvoltage category III / Pollution degree 2</i>
<i>Approvals per</i>	<i>UL 1059</i>
<i>Rated voltage UL (Use Group B) [V]</i>	<i>300 [V]</i>
<i>Rated current UL (Use Group B) [A]</i>	<i>15 [A]</i>
<i>Rated voltage UL (Use Group C) [V]</i>	<i>300 [V]</i>
<i>Rated current UL (Use Group C) [A]</i>	<i>15 [A]</i>
<i>Rated voltage UL (Use Group D) [V]</i>	<i>300 [V]</i>
<i>Rated current UL (Use Group D) [A]</i>	<i>10 [A]</i>
<i>Rated voltage CSA (Use Group B) [V]</i>	<i>300 [V]</i>
<i>Rated current CSA (Use Group B) [A]</i>	<i>15 [A]</i>
<i>Rated voltage CSA (Use Group C) [V]</i>	<i>300 [V]</i>
<i>Rated current CSA (Use Group C) [A]</i>	<i>15 [A]</i>
<i>Rated voltage CSA (Use Group D) [V]</i>	<i>300 [V]</i>
<i>Rated current CSA (Use Group D) [A]</i>	<i>10 [A]</i>
<i>No. of poles</i>	<i>10</i>
<i>Total number of connection points</i>	<i>10</i>
<i>Total number of potentials</i>	<i>10</i>
<i>Number of connection types</i>	<i>1</i>
<i>Number of levels</i>	<i>1</i>
<i>Connection technology</i>	<i>Push-in CAGE CLAMP®</i>
<i>Actuation type</i>	<i>Operating lever</i>
<i>Solid conductor</i>	<i>0.2 ... 2.5 mm² / 24 ... 12 AWG</i>
<i>Fine-stranded conductor</i>	<i>0.2 ... 2.5 mm² / 24 ... 12 AWG</i>


Printview: Female connector; with integrated push-buttons; 10-pole; Pin spacing 7.5 mm / 0.295 in; codable; with 2 latches - Item No.: 2231-210/026-000

Technical data	
<i>Fine-stranded conductor with ferrule with plastic collar</i>	<i>0.25 ... 1.5 mm²</i>
<i>Fine-stranded conductor with ferrule without plastic collar</i>	<i>0.25 ... 2.5 mm²</i>
<i>Strip length</i>	<i>10 ... 11 mm / 0.39 ... 0.43 Inch</i>
<i>Pin spacing</i>	<i>7.5 mm (0.295 in)</i>
<i>Width</i>	<i>74 mm / 2.913 Inch</i>
<i>Height</i>	<i>15 mm / 0.591 Inch</i>
<i>Depth</i>	<i>25.6 mm / 1.008 Inch</i>
<i>Contact type (pluggable connector)</i>	<i>Female connector/socket</i>
<i>Connector connection type</i>	<i>for conductors</i>
<i>Mismating protection</i>	<i>nein</i>
<i>Color</i>	<i>gray</i>
<i>Material group</i>	<i>I</i>
<i>Insulating material</i>	<i>Polyamide 66 (PA 66)</i>
<i>Flammability class per UL94</i>	<i>V0</i>
<i>Clamping spring material</i>	<i>Chrome nickel spring steel (CrNi)</i>
<i>Contact material</i>	<i>Copper alloy</i>
<i>Contact plating</i>	<i>tin-plated</i>
<i>Fire load [MJ]</i>	<i>0.434 [MJ]</i>
<i>Weight [g]</i>	<i>19.54 [g]</i>
<i>Limit temperature range</i>	<i>-60 ... 100 °C</i>
<i>Pin spacing from [in]</i>	<i>0.295 [in]</i>
<i>Pin spacing from [mm]</i>	<i>7.5 [mm]</i>
<i>Contact type</i>	<i>Female connector/socket; for conductors</i>
<i>Product Family</i>	<i>MCS MIDI Classic</i>
<i>Main product function</i>	<i>Female connector/socket</i>
<i>Product type</i>	<i>Pluggable PCB connectors</i>



Printview: Female connector; with integrated push-buttons; 10-pole; Pin spacing 7.5 mm / 0.295 in; codable; with 2 latches - Item No.: 2231-210/026-000

Images & drawings





Printview: Female connector; with integrated push-buttons; 10-pole; Pin spacing 7.5 mm / 0.295 in; codable; with 2 latches - Item No.: 2231-210/026-000



Printview: Female connector; with integrated push-buttons; 10-pole; Pin spacing 7.5 mm / 0.295 in;
codable; with 2 latches - Item No.: 2231-210/026-000

Address

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Telefon: 0571/887-0

Fax: 0571/887-169

<http://www.wago.com>

© WAGO Kontakttechnik GmbH & Co. KG

Technische Änderungen und Irrtümer vorbehalten.