



Specifications

| | |
|---------------------------------|-----------------|
| Pitch: | 2.5mm |
| Type: | Kinked Pin |
| Poles: | 2 to 6 |
| Rated Voltage: | 250V |
| Rated Current: | 3A |
| Operational Temperature: | -25°C to +85°C |
| Withstand Voltage: | 500V AC for 60s |
| Insulation Resistance: | 1000MΩ |
| Contact Resistance: | 30MΩ |
| Recommended PC Board Thickness: | 1.6mm |
| Housing Material: | Nylon 66 |




| Order Code | Poles | $A = (N+1) \times 2.5$ | $B = (N-1) \times 2.5$ |
|--------------------------|-------|------------------------|------------------------|
| 65-6666 | 2 | 7.5 | 2.5 |
| 65-6667 | 3 | 10.0 | 5.0 |
| 65-6668 | 4 | 12.5 | 7.5 |
| 65-6669 | 5 | 15.0 | 10.0 |
| 65-6670 | 6 | 17.5 | 12.5 |
| Note: N = No. of contact | | | |


Male Right Angle



Kinked Pin



2-7(include) pins



Recommend PCB layout
(Tolerance:±0.05)

