


Specifications


Pitch:	2.5mm
Type:	Kinked Pin A Bend
Poles:	2 to 6
Rated Voltage:	250V
Rated Current:	3A
Operational Temperature:	-25°C to +85°C
Withstand Voltage:	500V AC for 60s
Insulation Resistance:	1000MΩ
Contact Resistance:	30MΩ
Recommended PC Board Thickness:	1.6mm
Housing Material:	Nylon 66




Order Code	Poles	$A = (N+1) * 2.5$	$B = (N-1) * 2.5$
65-6679	2	7.5	2.5
65-6680	3	10.0	5.0
65-6681	4	12.5	7.5
65-6682	5	15.0	10.0
65-6683	6	17.5	12.5

Note: N = No. of contact

Male Right Angle




Kinked Pin



2-7(include) pins

Type A



Recommend PCB layout
(Tolerance:±0.05)

