

design • manufacture • supply

MCCOG128064B12W-FPTLW	128 x 64	128 x 64 N/A LCD N		
Specification				
Version: 1 Date: 31/10/2016				
	Re	evision		


Display F	Display Features				
Resolution	128 x 64				
Appearance	Black on White				
Logic Voltage	3.3V	RoHS			
Interface	Parallel / SPI				
Font Set	N/A	CC	mpliant		
Display Mode	Transflective		mphane		
LC Type	FSTN				
Module Size	54.60 x 42.20 x 4.48				
Operating Temperature	-20°C ~ +70°C				
Construction	COG	Box Quantity	Weight / Display		
LED Backlight	White	e • s unr	\/		

* - For full design functionality, please use this specification in conjunction with the ST7565P specification. (Provided Separately)

Display Accessories				
Part Number	Description			
MCIB-12	UNO 32 Breakout Board with SD Card and LED BKL driver.			
MPBV-7	30-Way FFC to Cable and Wires 0.5mm Pitch.			
MCCOG128064B-BEZEL	Bezel made for the MCCOG12064B series			
MDC28-0.5-BC	28 way connector with 0.5mm pitch.			

Optional Variants				
Voltage				

Mechanical Specifications					
Module Size 54.60 x 42.20 x 4.48 (With Backlight) W x H x D m					W x H x D mm
Viewing Area	50.60 x 31.00	50.60 x 31.00 W x H mm Hole-to-Hole			
Dot Size		W x H mm	Dot Pitch		W x H mm



MCCOG128064B12W-FPTLW	128 x 64	N/A	LCD Module
		Specification	
Version: 1 Date: 31/10/2016			
		Revision	

	Pin layout							
Pin	Symbol	Description	Remarks					
1	P/S	P/S = H: Parallel Data I/O P/S = L: Serial Data Input						
2	C86	MPU Interface Selection Pin						
3	V0	Multi-Level power supply for LCD. Voltage applied is						
4	V1	determined by LC cell, changed through resistive voltage divided or changing impedance using OP. AMP.						
5	V2	Levels determined on VSS must maintain magnitudes						
6	V3	shown: $V0 \ge V1 \ge V2 \ge V3 \ge V4 \ge VSS$						
7	V4							
8	C2-	DC/DC Converter. Capacitor between this terminal and CAP2P terminal.						
9	C2+	DC/DC Converter. Capacitor between this terminal and CAP2N terminal.						
10	C1+	DC/DC Converter. Capacitor between this terminal and CAP1N terminal.						
11	C1-	DC/DC Converter. Capacitor between this terminal and CAP1P terminal.						
12	C3+	DC/DC Converter. Capacitor between this terminal and CAP1N terminal.						
13	VOUT	Voltage Converter I/O						
14	VSS	Ground						
15	VDD	Power Sup <mark>pl</mark> y						
16	D7	8-Bit bi-directional data bus, connect to 8-bit or 16-bit						
17	D6	standard MPU data bus. SPI-4 is selected P/S = L						
18	D5	D7 Serial data input (SI); D6 Serial Clock Input (SCL).						
19	D4	D0~D5 connected to VDD or floating.	nlv					
20	D3 5 1 0	When chip select not active, D0~D7 set to high impedance.	Oty					
21	D2							
22	D1							
23	D0							
24	E (/RD)	When connected to 8080MPU, Pin treated as the "/RD" signal of the 8080MPU and is LOW-active. Data bus output status when signal is "L". Connect 6800 MPU, pin treated as "E" signal of 6800 MPU, and is HIGH-active.						
25	R/W (/WR)	When connected to 8080MPU, Pin treated as the "/WR" signal of the 8080MPU and is LOW-active. Connect 6800 MPU, pin treated as "R/W" signal of 6800 MPU, decides access type: R/W = H: Read R/W = L: Write.						
26	D/C	Determines whether data bits are data or command.						
27	/CS1	Chip Select.						
28	/RES	/Res is "L", register settings initialised. Reset operation is performed by the /RES signal Level.						

MCCOG128064B12W-FPTLW	128 x 64	N/A	LCD Module	
		Specification		
Version: 1		Date: 31/10/2016		
		Revision		

Absolute Maximums Ratings								
Item Symbol Minimum Typical Maximum Unit								
Power Supply Voltage	V0, VOUT	-0.3		14.5	V			
Power Supply Voltage	V1,V2,V3,V4	-0.3		V0+0.3	V			
Power Supply Voltage	VDD	-0.3		3.6	V			
Operating Temperature	Top	-20°C		70°C	°C			
Storage temperature	T _{ST}	-30°C		80°C	°C			

Electronic Characteristics						
Item	Symbol	Condition	Minimum	Typical	Maximum	Unit
						V
Supply Voltage Logic	V _{DD} ~ V _{SS}		3.20	3.30	3.40	V
Supply Voltage LCD	V _{DD} ~ V ₀	Ta=25°C	8.60	8.80	9.00	V
Supply Current	I _{DD}	V _{DD=} 3.3V		0.10		mA

LCD Characteristics							
For STN/FSTN LC	For STN/FSTN LCD Panel Types						
Item	Symbol	Condition	Minimum	Typical	Maximum	Unit	
Viewing Angle	Φ2 – Φ1 Θ	CR ≥ 2			45	ψ=180°	
Contrast Ratio	CR		3				
Response Time (Rise)	TR				250	ms	
Response Time (Fall)	SIGH •	m-an l	itactur	e • s	250	ms	

LED Characteristics							
Item	Symbol	Condition	Minimum	Typical	Maximum	Unit	
Supply Current	ILED	V=3.60V		32	40	mA	
Supply Voltage	V		3.50	3.60	3.70	V	
Reverse Voltage	VR				5	V	
Luminance (Without LCD)	IV	ILED=32mA	640	800		Cd/m ²	
LED Life Time		ILED=32mA		50K		Hour	

Attention: It is constant current, not constant voltage, which should be applied when driving the LED backlight, please ensure you adhere to this rule.

MCCOG128064B12W-FPTLW	128 x 64	N/A	LCD Module
Specification			
Version: 1		Date: 31/10/2016	
Revision			