

General Purpose PCB Relay, 8A



DESCRIPTION

General Purpose double pole Signal/Power Relays. These general purpose, low profile, double pole, through hole mounting relays are designed for switching control signals within circuits.

DISTINCTIVE FEATURES

- Low Profile
- Fully Sealed Construction
- DPST or DPDT Contact Configuration
- Contact Form: 2 Form A, 2 Form C
- Sensitivity: 400mW
- PCB Mounting

APPLICATIONS

These relays are suitable for a wide range of applications including automation control, automotive electronics, audio amplification, and industrial equipment.

8A

**2 Form
A**

**2 Form
C**

**440V
AC**

**120V
DC**



ELECTRICAL SPECIFICATION

Contact Form	2 Form A, 2 Form C (See Part Number Table)	
Contact Rating	Resistive	8A 250VAC/30VDC
	Inductive	4A 250VAC Cosφ=0.4
Contact Resistance	Maximum	100mΩ (6VDC 1A)
Insulation Resistance	Minimum	1000MΩ 500VDC
Load	Maximum Switching Voltage	440VAC/120VDC
	Maximum Switching Current	8A
	Maximum Switching Power	2,000VA, 240W
	Minimum Switching Load	5VDC, 100mA
Dielectric Strength	Between open contacts	1,000VAC, 1min
	Between coil and contacts	5,000VAC, 1min

Coil Data

Ambient Temperature: 23°C

Part number	Nominal Voltage VDC	Coil Resistance Ω+/-10%	Operate Voltage ≤VDC	Release Voltage ≥VDC	Coil Power mW
61-6293	12	360	8.4	1.2	400
61-6294	24	1440	16.8	2.4	400



GENERAL SPECIFICATION

Series	General Purpose Signal/Power Relays
Mounting Type	PCB mounting
RoHS	Yes



MATERIALS

Contact Material	Ag Alloy
Outer Case Material	PBT Plastic sealed



CERTIFICATION AND STANDARDS

File Number	Contact Form	Power Consumption	Coil Voltage	Contact rating	Remarks
UL E164730	A/C	0.4W	5-110VDC	8A 250VAC	Insulation calss: F Ambient Temperature: 85°C
TUV 50062453-0002	A/C	0.4W	5, 6, 9, 12, 24, 48, 60, 110VDC	8A 250VAC	Ambient Temperature: 85°C
CQC09002030014 (GB/T 21711.1-2008)	A/C	0.4W	5, 6, 9, 12, 24, 48, 60, 110VDC	8A 250VAC	Ambient Temperature: 85°C
VDE 40043990	A	0.4W	5, 6, 9, 12, 18, 24, 36, 48VDC	8A 250VAC	Ambient Temperature: 85°C

Specifications subject to change without notice.



ENVIRONMENTAL/OPERATING SPECIFICATION

Life	Electrical Life	100,000 operations
		50,000 operations (Inductive: Cosφ=0.4, L/R=7ms)
	Mechanical Life	20,000,000 operations
Operate Time	Maximum 10ms	
Release Time	Maximum 5ms	
Operating Temperature	-40°C to +85°C	
Humidity	35~95%RH, +40°C	
Shock Resistance	Endurance	1,000m/s ²
	Misoperation	100m/s ²
Vibration Resistance	Endurance	10~55Hz, 1.5mm double amplitude
	Misoperation	10~55Hz, 1.5mm double amplitude



TERMINALS

Terminal Type	Solder pins
Terminal Dimensions	See drawing on page 4 and 5



DIMENSIONS/DRAWINGS



Units	mm - unless stated otherwise
Dimensions (Summary)	29.0 x 12.6 x 15.8
Length	29.0
Width	12.6
Height (Excluding pins)	15.8
Weight	13g (approx.)




OUTLINE, WIRING DIAGRAM, MOUNTING HOLE LAYOUT (UNIT: mm)

2 Form C


Outline



Mounting Hole Layout
(Bottom View)




Wiring Diagram
(Bottom View)




2 Form A

Outline



Mounting Hole Layout (Bottom View)




Wiring Diagram (Bottom View)




REFERENCE DATA


Maximum Switching Power



Life Curve



Max. Ambient Temp. Vs. Coil Voltage



A: Coil temperature = Ambient temperature.

B: 110% of nominal coil voltage at rated contact load.



OPTIONS (MOQ may apply)

Coil Voltage	5, 6, 9, 12, 24 & 48V
Contact Form	2 Form A, 2 Form C
Contact Configuration	DPST



PART NUMBER TABLE

Part number	Nominal Coil Voltage	Contact Form	Enclosure	UNSPSC	EAN	Country of Origin
61-6293	12VDC	2 Form C	Sealed	39122325	5053556018727	China
61-6294	24VDC	2 Form C	Sealed	39122325	5053556018734	China

For further information on pricing, delivery, and long-term stock agreements please get in touch with your local business development contact, telephone our main office on **01206 838000** or email **Sales@Rapidonline.com**.



Tried & trusted technology

Important Notice: This data sheet and its contents (the "Information") belong to Rapid Electronics Limited or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but Rapid Electronics Limited assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where Rapid Electronics Limited were aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict Rapid Electronics Limited's liability for death or personal injury resulting from its negligence.