

SAFETY DATA SHEET

Denso Tape



This SDS is not mandated under the REACH Regulation (EC) No 1907/2006, as retained and amended in UK law and is provided for information only when it is not classified

Revision date 08/07/2024

Revision Number 1

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product Name Denso Tape

Pure substance/mixture Mixture

1.2. Relevant identified uses of the substance or mixture and uses advised against

Recommended use Corrosion protection

Uses advised against No specific uses advised against are identified.

1.3. Details of the supplier of the safety data sheet

Supplier

Winn & Coales (Denso) Ltd
Denso House
Chapel Road
West Norwood
SE27 0TR
+44 (0)208 670 7511
mail@denso.net

1.4. Emergency telephone number

Emergency Telephone +44 (0)208 670 7511 (M-F, 8-5 GMT)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Not classified

2.2. Label elements

Not classified

Hazard statements

Not classified

2.3. Other hazards

Other hazards No information available.

SECTION 3: Composition/information on ingredients

3.1 Substances

Not applicable

3.2 Mixtures

Full text of H- and EUH-phrases: see section 16

This product does not contain candidate substances of very high concern at a concentration $\geq 0.1\%$ (UK REACH Article 59)

SECTION 4: First aid measures

4.1. Description of first aid measures

General advice	Get medical advice/attention if you feel unwell. Show this safety data sheet to the doctor in attendance.
Inhalation	Not an expected route of exposure. Remove person to fresh air and keep comfortable for breathing. Loosen tight clothing such as collar, tie or belt.
Eye contact	Rinse thoroughly with plenty of water, also under the eyelids. Remove contact lenses, if present and easy to do. Continue rinsing. Get medical attention if irritation develops and persists.
Skin contact	Wash with soap and water. Do not use organic solvent. In the case of skin irritation or allergic reactions see a doctor.
Ingestion	Not an expected route of exposure. IF SWALLOWED: Get medical attention. Do not induce vomiting without medical advice. If vomiting occurs spontaneously, keep head below hips to prevent aspiration. Never give anything by mouth to an unconscious person. May cause suffocation.
Self-protection of the first aider	No specific requirements are anticipated under normal conditions of use. First aid personnel should wear appropriate protective equipment during any rescue.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms	The severity of the symptoms described will vary dependent on the concentration and the length of exposure. May cause suffocation.
-----------------	--

4.3. Indication of any immediate medical attention and special treatment needed

Note to doctors	Treat symptomatically.
------------------------	------------------------

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable Extinguishing Media	Use extinguishing measures that are appropriate to local circumstances and the surrounding environment. Dry chemical, CO ₂ , alcohol-resistant foam or water spray.
Large Fire	CAUTION: Use of water spray when fighting fire may be inefficient.

Unsuitable extinguishing media Do not scatter spilled material with high pressure water streams.

5.2. Special hazards arising from the substance or mixture

Specific hazards arising from the chemical No information available.

Hazardous combustion products Hydrocarbons. Carbon monoxide. Carbon dioxide (CO₂).

5.3. Advice for firefighters

Special protective equipment and precautions for fire-fighters Firefighters should wear self-contained breathing apparatus and full firefighting turnout gear. Use personal protection equipment. Avoid breathing gas. Evacuate area.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions No action shall be taken without appropriate training or involving any personal risk. Ensure procedures and training for emergency decontamination and disposal are in place. See Section 8 for information on appropriate personal protective equipment. Keep unnecessary and unprotected personnel away from spillage. Do not touch or walk through spilled material. Surfaces contaminated with the product may become slippery.

For emergency responders Use personal protection recommended in Section 8.

6.2. Environmental precautions

Environmental precautions Should not be released into the environment. Insoluble in water. Prevent product from entering drains. Do not flush into surface water or sanitary sewer system. Collect spillage. Inform the relevant authorities if environmental pollution occurs (sewers, waterways, soil or air). See Section 12 for additional Ecological Information.

6.3. Methods and material for containment and cleaning up

Methods for containment Wear personal protective clothing (see section 8). Prevent further leakage or spillage if safe to do so.

Methods for cleaning up Wear personal protective clothing (see section 8). Clear spills immediately. Take up mechanically, placing in appropriate containers for disposal. Disposal should be in accordance with applicable regional, national and local laws and regulations. See section 13 for more information. Take care as floors and other surfaces may become slippery.

Prevention of secondary hazards Clean contaminated objects and areas thoroughly observing environmental regulations.

6.4. Reference to other sections

Reference to other sections See section 8 for more information. See Section 11 for additional Toxicological Information. See Section 12 for additional Ecological Information. See section 13 for more information.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Advice on safe handling Read and follow manufacturers recommendations. Use personal protection recommended in Section 8. Keep away from food, drink and animal feedingstuffs. When not in use, keep containers tightly closed. Do not handle until all safety precautions have been read and

understood.

General hygiene considerations Do not eat, drink or smoke when using this product. Wash hands before breaks and after work. Take off contaminated clothing and wash it before reuse. Ensure that eyewash stations and safety showers are close to the workstation location.

7.2. Conditions for safe storage, including any incompatibilities

Storage Conditions Keep containers tightly closed in a dry, cool and well-ventilated place. Protect from sunlight. Keep in properly labelled containers. Protect from physical damage. The storage area floor should be leak-tight, jointless and not absorbent.

Packaging materials Keep/store only in original container.

7.3. Specific end use(s)

Risk Management Methods (RMM) The information required is contained in this Safety Data Sheet.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure Limits This product, as supplied, does not contain any hazardous materials with occupational exposure limits established by the region specific regulatory bodies.

Biological occupational exposure limits This product, as supplied, does not contain any hazardous materials with biological limits established by the region specific regulatory bodies.

Derived No Effect Level (DNEL) - Workers

Notes

[4] Systemic health effects.
[5] Local health effects.
[6] Long term.
[7] Short term.

Derived No Effect Level (DNEL) - General Public

Notes

[4] Systemic health effects.
[5] Local health effects.
[6] Long term.
[7] Short term.

Predicted No Effect Concentration (PNEC)

Ingredient Comments No dust formed during normal use.

8.2. Exposure controls

Engineering controls Ensure adequate ventilation. Ensure control measures are regularly inspected and maintained. Use engineering controls to keep exposures below the OEL or DNEL. Ensure operatives are trained to minimise exposures.

Personal protective equipment



Eye/face protection	No special protective equipment required. If there is a risk of contact: Wear safety glasses with side shields (or goggles).
Hand protection	Wear protective gloves. Wear suitable gloves tested to EN 374.
Skin and body protection	If there is a risk of contact: Wear suitable protective clothing.
Respiratory protection	No protective equipment is needed under normal use conditions. If exposure limits are exceeded or irritation is experienced, ventilation and evacuation may be required. When workers are facing concentrations above the exposure limit they must use appropriate certified respirators. Wear a respirator (conforming to EN140) fitted with the following P3 cartridge (conforming to EN143): Organic vapour filter.
Environmental exposure controls	Keep container closed when not in use.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	Solid
Appearance	Liquid-impregnated cloth
Colour	dark brown dark green
Odour	Characteristic.
Odour threshold	No information available

Property	Values	Remarks • Method
Melting point / freezing point	> 60 °C	None known
Initial boiling point and boiling range	No data available	None known
Flammability	No data available	None known
Flammability Limit in Air		None known
Upper flammability or explosive limits	No data available	
Lower flammability or explosive limits	No data available	
Flash point	No data available	None known
Autoignition temperature	No data available	None known
Decomposition temperature		None known
pH	No data available	None known
pH (as aqueous solution)	No data available	None known
Kinematic viscosity	No data available	None known
Dynamic viscosity	No data available	None known
Water solubility	Insoluble in water	None known
Solubility(ies)	Organic solvents	None known
Partition coefficient	No data available	None known
Vapour pressure	No data available	None known
Relative density	No data available	None known
Bulk density	No data available	
Liquid Density	No data available	
Relative vapour density	No data available	None known
Particle characteristics		
Particle Size	No information available	
Particle Size Distribution	No information available	
Explosive properties	No information available	

Oxidising properties No information available

9.2. Other information

SECTION 10: Stability and reactivity

10.1. Reactivity

Reactivity No information available.

10.2. Chemical stability

Stability Stable under normal conditions.

Explosion data

Sensitivity to mechanical impact None.

Sensitivity to static discharge None.

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions None under normal processing.

10.4. Conditions to avoid

Conditions to avoid None known based on information supplied.

10.5. Incompatible materials

Incompatible materials None known based on information supplied.

10.6. Hazardous decomposition products

Hazardous decomposition products Hydrocarbons. Carbon monoxide. Carbon dioxide (CO₂).

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Information on likely routes of exposure

Product Information

Inhalation Specific test data for the substance or mixture is not available.

Eye contact Specific test data for the substance or mixture is not available.

Skin contact Specific test data for the substance or mixture is not available.

Ingestion Specific test data for the substance or mixture is not available.

Symptoms related to the physical, chemical and toxicological characteristics

Symptoms No information available.

Acute toxicity

Numerical measures of toxicity

The following values are calculated based on chapter 3.1 of the GHS document

ATEmix (oral)	8,733.60 mg/kg
ATEmix (dermal)	15,957.30 mg/kg
ATEmix (inhalation-gas)	99,999.00 ppm
ATEmix (inhalation-dust/mist)	421.10 mg/l
ATEmix (inhalation-vapour)	99,999.00 mg/l

Component Information

Delayed and immediate effects as well as chronic effects from short and long-term exposure Based on available data, the classification criteria are not met

Skin corrosion/irritation Based on available data, the classification criteria are not met.

Serious eye damage/eye irritation Based on available data, the classification criteria are not met.

Respiratory or skin sensitisation Based on available data, the classification criteria are not met.

Germ cell mutagenicity Based on available data, the classification criteria are not met.

Carcinogenicity Based on available data, the classification criteria are not met.

Reproductive toxicity Based on available data, the classification criteria are not met.

STOT - single exposure Based on available data, the classification criteria are not met.

STOT - repeated exposure Based on available data, the classification criteria are not met.

Aspiration hazard Based on available data, the classification criteria are not met.

Other adverse effects No information available.

SECTION 12: Ecological information

12.1. Toxicity

Ecotoxicity

Unknown aquatic toxicity Contains 0.06009 % of components with unknown hazards to the aquatic environment

12.2. Persistence and degradability

Persistence and degradability No information available.

12.3. Bioaccumulative potential

Bioaccumulation There is no data for this product.

12.4. Mobility in soil

Mobility in soil No information available.

12.5. Results of PBT and vPvB assessment

PBT and vPvB assessment No information available.

12.6. Endocrine disrupting properties

No information available.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Waste from residues/unused products The generation of waste should be minimised or avoided wherever possible. When handling waste, the safety precautions applying to handling of the product should be considered. Should not be released into the environment. Dispose of contents and container in accordance with local, regional, national, and international regulations as applicable.

EWC waste code: 08 04 10* waste adhesives and sealants other than those mentioned in 08 04 09. The listed EWC waste code classification, according to the List of Waste (LoW), are to be understood as a recommendation. A final decision must be made in agreement with the regional waste disposal company.

Contaminated packaging The generation of waste should be minimised or avoided wherever possible. Empty containers should be taken to an approved waste handling site for recycling or disposal. Should not be released into the environment. Dispose of contents and container in accordance with local, regional, national, and international regulations as applicable.

SECTION 14: Transport information

IATA

14.1 UN number or ID number	Not regulated
14.2 UN proper shipping name	Not regulated
14.3 Transport hazard class(es)	Not regulated
14.4 Packing group	Not regulated
14.5 Environmental hazards	Not applicable
14.6 Special precautions for user	

IMDG

14.1 UN number or ID number	Not regulated
14.2 UN proper shipping name	Not regulated
14.3 Transport hazard class(es)	Not regulated
14.4 Packing group	Not regulated
14.5 Environmental hazards	Not applicable
14.6 Special precautions for user	
14.7 Maritime transport in bulk according to IMO instruments	No information available

RID

14.1 UN number or ID number	Not regulated
14.2 UN proper shipping name	Not regulated
14.3 Transport hazard class(es)	Not regulated
14.4 Packing group	Not regulated
14.5 Environmental hazards	Not applicable

14.6 Special precautions for user**ADR**

14.1 UN number or ID number	Not regulated
14.2 UN proper shipping name	Not regulated
14.3 Transport hazard class(es)	Not regulated
14.4 Packing group	Not regulated
14.5 Environmental hazards	Not applicable
14.6 Special precautions for user	

Transport Pictogram**SECTION 15: Regulatory information****15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture****National regulations****Authorisations and/or restrictions on use:**

This product does not contain substances subject to authorisation (UK REACH - Annex XIV). This product does not contain substances subject to restriction (UK REACH - Annex XVII).

Persistent Organic Pollutants

Not applicable

Export Notification requirements

Not applicable

Named dangerous substances per COMAH (SI 2015/483 as amended)

Not applicable

The Ozone-Depleting Substances Regulations 2015

Not applicable

The Biocidal Products Regulations 2001 (as amended)

Not applicable

The Water Environment (Water Framework Directive) (England and Wales) Regulations 2017 (as amended)

Not applicable

Poisons and Explosive Precursors

Not applicable

International Inventories

TSCA	Contact supplier for inventory compliance status
DSL/NDSL	Contact supplier for inventory compliance status
EINECS/ELINCS	Contact supplier for inventory compliance status
ENCS	Contact supplier for inventory compliance status
IECSC	Contact supplier for inventory compliance status
KECI	Contact supplier for inventory compliance status
PICCS	Contact supplier for inventory compliance status
AIIC	Contact supplier for inventory compliance status
NZIoC	Contact supplier for inventory compliance status

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory
DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List
EINECS/ELINCS - European Inventory of Existing Chemical Substances/European List of Notified Chemical Substances
ENCS - Japan Existing and New Chemical Substances
IECSC - China Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances
PICCS - Philippines Inventory of Chemicals and Chemical Substances
AIIC - Australian Inventory of Industrial Chemicals
NZIoC - New Zealand Inventory of Chemicals

15.2. Chemical safety assessment

Chemical Safety Report No information available

SECTION 16: Other information

Key or legend to abbreviations and acronyms used in the safety data sheet

Legend

SVHC: Substances of Very High Concern for Authorisation:

Legend Section 8: Exposure controls/personal protection

TWA	TWA (time-weighted average)	STEL	STEL (Short Term Exposure Limit)
Ceiling	Maximum limit value	Sk*	Skin designation
+	Sensitisers		

Classification procedure

Classification according to Regulation (EC) No. 1272/2008 [CLP]	Method Used
Acute oral toxicity	Calculation method
Acute dermal toxicity	Calculation method
Acute inhalation toxicity - gas	Calculation method
Acute inhalation toxicity - vapour	Calculation method
Acute inhalation toxicity - dust/mist	Calculation method
Skin corrosion/irritation	Calculation method
Serious eye damage/eye irritation	Calculation method
Respiratory sensitisation	Calculation method
Skin sensitisation	Calculation method
Mutagenicity	Calculation method
Carcinogenicity	Calculation method
Reproductive toxicity	Calculation method
STOT - single exposure	Calculation method
STOT - repeated exposure	Calculation method
Acute aquatic toxicity	Calculation method
Chronic aquatic toxicity	Calculation method
Aspiration hazard	Calculation method
Ozone	Calculation method

Key literature references and sources for data used to compile the SDS

Agency for Toxic Substances and Disease Registry (ATSDR)
 U.S. Environmental Protection Agency ChemView Database
 European Food Safety Authority (EFSA)
 European Chemicals Agency (ECHA) Committee for Risk Assessment (ECHA_RAC)
 European Chemicals Agency (ECHA) (ECHA_API)
 EPA (Environmental Protection Agency)
 Acute Exposure Guideline Level(s) (AEGl(s))
 U.S. Environmental Protection Agency Federal Insecticide, Fungicide, and Rodenticide Act
 U.S. Environmental Protection Agency High Production Volume Chemicals
 Food Research Journal
 Hazardous Substance Database
 International Uniform Chemical Information Database (IUCLID)
 National Institute of Technology and Evaluation (NITE)
 Australian National Industrial Chemicals Notification and Assessment Scheme (NICNAS)
 NIOSH (National Institute for Occupational Safety and Health)
 National Library of Medicine's ChemID Plus (NLM CIP)
 National Library of Medicine's PubMed database (NLM PUBMED)

National Toxicology Program (NTP)
New Zealand's Chemical Classification and Information Database (CCID)
Organisation for Economic Co-operation and Development Environment, Health, and Safety Publications
Organisation for Economic Co-operation and Development High Production Volume Chemicals Programme
Organisation for Economic Co-operation and Development Screening Information Data Set
World Health Organization

Revision date 08/07/2024

This SDS complies with the requirements of UK REACH Regulations SI 2019/758 (as amended)
Take note of Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet

UK SDS version information - XGHS

UL release:
GHS Revision 7
2022 Q1

United Kingdom

Partial process, including GHS Wizard, NO TW