


Micro Miniature High Sensitivity Signal Relay



DESCRIPTION

A range of Micro Miniature High Sensitivity SPDT Signal Relays. These general purpose, single pole, through hole mounting relays are designed for switching small measurement and control signals within circuits.

DISTINCTIVE FEATURES

- Micro miniature size
- Dimensions: 15.6×10.6×11.8(mm)
- High sensitivity
- Contact: 1 Form C
- Contact Material: AuAg overlay
- Electrical Life: 100,000 operations
- Through Hole Mounting
- Fully Sealed Construction
- Max. Switching capacity 3A

APPLICATIONS

The small dimensions of these high sensitivity signal relays make them suitable for a wide variety of applications, including communications, measurement, automation control and audio visual equipment.

3A

UL

CSA

SPDT



ELECTRICAL SPECIFICATION

Contact Form		1 Form C
Contact Rating		1A 120VAC/24VDC 3A 120VAC/24VDC
Contact Resistance		Max. 50mΩ (6VDC 0.1A)
Insulation Resistance		Min. 100MΩ 500VDC
Load	Max Switching Voltage	220VAC/30VDC
	Max Switching Current	3A
	Max Switching Power	360VA, 72W
	Min Switching Load	5VDC, 10mA
Dialectric Strength	Between Open Contacts	750VAC, 1min
	Between Coil & Contacts	1,000VAC, 1min
Nominal Coil Power		200mW, 360mW



ENVIRONMENTAL/OPERATING SPECIFICATION

Operating Temperature		-25c to +70C
Humidity		35~95%RH, +40C
Shock Resistance	Endurance	1,000m/s ²
	Misoperation	100m/s ²
Vibration Resistance	Endurance	10~55Hz, 1.5mm double amplitude
	Misoperation	10~55Hz, 1.5mm double amplitude



CERTIFICATION AND STANDARDS

File Number	Contact Form	Power Consumption	Coil Voltage	Contact Rating	Remarks
UL E164730	C	0.20W/0.36W	3-24VDC	1A 120VAC/24VDC 3A 120VAC/24VDC	-
TUV 50103498	C	0.20W/0.36W	3-24VDC	1A 120VAC/24VDC	Ambient Temperature: 70°C
				3A 250VAC	Ambient Temperature: -25°C~25°C
CQC 12002086133 1A 120VAC	C	0.20W/0.36W	3-24VDC	1A 120VAC	Ambient Temperature: -40°C~70°C
				3A 120VAC/24VDC	Ambient Temperature: -25°C~25°C



TERMINALS



Terminal Type	Solder pins
Terminal Dimensions	See Drawings




DIMENSIONS/DRAWINGS

Units	mm – unless stated otherwise
Height (excluding pins)	11.8 ± 0.3
Width/diameter	10.6 ± 0.3
Length/depth	15.6 ± 0.3
Weight	Approximately 2.2g


Dimensions



Wiring Diagram




Mounting hole layout






DIMENSIONS/DRAWINGS


Time Curve




Coil Temperature Rise




Operate Range



Life Curves



Maximum Switching Power





PART NUMBER TABLE

Part number	Coil Power mW	Nominal Voltage VDC	Coil Resistance Ω +/-10%	Operating Voltage \leq VDC	Release Voltage \geq VDC	UNSPSC	EAN
61-6402	200mW	24	2880	18	2.4	39122325	5053556032822



OPTIONS (MOQ MAY APPLY)

Also available with a coil voltage of	5, 12, 24 VDC
Also available with 360mW coil power with a coil voltage of	3, 5, 6, 9, 12, or 24VDC

For further information on pricing, delivery, and long-term stock agreements please get in touch with your local business development contact, telephone our main office on **01206 838000** or email **Sales@Rapidonline.com**.



Tried & trusted technology

Important Notice: This data sheet and its contents (the "Information") belong to Rapid Electronics Limited or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but Rapid Electronics Limited assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where Rapid Electronics Limited were aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict Rapid Electronics Limited's liability for death or personal injury resulting from its negligence.