

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 08.03.2017

Version number 5

Revision: 04.07.2016

**SECTION 1: Identification of the substance/mixture and of the company/
undertaking**

· **1.1 Product identifier**

· **Trade name:** *Glass cleaner concentrate RM 500*

· **1.2 Relevant identified uses of the substance or mixture and uses advised against**

· **Technical function** *Cleaning agent*

· **Application of the substance / the mixture** *Glass Cleaner*

· **1.3 Details of the supplier of the safety data sheet**

· **Manufacturer/Supplier:**

*Alfred Kärcher GmbH & Co. KG
Alfred-Kärcher-Str. 28-40
D - 71364 Winnenden*

*Postfach 160
D - 71349 Winnenden*

*Tel.: +49-7195-14-0
Fax : +49-7195-14-2212*

www.karcher.com

*Distributor:
Kaercher (UK) Ltd.
Kaercher House
Beaumont Road
Banbury
Oxon OX16 1TB
Great Britain*

*Tel.: +44-1295-752-000
Fax : +44-1295-266-436*

· **Further information obtainable from:**

*Department PCD-D
Tel.: +49-7195-14-2548
Fax : +49-7195-14-3164
safetydata@karcher.com*

· **1.4 Emergency telephone number:**

*For Hazardous Materials [or Dangerous Goods] Incidents
Spill, Leak, Fire, Exposure, or Accident
Call CHEMTREC Day or Night
Within USA and Canada: 1-800-424-9300
Outside USA and Canada: +1 703-741-5970 (collect calls accepted)*

GB

(Contd. on page 2)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 08.03.2017

Version number 5

Revision: 04.07.2016

Trade name: Glass cleaner concentrate RM 500

(Contd. of page 1)

SECTION 2: Hazards identification

- **2.1 Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**

Eye Irrit. 2 H319 Causes serious eye irritation.

- **2.2 Label elements**

- **Labelling according to Regulation (EC) No 1272/2008**

The product is classified and labelled according to the CLP regulation.

- **Hazard pictograms**



GHS07

- **Signal word** Warning

- **Hazard statements**

H319 Causes serious eye irritation.

- **Precautionary statements**

P102 Keep out of reach of children.

P280 Wear eye protection / face protection.

P264 Wash hands thoroughly after handling.

P305+P351+P338 **IF IN EYES:** Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P337+P313 If eye irritation persists: Get medical advice/attention.

- **2.3 Other hazards**

The product does not contain any organic halogen compounds (AOX), nitrates, heavy metal compounds.

- **Results of PBT and vPvB assessment**

- **PBT:** Not applicable.

- **vPvB:** Not applicable.

SECTION 3: Composition/information on ingredients

- **3.2 Chemical characterisation: Mixtures**

- **Description:** Cleaning agent

- **Dangerous components:**

CAS: 67-63-0 EINECS: 200-661-7 Index number: 603-117-00-0 Reg.nr.: 02-2119752543-38-XXXX	propan-2-ol Flam. Liq. 2, H225; Eye Irrit. 2, H319; STOT SE 3, H336	0.1-<3%
EC number: 931-952-3	alcohols, C10-12, ethoxylated (<5 - <15 EO) Eye Dam. 1, H318; Acute Tox. 4, H302	0.1-<3%

(Contd. on page 3)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 08.03.2017

Version number 5

Revision: 04.07.2016

Trade name: Glass cleaner concentrate RM 500

(Contd. of page 2)

CAS: 1336-21-6 EINECS: 215-647-6 Index number: 007-001-01-2 Reg.nr.: 02-2119752451-43-0000	ammonia, aqueous solution ⚠ Skin Corr. 1C, H314; ⚠ Aquatic Acute 1, H400; ⚠ STOT SE 3, H335	0.1-0.2%
---	---	----------

· Regulation (EC) No 648/2004 on detergents / Labelling for contents

non-ionic surfactants

<5%

· Additional information For the wording of the listed hazard phrases refer to section 16.

SECTION 4: First aid measures

- **4.1 Description of first aid measures**
- **After inhalation** Supply fresh air; consult doctor in case of complaints.
- **After skin contact** Rinse with warm water.
- **After eye contact** Rinse opened eye for several minutes under running water.
- **After swallowing**
Rinse out mouth and then drink plenty of water.
If symptoms persist consult doctor.
- **4.2 Most important symptoms and effects, both acute and delayed**
No further relevant information available.
- **4.3 Indication of any immediate medical attention and special treatment needed**
No further relevant information available.

SECTION 5: Firefighting measures

- **5.1 Extinguishing media**
- **Suitable extinguishing agents**
CO₂, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.
- **For safety reasons unsuitable extinguishing agents** Water with full jet.
- **5.2 Special hazards arising from the substance or mixture**
No further relevant information available.
- **5.3 Advice for firefighters**
- **Protective equipment:** No special measures required.
- **Additional information**
Collect contaminated fire fighting water separately. It must not enter the sewage system.

SECTION 6: Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures** Not required.
- **6.2 Environmental precautions:**
Dilute with plenty of water.
Do not allow to enter sewers/ surface or ground water.
Do not allow to penetrate the ground/soil.
- **6.3 Methods and material for containment and cleaning up:**
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders).
- **6.4 Reference to other sections**
No dangerous substances are released.
See Section 7 for information on safe handling

(Contd. on page 4)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 08.03.2017

Version number 5

Revision: 04.07.2016

Trade name: Glass cleaner concentrate RM 500

(Contd. of page 3)

See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.

SECTION 7: Handling and storage

- **7.1 Precautions for safe handling** Avoid contact with eyes and skin.
- **Information about fire - and explosion protection:** No special measures required.
- **7.2 Conditions for safe storage, including any incompatibilities**
- **Storage**
- **Requirements to be met by storerooms and receptacles:** No special requirements.
- **Information about storage in one common storage facility:**
Keep away from food, beverages and feed.
- **Further information about storage conditions:** None.
- **7.3 Specific end use(s)** No further relevant information available.

SECTION 8: Exposure controls/personal protection

- **Additional information about design of technical facilities:** No further data; see item 7.

- **8.1 Control parameters**

- **Ingredients with limit values that require monitoring at the workplace:**

67-63-0 propan-2-ol

WEL	Short-term value: 1250 mg/m ³ , 500 ppm
	Long-term value: 999 mg/m ³ , 400 ppm

- **DNELs**

67-63-0 propan-2-ol

Oral	DNEL	26 mg/kg*d (consumer)
Dermal	DNEL	888 mg/kg*d (employee) 319 mg/kg*d (consumer)
Inhalative	DNEL	500 mg/m ³ (employee) 89 mg/m ³ (consumer)

- **8.2 Exposure controls**
- **Personal protective equipment**
- **General protective and hygienic measures** Wash hands before breaks and at the end of work.
- **Respiratory protection:** Not necessary if room is well-ventilated.
- **Protection of hands:** Not required.
- **Material of gloves**
The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.
- **Penetration time of glove material**
The exact break trough time has to be found out by the manufacturer of the protective gloves and has to be observed.

(Contd. on page 5)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 08.03.2017

Version number 5

Revision: 04.07.2016

Trade name: Glass cleaner concentrate RM 500

(Contd. of page 4)

· **Eye protection:**



Tightly sealed goggles.

SECTION 9: Physical and chemical properties

· **9.1 Information on basic physical and chemical properties**

· **General Information**

· **Appearance:**

Form:	Fluid
Colour:	Colourless
· Odour:	Characteristic
· Odour threshold:	Not determined.

· pH-value at 20 °C:	10.3
· pH-value 1 %:	9

· **Change in condition**

Melting point/freezing point:	0 °C
Initial boiling point and boiling range:	100 °C

· Flash point:	>100 °C
-----------------------	---------

· Flammability (solid, gaseous)	Not applicable.
--	-----------------

· Ignition temperature:	not applicable
--------------------------------	----------------

· Decomposition temperature:	Not determined.
-------------------------------------	-----------------

· Auto-ignition temperature:	Product is not selfigniting.
-------------------------------------	------------------------------

· Explosive properties:	Product does not present an explosion hazard.
--------------------------------	---

· **Explosion limits:**

Lower:	Not determined.
Upper:	Not determined.

· Vapour pressure:	Not determined.
---------------------------	-----------------

· Density at 20 °C:	0.994 g/cm ³
· Relative density	Not determined.
· Vapour density	Not determined.
· Evaporation rate	Not determined.

· **Solubility in / Miscibility with**

Water:	Fully miscible
---------------	----------------

· Partition coefficient: n-octanol/water:	Not determined.
--	-----------------

· **Viscosity:**

dynamic at 20 °C:	3 mPas
--------------------------	--------

(Contd. on page 6)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 08.03.2017

Version number 5

Revision: 04.07.2016

Trade name: Glass cleaner concentrate RM 500

(Contd. of page 5)

kinematic:	<i>Not determined.</i>
· Solvent content:	
Organic solvents:	1.5 %
VOC (EC)	1,50 %
Solids content:	2.0 %
· 9.2 Other information	<i>No further relevant information available.</i>

SECTION 10: Stability and reactivity

- **10.1 Reactivity** corresponds to 10.3
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:**
No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** *No dangerous reactions known*
- **10.4 Conditions to avoid** *No further relevant information available.*
- **10.5 Incompatible materials:** *No further relevant information available.*
- **10.6 Hazardous decomposition products:** *No dangerous decomposition products known*

SECTION 11: Toxicological information

- **11.1 Information on toxicological effects**
- **Acute toxicity** *Based on available data, the classification criteria are not met.*

· LD/LC50 values relevant for classification:

67-63-0 propan-2-ol		
Dermal	LD50	12800 mg/kg (can)
		12800 mg/kg (rabbit)
Inhalative	LC50	5280 mg/kg (Rat)
alcohols, C10-12, ethoxylated (<5 - <15 EO)		
Oral	LD50	> 300-2000 mg/kg (Rat)
1336-21-6 ammonia, aqueous solution		
Oral	LDLo	43 mg/kg (human)
		750 mg/kg (cat)
Inhalative	LC50	350 mg/kg (Rat)
	LCLo	5000 ppm (human)

- **Primary irritant effect:**
- **Skin corrosion/irritation** *Based on available data, the classification criteria are not met.*
- **Serious eye damage/irritation**
Causes serious eye irritation.
- **Respiratory or skin sensitisation** *Based on available data, the classification criteria are not met.*
- **CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)**
- **Germ cell mutagenicity** *Based on available data, the classification criteria are not met.*
- **Carcinogenicity** *Based on available data, the classification criteria are not met.*
- **Reproductive toxicity** *Based on available data, the classification criteria are not met.*

(Contd. on page 7)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 08.03.2017

Version number 5

Revision: 04.07.2016

Trade name: Glass cleaner concentrate RM 500

(Contd. of page 6)

- **STOT-single exposure** Based on available data, the classification criteria are not met.
- **STOT-repeated exposure** Based on available data, the classification criteria are not met.
- **Aspiration hazard** Based on available data, the classification criteria are not met.

SECTION 12: Ecological information

· **12.1 Toxicity**

· **Aquatic toxicity:**

67-63-0 propan-2-ol

LC50/96 h	9640 mg/l (<i>Pimephales promelas</i>)
EC50/48 h	13299 mg/l (<i>Daphnia magna</i>)
EC50/72 h	> 1000 mg/l (<i>Desmodesmus subspicatus</i>)
EC10/18 h	> 1000 mg/l (<i>Pseudomonas putida</i>) (DIN 38412)

1336-21-6 ammonia, aqueous solution

LC50/96 h	0.75 - 3.4 mg/l (<i>Pimephales promelas</i>)
EC50/48 h	24 mg/l (<i>Daphnia magna</i>)
EC50/96 h	0.53 mg/l (<i>Oncorhynchus mykiss</i>)

- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.

· **Additional ecological information:**

· **COD-value:** 108000 mg/l

· **General notes:**

The surfactant(s) contained in this preparation complies (comply) with the biodegradability criteria as laid down in Regulation (EC) No.648/2004 on detergents. Data to support this assertion are held at the disposal of the competent authorities of the Member States and will be made available to them, at their direct request or at the request of a detergent manufacturer.

Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.

· **12.5 Results of PBT and vPvB assessment**

· **PBT:** Not applicable.

· **vPvB:** Not applicable.

· **12.6 Other adverse effects** No further relevant information available.

SECTION 13: Disposal considerations

· **13.1 Waste treatment methods**

· **Recommendation**

Must not be disposed together with household garbage. Do not allow product to reach sewage system.

Must be specially treated adhering to official regulations.

· **European waste catalogue**

07 06 01*	aqueous washing liquids and mother liquors
-----------	--

(Contd. on page 8)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 08.03.2017

Version number 5

Revision: 04.07.2016

Trade name: Glass cleaner concentrate RM 500

(Contd. of page 7)

- **Uncleaned packaging:**
- **Recommendation:** Non contaminated packagings may be recycled.
- **Recommended cleansing agents:** Water, if necessary together with cleaning agents.

SECTION 14: Transport information

· 14.1 UN-Number · ADR, ADN, IMDG, IATA	Void
· 14.2 UN proper shipping name · ADR, ADN, IMDG, IATA	Void
· 14.3 Transport hazard class(es) · ADR, ADN, IMDG, IATA · Class	Void
· 14.4 Packing group · ADR, IMDG, IATA	Void
· 14.5 Environmental hazards: · Marine pollutant:	No
· 14.6 Special precautions for user	Not applicable.
· 14.7 Transport in bulk according to Annex II of Marpol and the IBC Code	Not applicable.
· Transport/Additional information:	Not dangerous according to the above specifications.
· UN "Model Regulation":	Void

SECTION 15: Regulatory information

- **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**
 - **Directive 2012/18/EU**
 - **Named dangerous substances - ANNEX I Keiner der Inhaltsstoffe ist enthalten.**
 - **REGULATION (EC) No 1907/2006 ANNEX XVII Conditions of restriction: 3**
 - **National regulations**
- **Information about limitation of use:**
Employment restrictions concerning juveniles must be observed.
- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship. A product information sheet can be provided if requested.

(Contd. on page 9)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 08.03.2017

Version number 5

Revision: 04.07.2016

Trade name: Glass cleaner concentrate RM 500

(Contd. of page 8)

· **Relevant phrases**

H225 Highly flammable liquid and vapour.
H302 Harmful if swallowed.
H314 Causes severe skin burns and eye damage.
H318 Causes serious eye damage.
H319 Causes serious eye irritation.
H335 May cause respiratory irritation.
H336 May cause drowsiness or dizziness.
H400 Very toxic to aquatic life.

· **Department issuing SDS: PCD-D**

· **Contact:**

Department PCD-D
Tel.: +49-7195-14-2548
Fax : +49-7195-14-3164
safetydata@karcher.com

· **Abbreviations and acronyms:**

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)
IMDG: International Maritime Code for Dangerous Goods
IATA: International Air Transport Association
GHS: Globally Harmonised System of Classification and Labelling of Chemicals
EINECS: European Inventory of Existing Commercial Chemical Substances
ELINCS: European List of Notified Chemical Substances
CAS: Chemical Abstracts Service (division of the American Chemical Society)
VOCV: Lenkungsabgabe auf flüchtigen organischen Verbindungen, Schweiz (Swiss Ordinance on volatile organic compounds)
VOC: Volatile Organic Compounds (USA, EU)
DNEL: Derived No-Effect Level (REACH)
LC50: Lethal concentration, 50 percent
LD50: Lethal dose, 50 percent
PBT: Persistent, Bioaccumulative and Toxic
vPvB: very Persistent and very Bioaccumulative
Flam. Liq. 2: Flammable liquids – Category 2
Acute Tox. 4: Acute toxicity – Category 4
Skin Corr. 1C: Skin corrosion/irritation – Category 1C
Eye Dam. 1: Serious eye damage/eye irritation – Category 1
Eye Irrit. 2: Serious eye damage/eye irritation – Category 2
STOT SE 3: Specific target organ toxicity (single exposure) – Category 3
Aquatic Acute 1: Hazardous to the aquatic environment - acute aquatic hazard – Category 1

· *** Data compared to the previous version altered.**

· 0-011-373-0 RM 500/7-2 1-894