

Warton Brown Flux Jelly is suitable for electrical and general purpose solder work, jointing commonly encountered metals.

- Non Corrosive Jelly based soldering flux
- Flux residue can be removed using with solvent cleaner
- Disposable polyethylene gloves are recommended when handling soldering flux.
- Manufactured in the UK
- Easy to use

For more information Telephone: +44 (0)1706 218888





Material Safety Datasheet Brown Flux Jelly

Section 1. Identification of t	he substance / preparation and of the company / undertaking	
Product Name:	Brown Flux Jelly	
Manufactured By:	Warton Metals Limited	
	Grove Mill, Commerce Street. Haslingden. Lancashire. BB4 5JT. ENGLAND.	
Emergency Telephone:	+44 (0)1706 218888	
Emergency Fax:	+44 (0)1706 221188	
Section 2. Composition / Info	ormation on Ingredients	
Ingredient	CAS No: Classification Symbol Risk phrases Safety Phrases % Present	

Ingredient Modified rosins: Acivators	CAS No: Classification Symbol Risk phrases Safety Phrases % Present * - 42/43 40-50
	*CAS No: is variable and depends on the exact identity of the modified rosin used. The classification symbol and risk phrases are only a requirement for rosin (colophony CAS No: 8050-09-7) but are used by Warton for all modified rosins in the absence of data indicating that they are not sensitises.
Section 3. Hazards Identification	

Section 3. Hazards identification		
Rosin or Modified Rosin	This product contains rosin or modified rosin, prolonged or repeated skin contact can cause an allergic reaction to develop. Inhalation of the fumes will irritate the respiratory system. Prolonged or repeated	
	exposure to the fumes emitted during reflow may cause sensitisation which could lead to occupational asthma.	

Section 4. First Aid Measures	
Inhalation:	Irritates nose and throat, can cause an asthmatic type reaction. Remove affected person to fresh air, obtain medical attention if there is any respiratory distress. Remove from exposure.
Skin Contact:	Rosin and rosin derivatives can cause a rash to develop. Wash hands with soap and warm water after handling. If any skin irritation develops seek medical advice. Hot contact - cool affected parts thoroughly under running water. DO NOT remove adhering material, obtain medical attention.
Eye Contact:	Irritating and abrasive. Flush immediately with plenty of water, ensure that the eyeball and the inside of the eyelids are properly bathed by gently prising open the eyelids. Also make sure that the contaminated water runs off the face away from the eyes. Seek medical attention.
Ingestion:	Will irritate gastric tract. If the casualty is unconscious but breathing, place on one side in the recovery position. If breathing has stopped apply artificial respiration or give oxygen by mask. If the patient is conscious, then encourage the patient to rinse the mouth out several times with water but do not induce vomiting. Do not give anything to drink if the patient finds it difficult to swallow. *Obtain urgent medical attention.

Section 5. Fire Fighting Measures	
Suitable extinguishing media:	Dry chemical, carbon dioxide, water spray or foam.
Do not use:	Water in a jet.
Exposure hazards:	Irritant fumes.
Protective measures:	Fire fighters should wear full protective clothing and breathing apparatus, operated in positive pressure
	mode.

Section 6. Accidental Release Measures		
Personal precautions:	Refer to Section 8, Personal Protection.	
Environmental precautions:	Refer to Section 13, Disposal.	
Methods of clearing up:	Avoid contact with the skin. Scrape up and place in closed container for subsequent disposal.	

Avoid inhaling the flux fumes. Wash the hands with soap and warm water after handling, particularly	
before eating and drinking and smoking.	
These products should be stored in a cool dry area.	

Section 8. Exposure Controls & Personal Protection		
Occupational Exposure Limits:-		
Substance: Lo	ng Term Exposure Limits (8 Hour TWA) Short Term Exposure Limit (15 min)	
Rosin core solder pyrolisis products (as formaldehyde).	0.1 mg/m ³ 0.3 mg/m ³ Sen	
Personal Protection:- Respiratory protection Eye Protection: Skin Protection:	Not generally required unless there is inadequate extraction. Use of safety glasses or goggles is recommended. Butyl rubber gloves, suitable work wear should be worn to protect clothing.	

Section 9. Physical & Chemi	cal Properties.			
Appearance / colour:	Brown jelly	Melting Point ^o C:	50-56	
Odour:	Mild.	Auto ignition temperature °C:	N/A	
Boiling point ^o C:	above 300	Explosive limits (% vol):	Insoluble	
Flash point (closed) °C:	above 250	Solubility/miscibility:	N/D	
Explosive / oxidising:	N/A	Volatile content (V.O.C):	N/A	
Viscosity:	N/D	Vapour density (air = 1):	N/D	
Vapour pressure:	N/A	Conductivity	N/D	
Evaporation rate:	N/A	Specific Gravity:	N/D	
Flammability:	N/A			
pH/Concentration:	N/D			

Section 10. Stability & Reactivity	
Conditions to avoid:	Any sources of ignition
Materials to avoid:	Strong oxidising agents
	Irritant fumes

	experimental data)
Inhalation:	Main route of exposure for flux fumes. When heated emits fumes that irritate the respiratory system.
Eye contact:	The flux fumes may irritate the eyes.
Skin contact:	Rosin and rosin derivatives can cause an allergic skin reaction. Heated material may cause burns.
Ingestion:	The flux fumes produced during soldering will irritate the nose and throat. For personnel that have
Acute toxicity:Flux	become sensitised to rosin fumes, exposure can cause symptoms of asthma attacks of wheezing chest tightness and breathlessness - alveolitis breathlessness and flu like symptoms), or rhinitis an conjunctivitis (runny or stuffy nose and watery or prickly eyes typical of hay fever). Rosin can also caus sensitisation by skin contact causing dermatitis. Note that personnel that are sensitised to rosin ma also react to modified rosins or vice versa.
LD50 (Oral rat):	Modified rosin >2500mg/Kg.

Section 12. Ecological Information (Possible environmental effects and behaviour /ODP/aquatic toxicity): (See section 13. Disposal Considerations).

Section 13. Disposal Considerations		
(Safe disposal of product, its	Disposal must be in accordance with local and national legislation.	
residues and packaging materials):		

Section 14. Transport Information

This product is NOT classified as dangerous for transportation.

Section 15. Regulatory Information		
Labelling Information		
Indication of danger:	-	
Contains:	Modified rosins.	
Risk phrases:	42/43 - May cause sensitisation by inhalation (flux fumes) and skin contact.	
Safety phrases:	23 - Do not breath fumes	
	24 - Avoid contact with skin	
	37 - Wear Suitable gloves.	

Section 16. Other Information		
Recommended uses and restrictions: Publications references:	Use only as directed. Compiled in accordance with CHIP 2 Regulations 1994. HSE Approved Code Of Practise, document L62. Dangerous Substances Directive 57/548/EEC as amended by directive 92/32/EEC Dangerous Preparations Directive 88/379/EE as amended by Directive 90/492/EEC The Health & Safety at Work Act 1974 The Control of Substances Hazardous to Health Regulations 1994 The Management of Health and Safety at Work Regulations 1992 The Management of Health and Safety at Work (Amendment) Regulations 1994	

Section 17. Revision Dates	
Revised Date / Initials:	July 2011/ VHM
Replacing:	All previous health and safety datasheets
Legend:	N/A = Not applicable or available at time of printing.
-	N/D = Not determined or not determinable.
	Est. = Estimated
combination with any other materials information and believed accurate an	hs on this sheet relate to the specific material designated and may not be valid for such material used in or in any process. The information is given in good faith and the best of Warton Metals Ltd knowledge, d reliable at the time of preparation. Nothing herein is to be construed as a guarantee, express or implied if the user to determine the applicability of this information or the suitability of the products for his own

2/2