



## Safety Data Sheet according to (EC) No 1907/2006

Page 1 of 10

Loctite 242

SDS No. : 173036  
V004.0

Revision: 26.01.2015

printing date: 12.03.2015

Replaces version from: 14.02.2014

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

Loctite 242

#### Contains:

Cumene hydroperoxide

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:

Adhesive

#### 1.3. Details of the supplier of the safety data sheet

Henkel Ltd

Wood Lane End

HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 1442 278000

Fax-no.: +44 1442 278071

ua-productsafety.uk@uk.henkel.com

#### 1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

### SECTION 2: Hazards identification

#### 2.1. Classification of the substance or mixture

##### Classification (CLP):

Serious eye irritation

Category 2

H319 Causes serious eye irritation.

Specific target organ toxicity - single exposure

Category 3

H335 May cause respiratory irritation.

Target organ: respiratory tract irritation

##### Classification (DPD):

Xi - Irritant

R36/37 Irritating to eyes and respiratory system.

#### 2.2. Label elements

##### Label elements (CLP):

**Hazard pictogram:**



**Signal word:**

Warning

**Hazard statement:**

H319 Causes serious eye irritation.  
H335 May cause respiratory irritation.

**Precautionary statement:**

\*\*\*For consumer use only: P101 If medical advice is needed, have product container or label at hand. P102 Keep out of reach of children. P501 Dispose of waste and residues in accordance with local authority requirements\*\*\*

**Precautionary statement:  
Prevention**

P261 Avoid breathing vapours.

**Precautionary statement:  
Response**

P337+P313 If eye irritation persists: Get medical advice/attention.

**Label elements (DPD):**

Xi - Irritant



**Risk phrases:**

R36/37 Irritating to eyes and respiratory system.

**Safety phrases:**

S25 Avoid contact with eyes.  
S26 In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.  
S51 Use only in well-ventilated areas.

**Additional labeling:**

For consumer use only: S2 Keep out of the reach of children.  
S46 If swallowed, seek medical advice immediately and show this container or label.

**2.3. Other hazards**

None if used properly.

**SECTION 3: Composition/information on ingredients**

**3.2. Mixtures**

**General chemical description:**

Anaerobic adhesive

**Declaration of the ingredients according to CLP (EC) No 1272/2008:**

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Cumene hydroperoxide 80-15-9	201-254-7	1 - < 2,5 %	Acute toxicity 4; Dermal H312 Specific target organ toxicity - repeated exposure 2 H373 Acute toxicity 4; Oral H302 Organic peroxides E H242 Acute toxicity 3; Inhalation H331 Skin corrosion 1B H314 Chronic hazards to the aquatic environment 2 H411
N,N-Diethyl-p-toluidine 613-48-9	210-345-0	0,1 - < 1 %	Acute toxicity 3; Oral H301 Acute toxicity 3; Dermal H311 Acute toxicity 3; Inhalation H331 Specific target organ toxicity - repeated exposure 2 H373 Chronic hazards to the aquatic environment 3 H412
1,4-Naphthalenedione 130-15-4	204-977-6	100 - < 250 PPM	Acute toxicity 3; Oral H301 Skin irritation 2; Dermal H315 Skin sensitizer 1; Dermal H317 Serious eye irritation 2 H319 Acute toxicity 1; Inhalation H330 Specific target organ toxicity - single exposure 3; Inhalation H335 Acute hazards to the aquatic environment 1 H400 Chronic hazards to the aquatic environment 1 H410 M factor: 10

For full text of the H - statements and other abbreviations see section 16 "Other information".  
Substances without classification may have community workplace exposure limits available.

**Declaration of ingredients according to DPD (EC) No 1999/45:**

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Cumene hydroperoxide 80-15-9	201-254-7	1 - < 2,5 %	T - Toxic; R23 Xn - Harmful; R21/22, R48/20/22 C - Corrosive; R34 O - Oxidizing; R7 N - Dangerous for the environment; R51/53
N,N-Diethyl-p-toluidine 613-48-9	210-345-0	0,1 - < 1 %	T - Toxic; R23/24/25 R33 R52/53
Cumene 98-82-8	202-704-5	0,1 - < 1 %	R10 Xn - Harmful; R65 Xi - Irritant; R37 N - Dangerous for the environment; R51/53
1,4-Naphthalenedione 130-15-4	204-977-6	100 - < 250 PPM	T+ - Very toxic; R25, R26 Xi - Irritant; R36/37/38, R43 N - Dangerous for the environment; R50/53

For full text of the R-Phrases indicated by codes see section 16 'Other Information'.

Substances without classification may have community workplace exposure limits available.

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

#### Inhalation:

Move to fresh air. If symptoms persist, seek medical advice.

#### Skin contact:

Rinse with running water and soap.  
Obtain medical attention if irritation persists.

#### Eye contact:

Rinse immediately with plenty of running water (for 10 minutes), seek medical attention from a specialist.

#### Ingestion:

Rinse mouth, drink 1-2 glasses of water, do not induce vomiting, consult a doctor.

### 4.2. Most important symptoms and effects, both acute and delayed

Causes serious eye irritation.

RESPIRATORY: Irritation, coughing, shortness of breath, chest tightness.

### 4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

## SECTION 5: Firefighting measures

### 5.1. Extinguishing media

#### Suitable extinguishing media:

Carbon dioxide, foam, powder

#### Extinguishing media which must not be used for safety reasons:

None known

### 5.2. Special hazards arising from the substance or mixture

In the event of a fire, carbon monoxide (CO) and carbon dioxide (CO<sub>2</sub>) can be released.

In case of fire, keep containers cool with water spray.

Oxides of carbon, oxides of nitrogen, irritating organic vapors.

### 5.3. Advice for firefighters

Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

Avoid skin and eye contact.  
Ensure adequate ventilation.

### 6.2. Environmental precautions

Do not let product enter drains.

### 6.3. Methods and material for containment and cleaning up

For small spills wipe up with paper towel and place in container for disposal.

For large spills absorb onto inert absorbent material and place in sealed container for disposal.

### 6.4. Reference to other sections

See advice in section 8

**SECTION 7: Handling and storage****7.1. Precautions for safe handling**

Use only in well-ventilated areas.  
Prolonged or repeated skin contact should be avoided to minimise any risk of sensitisation.  
Avoid skin and eye contact.  
See advice in section 8

**Hygiene measures:**

Good industrial hygiene practices should be observed.  
Do not eat, drink or smoke while working.  
Wash hands before work breaks and after finishing work.

**7.2. Conditions for safe storage, including any incompatibilities**

Store in original containers at 8-21°C (46.4-69.8°F) and do not return residual materials to containers as contamination may reduce the shelf life of the bulk product.

**7.3. Specific end use(s)**

Adhesive

**SECTION 8: Exposure controls/personal protection****8.1. Control parameters****Occupational Exposure Limits**

Valid for  
Great Britain

Ingredient	ppm	mg/m <sup>3</sup>	Type	Category	Remarks
PROPANE-1,2-DIOL, PARTICULATES 57-55-6		10	Time Weighted Average (TWA):		EH40 WEL
PROPANE-1,2-DIOL, TOTAL VAPOUR AND PARTICULATES 57-55-6	150	474	Time Weighted Average (TWA):		EH40 WEL
CUMENE 98-82-8	50	250	Short Term Exposure Limit (STEL):		EH40 WEL
CUMENE 98-82-8			Skin designation:	Can be absorbed through the skin.	EH40 WEL
CUMENE 98-82-8	25	125	Time Weighted Average (TWA):		EH40 WEL
CUMENE 98-82-8	50	250	Short Term Exposure Limit (STEL):	Indicative	ECLTV
CUMENE 98-82-8	20	100	Time Weighted Average (TWA):	Indicative	ECLTV

**Biological Exposure Indices:**

None

**8.2. Exposure controls:****Engineering controls:**

Ensure good ventilation/extraction.

**Respiratory protection:**

Ensure adequate ventilation.  
An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area  
Filter type: A

**Hand protection:**

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):

nitrile rubber (NBR;  $\geq 0.4$  mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):

nitrile rubber (NBR;  $\geq 0.4$  mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

**Eye protection:**

Wear protective glasses.

**Skin protection:**

Wear suitable protective clothing.

**SECTION 9: Physical and chemical properties****9.1. Information on basic physical and chemical properties**

Appearance	liquid blue
Odor	characteristic
Odour threshold	No data available / Not applicable
pH ( )	3 - 6
Initial boiling point	> 149 °C (> 300.2 °F)
Flash point	> 100 °C (> 212 °F)
Decomposition temperature	No data available / Not applicable
Vapour pressure (25 °C (77 °F))	< 0,1 mm hg
Vapour pressure (50 °C (122 °F))	< 300 mbar
Density ( )	1,08 g/cm <sup>3</sup>
Bulk density	No data available / Not applicable
Viscosity	No data available / Not applicable
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Solubility (qualitative) (Solvent: Water)	Not miscible
Solubility (qualitative) (Solvent: Acetone)	Miscible
Solidification temperature	No data available / Not applicable
Melting point	No data available / Not applicable
Flammability	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Explosive limits	No data available / Not applicable
Partition coefficient: n-octanol/water	No data available / Not applicable
Evaporation rate	No data available / Not applicable
Vapor density	No data available / Not applicable
Oxidising properties	No data available / Not applicable

**9.2. Other information**

No data available / Not applicable

**SECTION 10: Stability and reactivity****10.1. Reactivity**

Reacts with strong oxidants.

**10.2. Chemical stability**

Stable under recommended storage conditions.

**10.3. Possibility of hazardous reactions**

See section reactivity

**10.4. Conditions to avoid**

No decomposition if used according to specifications.

**10.5. Incompatible materials**

See section reactivity

**10.6. Hazardous decomposition products**

Irritating organic vapours.  
Oxides of carbon.

**SECTION 11: Toxicological information****11.1. Information on toxicological effects****General toxicological information:**

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation 1272/2008/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

**STOT-single exposure:**

May cause respiratory irritation.

**Oral toxicity:**

This material is considered to have low toxicity if swallowed.

**Skin irritation:**

Prolonged or repeated contact may cause skin irritation.

**Eye irritation:**

Causes serious eye irritation.

**Acute oral toxicity:**

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
Cumene hydroperoxide 80-15-9	LD50	550 mg/kg	oral		rat	

**Skin corrosion/irritation:**

Hazardous components CAS-No.	Result	Exposure time	Species	Method
Cumene hydroperoxide 80-15-9	corrosive		rabbit	Draize Test

**Germ cell mutagenicity:**

Hazardous components CAS-No.	Result	Type of study / Route of administration	Metabolic activation / Exposure time	Species	Method
Cumene hydroperoxide 80-15-9	positive	bacterial reverse mutation assay (e.g Ames test)	without		OECD Guideline 471 (Bacterial Reverse Mutation Assay)
Cumene hydroperoxide 80-15-9	negative	dermal		mouse	

**Repeated dose toxicity**

Hazardous components CAS-No.	Result	Route of application	Exposure time / Frequency of treatment	Species	Method
Cumene hydroperoxide 80-15-9		inhalation: aerosol	6 h/d 5 d/w	rat	

**SECTION 12: Ecological information****General ecological information:**

Cured Loctite products are typical polymers and do not pose any immediate environmental hazards.

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation 1272/2008/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

**12.1. Toxicity****Ecotoxicity:**

Do not empty into drains / surface water / ground water.

Hazardous components CAS-No.	Value type	Value	Acute Toxicity Study	Exposure time	Species	Method
Cumene hydroperoxide 80-15-9	LC50	3,9 mg/l	Fish	96 h	Oncorhynchus mykiss	OECD Guideline 203 (Fish, Acute Toxicity Test)
Cumene hydroperoxide 80-15-9	EC50	18 mg/l	Daphnia	48 h	Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)
Cumene hydroperoxide 80-15-9	ErC50	3,1 mg/l	Algae	72 h	Pseudokirchnerella subcapitata	OECD Guideline 201 (Alga, Growth Inhibition Test)
1,4-Naphthalenedione 130-15-4	EC50	0,011 mg/l	Algae	72 h	Dunaliella bioculata	OECD Guideline 201 (Alga, Growth Inhibition Test)

**12.2. Persistence and degradability****Persistence and Biodegradability:**

The product is not biodegradable.

Hazardous components CAS-No.	Result	Route of application	Degradability	Method
Cumene hydroperoxide 80-15-9		no data	0 %	OECD Guideline 301 B (Ready Biodegradability: CO2 Evolution Test)
1,4-Naphthalenedione 130-15-4		no data	0 - 60 %	OECD 301 A - F

**12.3. Bioaccumulative potential / 12.4. Mobility in soil****Mobility:**

Cured adhesives are immobile.

**Bioaccumulative potential:**

No data available.

**12.5. Results of PBT and vPvB assessment**



No data available.

#### 12.6. Other adverse effects

No data available.

### SECTION 13: Disposal considerations

#### 13.1. Waste treatment methods

Product disposal:

Dispose of in accordance with local and national regulations.

Contribution of this product to waste is very insignificant in comparison to article in which it is used

Disposal of uncleaned packages:

After use, tubes, cartons and bottles containing residual product should be disposed of as chemically contaminated waste in an authorised legal land fill site or incinerated.

Waste code

08 04 09 waste adhesives and sealants containing organic solvents and other dangerous substances

The valid EWC waste code numbers are source-related. The manufacturer is therefore unable to specify EWC waste codes for the articles or products used in the various sectors. The EWC codes listed are intended as a recommendation for users. We will be happy to advise you.

### SECTION 14: Transport information

#### 14.1. UN number

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

#### 14.2. UN proper shipping name

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

#### 14.3. Transport hazard class(es)

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

#### 14.4. Packaging group

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

#### 14.5. Environmental hazards

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

#### 14.6. Special precautions for user

Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.

#### 14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

not applicable

### SECTION 15: Regulatory information

#### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

VOC content < 3 %  
(1999/13/EC)

#### 15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

## SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

- R10 Flammable.
- R21/22 Harmful in contact with skin and if swallowed.
- R23 Toxic by inhalation.
- R23/24/25 Toxic by inhalation, in contact with skin and if swallowed.
- R25 Toxic if swallowed.
- R26 Very toxic by inhalation.
- R33 Danger of cumulative effects.
- R34 Causes burns.
- R36/37/38 Irritating to eyes, respiratory system and skin.
- R37 Irritating to respiratory system.
- R43 May cause sensitisation by skin contact.
- R48/20/22 Harmful: danger of serious damage to health by prolonged exposure through inhalation and if swallowed.
- R50/53 Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
- R51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
- R52/53 Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
- R65 Harmful: may cause lung damage if swallowed.
- R7 May cause fire.
- H242 Heating may cause a fire.
- H301 Toxic if swallowed.
- H302 Harmful if swallowed.
- H311 Toxic in contact with skin.
- H312 Harmful in contact with skin.
- H314 Causes severe skin burns and eye damage.
- H315 Causes skin irritation.
- H317 May cause an allergic skin reaction.
- H319 Causes serious eye irritation.
- H330 Fatal if inhaled.
- H331 Toxic if inhaled.
- H335 May cause respiratory irritation.
- H373 May cause damage to organs through prolonged or repeated exposure.
- H400 Very toxic to aquatic life.
- H410 Very toxic to aquatic life with long lasting effects.
- H411 Toxic to aquatic life with long lasting effects.
- H412 Harmful to aquatic life with long lasting effects.

### Further information:

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

**Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.**