

PCB TERMINAL BLOCKS

5.08mm Pitch Screwless 45° Terminal Blocks

- 2-7 pole solid block
- Moulded in grey UL94-V0 flame retardant PA
- 0.5-1.5mm² (22-16AWG) solid & stranded cable
-  approved


CSTB



SPECIFICATION

Rating	10A/250V UL=10A/300V, VDE&IMQ=10A/250V
Dielectric strength	≥4kV
Impulse withstand voltage	6kV
Working temperature	110°C
Moulding	UL 94 V0 flame retardant PA
Pin/terminal	Tinned, phosphor bronze
Spring	Zinc plated steel
Recommended PCB hole size	ø1.1mm

TYPE NO.	POLES	LENGTH
CSTB/2	2	10.16mm
CSTB/3	3	15.24mm
CSTB/4	4	20.32mm
CSTB/5	5	25.4mm
CSTB/6	6	30.48mm
CSTB/7	7	35.56mm



PCB
TERMINAL
BLOCKS

INTER-
CONNECTION

FUSES &
FUSE-
HOLDERS

LEDs &
INDICATORS

MINIATURE
SWITCHES

LIMIT &
SAFETY
SWITCHES

CONTROL
PRODUCTS

INTERFACE
MODULES &
SUPPORTS

RELAY
BASES

DIN RAIL
ENCLOSURES

BATTERIES

SOLAR
PANELS

TRANS-
FORMERS