

LOGO! AM2 RTD EXPAN. MODULE, PU: DC 12/24V, 2AI, -50 ...
+200 DEGR/C PT100/1000



Installation type/mounting	
Mounting	on 35 mm DIN rail, 2 spacing units wide
Supply voltage	
Rated value (DC)	
• 12 V DC	Yes; 10.8 V DC to 28.8 V DC
• 24 V DC	Yes; 10.8 V DC to 28.8 V DC
Analog inputs	
Number of analog inputs	2; 2 or 3 wire connection
Input ranges	
• Voltage	No
• Current	No
• Resistance thermometer	Yes; For PT100/PT1000 sensors
Input ranges (rated values), voltages	
• 0 to +10 V	No
Input ranges (rated values), currents	
• 0 to 20 mA	No
Input ranges (rated values), resistance thermometer	
• Pt 100	Yes

EMC	
Emission of radio interference acc. to EN 55 011	
• Limit class B, for use in residential areas	Yes; Radio interference suppression according to EN55011, Limit Value Class B
Degree and class of protection	
Degree of protection acc. to EN 60529	
• IP20	Yes
Standards, approvals, certificates	
CSA approval	Yes; C22.2 Number 142
UL approval	Yes; UL 508
FM approval	Yes; FM-Standards No. 3611, 3600, 3810 Class I, Division 2, Group A, B, C, D
developed in accordance with IEC 61131	Yes; EN 61131-2 (IEC 1131-2)
Marine approval	
• Marine approval	Yes; ABS, BV, DNV, GL, LRS, Class NK
Ambient conditions	
Ambient temperature during operation	
• min.	0 °C
• max.	55 °C
Dimensions	
Width	36 mm
Height	90 mm
Depth	53 mm
last modified:	24.02.2016