

LOGO! DM16 24R, EXP. MODULE, PU/I/O: 24V DC/24V DC/RELAY, 8 DI/8 DO, 4TE FOR LOGO! 8



Installation type/mounting

Mounting	on 35 mm DIN rail, 4 spacing units wide
----------	---

Supply voltage

Rated value (DC)	Yes
<ul style="list-style-type: none"> • 24 V DC 	
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V
Rated value (AC)	No
<ul style="list-style-type: none"> • 24 V AC 	

Digital inputs

Number of digital inputs	8
Input voltage	
<ul style="list-style-type: none"> • Type of input voltage 	DC
<ul style="list-style-type: none"> • for signal "0" 	< 5 V DC
<ul style="list-style-type: none"> • for signal "1" 	> 12 V DC
Input current	
<ul style="list-style-type: none"> • for signal "0", max. (permissible quiescent current) 	0.85 mA

• for signal "1", typ.	2 mA
Input delay (for rated value of input voltage)	
for standard inputs	
— at "0" to "1", max.	1.5 ms
— at "1" to "0", max.	1.5 ms
Digital outputs	
Number of digital outputs	8; Relays
Short-circuit protection	No
Controlling a digital input	Yes
Switching capacity of the outputs	
• on lamp load, max.	1 000 W
Output current	
• for signal "1" rated value	5 A
• for signal "1" minimum load current	100 mA
Parallel switching of two outputs	
• for uprating	No
Switching frequency	
• with resistive load, max.	2 Hz
• with inductive load, max.	0.5 Hz
• mechanical, max.	10 Hz
Relay outputs	
Switching capacity of contacts	
— with inductive load, max.	3 A
— with resistive load, max.	5 A
EMC	
Emission of radio interference acc. to EN 55 011	
• Limit class B, for use in residential areas	Yes
Degree and class of protection	
Degree of protection acc. to EN 60529	
• IP20	Yes
Standards, approvals, certificates	
CSA approval	Yes
UL approval	Yes
FM approval	Yes
developed in accordance with IEC 61131	Yes
according to VDE 0631	Yes
Marine approval	
• Marine approval	Yes
Ambient conditions	
Ambient temperature during operation	

- min.
- max.

0 °C
55 °C

Dimensions

Width	71.5 mm
Height	90 mm
Depth	58 mm

last modified: 24.02.2016