



Data

Electrical data

| | |
|-----------------|--------|
| Nominal voltage | 250 V |
| Reverse voltage | 1000 V |

Ratings per IEC/EN 60664-1

| | |
|---------------|-------|
| Rated current | 1.5 A |
|---------------|-------|

Connection data

| | |
|--------------------------------------|---|
| Connection technology | Push-in CAGE CLAMP® |
| Actuation type | Push-in Open Tool Slot |
| Connectable conductor materials | Copper |
| Nominal cross section | 4 mm ² |
| Solid conductor | 0.5 ... 6 mm ² / 20 ... 10 AWG |
| Solid conductor, push-in termination | 1.5 ... 6 mm ² / 14 ... 10 AWG |



| | |
|---|---|
| Fine-stranded conductor | 0.5 ... 6 mm ² / 20 ... 10 AWG |
| Fine-stranded conductor with ferrule, push-in termination, from | 1.5 mm ² / 18 AWG |
| Strip length | 11 ... 13 mm / 0.43 ... 0.51 Inch |
| Total number of connection points | 2 |
| Total number of potentials | 1 |
| Number of levels | 1 |
| Type of wiring | Front-entry wiring |

Geometrical Data

| | |
|---------------------------------------|----------------------|
| Width | 6.2 mm / 0.244 inch |
| Height from upper-edge of DIN-35 rail | 32.9 mm / 1.295 inch |
| Depth | 52.3 mm / 2.059 inch |

Mechanical data

| | |
|------------------|---------------------|
| Design | horizontal |
| Type of mounting | DIN-35 rail |
| Marking level | Center/side marking |

Material Data

| | |
|---------------------|----------------------|
| Color | gray |
| Insulating material | Polyamide 66 (PA 66) |
| Fire load | 0.142 MJ |
| Weight | 8.296 g |

Subject to changes.