



2-conductor ground terminal block; Ground supply terminal block

Item No.: 2016-7607



Marking

RoHS ✓
Compliant

Business data

Supplier	WAGO
Item no.	2016-7607
GTIN / EAN	4045454725112
Content	1

Notes

Safety information 1: DIN-35 rails with a height of 15 mm, must be used if the current load is higher than 76 A!


Technical data



Miscellaneous

Ratings per	IEC/EN 60947-7-2
Legend (ratings)	(III / 3) Overvoltage category III / Pollution degree 3
Type of wiring	Front-entry wiring
Total number of connection points	2
Total number of potentials	1

Technical data	
<i>Number of levels</i>	1
<i>Connection technology</i>	Push-in CAGE CLAMP®
<i>Actuation type</i>	Push-in
<i>Connectable conductor materials</i>	Copper
<i>Nominal cross section</i>	16 mm ²
<i>Solid conductor</i>	0.5 ... 16 mm ² / 20 ... 6 AWG
<i>Solid conductor, push-in termination</i>	2.5 ... 16 mm ² / 14 ... 6 AWG
<i>Fine-stranded conductor</i>	0.5 ... 25 mm ² / 20 ... 4 AWG
<i>Fine-stranded conductor with ferrule, push-in termination, f</i>	2.5 mm ² / 14 AWG
<i>Strip length</i>	18 ... 20 mm / 0.71 ... 0.79 Inch
<i>Width</i>	12 mm / 0.472 Inch
<i>Height from upper-edge of DIN-35 rail</i>	40.8 mm / 1.606 Inch
<i>Depth</i>	85.7 mm / 3.374 Inch
<i>Design</i>	angled
<i>Type of mounting</i>	Carrier rail 35 x 15
<i>Marking level</i>	Center/side marking
<i>Color</i>	green-yellow
<i>Insulating material</i>	Polyamide 66 (PA 66)
<i>Weight [g]</i>	43.566 [g]
<i>Product Family</i>	TOPJOB® S
<i>Main product function</i>	GND cond. term. block
<i>Product type</i>	Installation rail-mount terminal blocks

Images & drawings





Address

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Telefon: 0571/887-0

Fax: 0571/887-169

<http://www.wago.com>

© WAGO Kontakttechnik GmbH & Co. KG

Technische Änderungen und Irrtümer vorbehalten.