

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

### 1.1. Product identifier

Product form : Mixture  
Product name : FASTGLAS-R  
Product group : Unsaturated polyester

### 1.2. Relevant identified uses of the substance or mixture and uses advised against

#### 1.2.1. Relevant identified uses

Intended for general public  
Industrial/Professional use spec : Intended for general public  
Function or use category : Unsaturated polyester

#### 1.2.2. Uses advised against

No additional information available

### 1.3. Details of the supplier of the safety data sheet

U-POL LIMITED  
Denington Road, Wellingborough  
NN8 2QH - UK  
T +44 (0) 1933 230310 - F +44 (0) 1933 425797  
[technical.department@u-pol.com](mailto:technical.department@u-pol.com) - [www.u-pol.com](http://www.u-pol.com)

### 1.4. Emergency telephone number

Emergency number : +44 (0) 870 8200418

## SECTION 2: Hazards identification

### 2.1. Classification of the substance or mixture

#### Classification according to Regulation (EC) No. 1272/2008 [CLP]

Flammable liquids, Category 3	H226
Skin corrosion/irritation, Category 2	H315
Serious eye damage/eye irritation, Category 2	H319
Reproductive toxicity, Category 2	H361
Specific target organ toxicity — Repeated exposure, Category 1	H372

Full text of hazard classes and H-statements : see section 16

#### Adverse physicochemical, human health and environmental effects

No additional information available

### 2.2. Label elements

#### Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms (CLP) :



Signal word (CLP) :

Danger

Hazardous ingredients :

styrene

Hazard statements (CLP) :

H226 - Flammable liquid and vapour  
H315 - Causes skin irritation  
H319 - Causes serious eye irritation  
H361 - Suspected of damaging fertility or the unborn child  
H372 - Causes damage to organs (hearing organs) through prolonged or repeated exposure (Inhalation)

Precautionary statements (CLP) :

P102 - Keep out of reach of children  
P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking  
P261 - Avoid breathing fume, vapours

# FASTGLAS-R

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

P263 - Avoid contact during pregnancy/while nursing  
P280 - Wear eye protection, protective clothing, protective gloves  
P302+P352 - IF ON SKIN: Wash with plenty of water  
P305 - IF IN EYES: Wash with plenty of water and if necessary take medical advice

EUH-statements : EUH208 - Contains phthalic anhydride. May produce an allergic reaction

### 2.3. Other hazards

No additional information available

## SECTION 3: Composition/information on ingredients

### 3.1. Substance

Not applicable

### 3.2. Mixture

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
styrene	(CAS No) 100-42-5 (EC no) 202-851-5 (REACH-no) 01-2119457861-32	< 43	Flam. Liq. 3, H226 Acute Tox. 4 (Inhalation:dust,mist), H332 Skin Irrit. 2, H315 Eye Irrit. 2, H319 Repr. 2, H361d STOT RE 1, H372
phthalic anhydride	(CAS No) 85-44-9 (EC no) 201-607-5 (EC index no) 607-009-00-4	< 5	Acute Tox. 4 (Oral), H302 STOT SE 3, H335 Skin Irrit. 2, H315 Eye Dam. 1, H318 Resp. Sens. 1, H334 Skin Sens. 1, H317

Full text of H-statements: see section 16

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

First-aid measures general : Never give anything by mouth to an unconscious person. IF exposed or concerned: Get medical advice/attention.

First-aid measures after inhalation : Assure fresh air breathing. Allow the victim to rest. Remove victim to fresh air and keep at rest in a position comfortable for breathing. Call a POISON CENTER or doctor/physician if you feel unwell.

First-aid measures after skin contact : Remove/Take off immediately all contaminated clothing. Rinse skin with water/shower. Wash with plenty of soap and water. Wash contaminated clothing before reuse. If skin irritation occurs: Get medical advice/attention. Get medical advice/attention.

First-aid measures after eye contact : Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention. Get medical advice/attention.

First-aid measures after ingestion : Rinse mouth. Do NOT induce vomiting. Obtain emergency medical attention.

### 4.2. Most important symptoms and effects, both acute and delayed

Symptoms/injuries : Suspected of damaging the unborn child. Causes damage to organs (hearing organs) through prolonged or repeated exposure (Inhalation).

Symptoms/injuries after inhalation : Danger of serious damage to health by prolonged exposure through inhalation. Harmful if inhaled.

Symptoms/injuries after skin contact : Causes skin irritation.

Symptoms/injuries after eye contact : Causes serious eye irritation.

### 4.3. Indication of any immediate medical attention and special treatment needed

No additional information available

## SECTION 5: Firefighting measures

### 5.1. Extinguishing media

Suitable extinguishing media : Foam. Dry powder. Carbon dioxide. Water spray. Sand.

Unsuitable extinguishing media : Do not use a heavy water stream.

### 5.2. Special hazards arising from the substance or mixture

Fire hazard : Flammable liquid and vapour.

Explosion hazard : May form flammable/explosive vapour-air mixture.

# FASTGLAS-R

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

### 5.3. Advice for firefighters

- Firefighting instructions : Use water spray or fog for cooling exposed containers. Exercise caution when fighting any chemical fire. Prevent fire fighting water from entering the environment.
- Protection during firefighting : Do not enter fire area without proper protective equipment, including respiratory protection.

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

- General measures : Remove ignition sources. Use special care to avoid static electric charges. No open flames. No smoking.

#### 6.1.1. For non-emergency personnel

- Protective equipment : Safety glasses. Protective clothing. Gloves.
- Emergency procedures : Evacuate unnecessary personnel.

#### 6.1.2. For emergency responders

- Protective equipment : Equip cleanup crew with proper protection.
- Emergency procedures : Ventilate area.

### 6.2. Environmental precautions

Prevent entry to sewers and public waters. Notify authorities if liquid enters sewers or public waters.

### 6.3. Methods and material for containment and cleaning up

- For containment : Contain released substance, pump into suitable containers. Collect spillage.
- Methods for cleaning up : Soak up spills with inert solids, such as clay or diatomaceous earth as soon as possible. Collect spillage. Store away from other materials.

### 6.4. Reference to other sections

See Heading 8. Exposure controls and personal protection. For further information refer to section 13.

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

- Additional hazards when processed : Handle empty containers with care because residual vapours are flammable.
- Precautions for safe handling : Wash hands and other exposed areas with mild soap and water before eating, drinking or smoking and when leaving work. Provide good ventilation in process area to prevent formation of vapour. No open flames. No smoking. Take precautionary measures against static discharge. Use only non-sparking tools. Use only outdoors or in a well-ventilated area. Avoid breathing spray, vapours, fume. Obtain special instructions before use. Do not handle until all safety precautions have been read and understood. Do not breathe spray, vapours, fume.
- Hygiene measures : Wash hands thoroughly after handling. Do not eat, drink or smoke when using this product.

### 7.2. Conditions for safe storage, including any incompatibilities

- Technical measures : Proper grounding procedures to avoid static electricity should be followed. Ground/bond container and receiving equipment. Use explosion-proof electrical, Lighting equipment equipment.
- Storage conditions : Keep only in the original container in a cool, well ventilated place away from : Ignition sources, Heat sources, Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. Keep container tightly closed.
- Incompatible products : Strong bases. Strong acids. Oxidizing agent.
- Incompatible materials : Sources of ignition. Direct sunlight. Heat sources.
- Storage temperature : < 25 °C
- Storage area : Store in a well-ventilated place.
- Special rules on packaging : Keep only in original container.

### 7.3. Specific end use(s)

No additional information available

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

styrene (100-42-5)		
United Kingdom	Local name	Styrene
United Kingdom	WEL TWA (mg/m <sup>3</sup> )	430 mg/m <sup>3</sup>
United Kingdom	WEL TWA (ppm)	100 ppm
United Kingdom	WEL STEL (mg/m <sup>3</sup> )	1080 mg/m <sup>3</sup>
United Kingdom	WEL STEL (ppm)	250 ppm

# FASTGLAS-R

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

### 8.2. Exposure controls

Personal protective equipment : Avoid all unnecessary exposure. Gloves. Protective clothing. Safety glasses.

Materials for protective clothing:

Impermeable clothing

Hand protection:

Wear protective gloves

Eye protection:

Chemical goggles or safety glasses

Skin and body protection:

Wear suitable protective clothing

Respiratory protection:

In case of inadequate ventilation wear respiratory protection. Gas mask with filter type A



Other information : Do not eat, drink or smoke during use.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

Physical state	: Liquid
Appearance	: Liquid.
Colour	: amber.
Odour	: characteristic.
Odour threshold	: No data available
pH	: No data available
Relative evaporation rate (butylacetate=1)	: No data available
Melting point	: -30 °C
Freezing point	: No data available
Boiling point	: 145 °C
Flash point	: 31 °C
Auto-ignition temperature	: No data available
Decomposition temperature	: No data available
Flammability (solid, gas)	: Flammable liquid and vapour
Vapour pressure	: 6 hPa
Relative vapour density at 20 °C	: 3.6
Relative density	: No data available
Density	: $\approx 1.09 \text{ g/cm}^3$
Solubility	: Insoluble in water. Soluble in aromatic hydrocarbons.
Log Pow	: No data available
Viscosity, kinematic	: 477 - 624 mm <sup>2</sup> /s
Viscosity, dynamic	: 520 - 680 mPa.s
Explosive properties	: No data available
Oxidising properties	: No data available
Explosive limits	: No data available

### 9.2. Other information

No additional information available

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

No additional information available

### 10.2. Chemical stability

Flammable liquid and vapour. May form flammable/explosive vapour-air mixture.

# FASTGLAS-R

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

### 10.3. Possibility of hazardous reactions

Not established.

### 10.4. Conditions to avoid

Direct sunlight. Extremely high or low temperatures. Open flame. Overheating. Heat. Sparks.

### 10.5. Incompatible materials

Strong acids. Strong bases.

### 10.6. Hazardous decomposition products

fume. Carbon monoxide. Carbon dioxide. May release flammable gases.

## SECTION 11: Toxicological information

### 11.1. Information on toxicological effects

Acute toxicity	: Not classified
Skin corrosion/irritation	: Causes skin irritation.
Serious eye damage/irritation	: Causes serious eye irritation.
Respiratory or skin sensitisation	: Not classified
Additional information	: Based on available data, the classification criteria are not met
Germ cell mutagenicity	: Not classified Based on available data, the classification criteria are not met
Carcinogenicity	: Not classified
Additional information	: Based on available data, the classification criteria are not met
Reproductive toxicity	: Suspected of damaging fertility or the unborn child.
Specific target organ toxicity (single exposure)	: Not classified
Additional information	: Based on available data, the classification criteria are not met
Specific target organ toxicity (repeated exposure)	: Causes damage to organs (hearing organs) through prolonged or repeated exposure (Inhalation).
Aspiration hazard	: Not classified
Additional information	: Based on available data, the classification criteria are not met

#### FASTGLAS-R

Viscosity, kinematic	477 - 624 mm <sup>2</sup> /s
----------------------	------------------------------

Potential adverse human health effects and symptoms : Harmful if inhaled.

## SECTION 12: Ecological information

### 12.1. Toxicity

No additional information available

### 12.2. Persistence and degradability

#### FASTGLAS-R

Persistence and degradability	Not established.
-------------------------------	------------------

### 12.3. Bioaccumulative potential

#### FASTGLAS-R

Bioaccumulative potential	Not established.
---------------------------	------------------

### 12.4. Mobility in soil

No additional information available

### 12.5. Results of PBT and vPvB assessment

No additional information available

### 12.6. Other adverse effects

Additional information : Avoid release to the environment

## SECTION 13: Disposal considerations

### 13.1. Waste treatment methods

Regional legislation (waste)	: Disposal must be done according to official regulations.
Waste disposal recommendations	: Dispose in a safe manner in accordance with local/national regulations. Dispose of contents/container to Dispose in a safe manner in accordance with local/national regulations.

# FASTGLAS-R

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Additional information : Handle empty containers with care because residual vapours are flammable.  
Ecology - waste materials : Avoid release to the environment.

### SECTION 14: Transport information

In accordance with ADR / RID / IMDG / IATA / ADN

#### 14.1. UN number

UN-No. (ADR) : Not applicable  
UN-No. (IMDG) : 1866  
UN-No. (IATA) : 1866  
UN-No. (ADN) : Not applicable  
UN-No. (RID) : Not applicable

#### 14.2. UN proper shipping name

Proper Shipping Name (ADR) : Not applicable  
Proper Shipping Name (IMDG) : RESIN SOLUTION  
Proper Shipping Name (IATA) : Resin solution  
Proper Shipping Name (ADN) : Not applicable  
Proper Shipping Name (RID) : Not applicable  
Transport document description (IMDG) : UN 1866 RESIN SOLUTION, 3, III  
Transport document description (IATA) : UN 1866 Resin solution, 3, III

#### 14.3. Transport hazard class(es)

##### ADR

Transport hazard class(es) (ADR) : Not applicable

##### IMDG

Transport hazard class(es) (IMDG) : 3  
Danger labels (IMDG) : 3



##### IATA

Transport hazard class(es) (IATA) : 3  
Hazard labels (IATA) : 3



##### ADN

Transport hazard class(es) (ADN) : Not applicable

##### RID

Transport hazard class(es) (RID) : Not applicable

#### 14.4. Packing group

Packing group (ADR) : Not applicable  
Packing group (IMDG) : III  
Packing group (IATA) : III  
Packing group (ADN) : Not applicable  
Packing group (RID) : Not applicable

#### 14.5. Environmental hazards

Dangerous for the environment : No  
Marine pollutant : No

# FASTGLAS-R

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Other information : No supplementary information available

### 14.6. Special precautions for user

#### - Overland transport

Not applicable

#### - Transport by sea

Special provisions (IMDG) : 223, 955  
Limited quantities (IMDG) : 5 L  
Excepted quantities (IMDG) : E1  
Packing instructions (IMDG) : P001, LP01  
Special packing provisions (IMDG) : PP1  
IBC packing instructions (IMDG) : IBC03  
Tank instructions (IMDG) : T2  
Tank special provisions (IMDG) : TP1  
EmS-No. (Fire) : F-E  
EmS-No. (Spillage) : S-E  
Stowage category (IMDG) : A  
Properties and observations (IMDG) : Miscibility with water depends upon the composition.

#### - Air transport

PCA Excepted quantities (IATA) : E1  
PCA Limited quantities (IATA) : Y344  
PCA limited quantity max net quantity (IATA) : 10L  
PCA packing instructions (IATA) : 355  
PCA max net quantity (IATA) : 60L  
CAO packing instructions (IATA) : 366  
CAO max net quantity (IATA) : 220L  
Special provisions (IATA) : A3  
ERG code (IATA) : 3L

#### - Inland waterway transport

Not applicable

#### - Rail transport

Not applicable

### 14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Not applicable

## SECTION 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

#### 15.1.1. EU-Regulations

Contains no REACH substances with Annex XVII restrictions  
Contains no substance on the REACH candidate list  
Contains no REACH Annex XIV substances

#### 15.1.2. National regulations

No additional information available

### 15.2. Chemical safety assessment

No chemical safety assessment has been carried out

## SECTION 16: Other information

Data sources : REGULATION (EC) No 1272/2008 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006.

Other information : None.

Full text of H- and EUH-statements:

# FASTGLAS-R

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Acute Tox. 4 (Inhalation:dust,mist)	Acute toxicity (inhalation:dust,mist) Category 4
Acute Tox. 4 (Oral)	Acute toxicity (oral), Category 4
Eye Dam. 1	Serious eye damage/eye irritation, Category 1
Eye Irrit. 2	Serious eye damage/eye irritation, Category 2
Flam. Liq. 3	Flammable liquids, Category 3
Repr. 2	Reproductive toxicity, Category 2
Repr. 2	Reproductive toxicity, Category 2
Resp. Sens. 1	Sensitisation — Respiratory, Category 1
Skin Irrit. 2	Skin corrosion/irritation, Category 2
Skin Sens. 1	Sensitisation — Skin, Category 1
STOT RE 1	Specific target organ toxicity — Repeated exposure, Category 1
STOT SE 3	Specific target organ toxicity — Single exposure, Category 3, Respiratory tract irritation
H226	Flammable liquid and vapour
H302	Harmful if swallowed
H315	Causes skin irritation
H317	May cause an allergic skin reaction
H318	Causes serious eye damage
H319	Causes serious eye irritation
H332	Harmful if inhaled
H334	May cause allergy or asthma symptoms or breathing difficulties if inhaled
H335	May cause respiratory irritation
H361	Suspected of damaging fertility or the unborn child
H361d	Suspected of damaging the unborn child
H372	Causes damage to organs through prolonged or repeated exposure
EUH208	Contains . May produce an allergic reaction

Flam. Liq. 3	H226	On basis of test data
Skin Irrit. 2	H315	Calculation method
Eye Irrit. 2	H319	Calculation method
Repr. 2	H361	Calculation method
STOT RE 1	H372	Calculation method

UPOL SDS EU (no product code)

*The information contained within this Safety Data Sheet (SDS) is believed to be correct as of the date issued however it is subject to change from time to time. It does not purport to be all inclusive or exhaustive and shall only be used as a guide. U-POL makes no warranties, expressed or implied, including but not limited to, any implied warranty of fitness for a given purpose or usage. It is the Buyers responsibility to ensure the suitability of the products for their own use and to check the information is up to date. U-POL cannot be held responsible for the suitability of use for any of its products, considering the wide range of factors such as application, substrates and handling methods. Since these conditions of use are outside of our control, the company shall not be held liable for any damage resulting from handling or from contact with the product detailed. Moreover, addition of reducers, hardeners or other additives over and above U-POL's recommendations for use, may substantially alter the composition and hazards of the product. U-POL data sheets are available via the U-POL website at WWW.U-POL.COM.*