

SAFETY DATA SHEET

High Viscosity Peelable Coating Mask

SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1. Product identifier

Product name High Viscosity Peelable Coating Mask
Product No. PCM-HV, EPCM250HV, EPCM310HV, ZE

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Manufacture of electrical equipment
Uses advised against No specific uses advised against are identified.

1.3. Details of the supplier of the safety data sheet

Supplier ELECTROLUBE. A division of HK
 WENTWORTH LTD
 ASHBY PARK, COALFIELD WAY,
 ASHBY DE LA ZOUCH, LEICESTERSHIRE
 LE65 1JR
 UNITED KINGDOM
 +44 (0)1530 419600
 +44 (0)1530 416640
 info@hkw.co.uk

1.4. Emergency telephone number

+44 (0)1530 419600 between 8.30am - 5.00pm GMT Mon – Fri

SECTION 2: HAZARDS IDENTIFICATION

2.1. Classification of the substance or mixture

Classification (EC 1272/2008)	Physical and Chemical Hazards	Not classified.
	Human health	Not classified.
	Environment	Not classified.
	Classification (1999/45/EEC)	Not classified.

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

2.2. Label elements

Label In Accordance With (EC) No. 1272/2008
 No pictogram required.

2.3. Other hazards

Not Classified as PBT/vPvB by current EU criteria.

SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

3.2. Mixtures

High Viscosity Peelable Coating Mask

AMMONIA ...%		<0.5%
CAS-No.: 1336-21-6	EC No.: 215-647-6	
Classification (EC 1272/2008) Skin Corr. 1B - H314 STOT SE 3 - H335 Aquatic Acute 1 - H400	Classification (67/548/EEC) C;R34 N;R50	

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

Composition Comments

Ingredients not listed are classified as non-hazardous or at a concentration below reportable levels.

SECTION 4: FIRST AID MEASURES

4.1. Description of first aid measures

Inhalation

Move the exposed person to fresh air at once. Provide rest, warmth and fresh air.

Ingestion

Rinse mouth thoroughly. Get medical attention.

Skin contact

Wash the skin immediately with soap and water. Get medical attention if irritation persists after washing.

Eye contact

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes. Get medical attention if any discomfort continues.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact

No specific symptoms noted.

4.3. Indication of any immediate medical attention and special treatment needed

Treat Symptomatically.

SECTION 5: FIREFIGHTING MEASURES

5.1. Extinguishing media

Extinguishing media

This product is not flammable. Use fire-extinguishing media appropriate for surrounding materials.

5.2. Special hazards arising from the substance or mixture

Hazardous combustion products

None under normal conditions.

Unusual Fire & Explosion Hazards

No unusual fire or explosion hazards noted.

5.3. Advice for firefighters

Special Fire Fighting Procedures

No specific fire fighting procedure given.

SECTION 6: ACCIDENTAL RELEASE MEASURES

6.1. Personal precautions, protective equipment and emergency procedures

Wear protective clothing as described in Section 8 of this safety data sheet.

6.2. Environmental precautions

Do not discharge onto the ground or into water courses.

6.3. Methods and material for containment and cleaning up

Absorb in vermiculite, dry sand or earth and place into containers. Flush with plenty of water to clean spillage area.

6.4. Reference to other sections

High Viscosity Peelable Coating Mask

Wear protective clothing as described in Section 8 of this safety data sheet. See section 11 for more detailed information on health effects and symptoms. Collect and dispose of spillage as indicated in section 13.

SECTION 7: HANDLING AND STORAGE

7.1. Precautions for safe handling

Avoid spilling, skin and eye contact.

7.2. Conditions for safe storage, including any incompatibilities

Store in tightly closed original container in a dry, cool and well-ventilated place. Keep in original container.

7.3. Specific end use(s)

The identified uses for this product are detailed in Section 1.2.

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1. Control parameters

8.2. Exposure controls

Process conditions

Use engineering controls to reduce air contamination to permissible exposure level. Provide eyewash station.

Engineering measures

No particular ventilation requirements.

Hand protection

Use suitable protective gloves if risk of skin contact. The most suitable glove must be chosen in consultation with the gloves supplier, who can inform about the breakthrough time of the glove material. Gloves should conform to EN374

Eye protection

If risk of splashing, wear safety goggles or face shield. EN166

Other Protection

Wear appropriate clothing to prevent any possibility of skin contact.

Hygiene measures

Wash hands at the end of each work shift and before eating, smoking and using the toilet. Wash promptly if skin becomes wet or contaminated. When using do not eat, drink or smoke.

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

9.1. Information on basic physical and chemical properties

Appearance	Liquid
Colour	Cream.
Odour	Characteristic.
Relative density	1.2 @ 20 °c (68 F)
Bulk Density	1200 kg/m ³
pH-Value, Conc. Solution	10-11
Viscosity	40.000 - 60.000 cP @ 20 °c (68 F)
Flash point (°C)	
Will not flash.	

9.2. Other information

None.

SECTION 10: STABILITY AND REACTIVITY

10.1. Reactivity

No specific reactivity hazards associated with this product.

10.2. Chemical stability

Stable under normal temperature conditions.

10.3. Possibility of hazardous reactions

Not known.

High Viscosity Peelable Coating Mask

Hazardous Polymerisation

Will not polymerise.

10.4. Conditions to avoid

Avoid excessive heat for prolonged periods of time.

10.5. Incompatible materials

Materials To Avoid

No specific, or groups of materials are likely to react to produce a hazardous situation.

10.6. Hazardous decomposition products

No hazardous decomposition products.

SECTION 11: TOXICOLOGICAL INFORMATION

11.1. Information on toxicological effects

Other Health Effects

This substance has no evidence of carcinogenic properties.

Ingestion

Rinse mouth thoroughly. Get medical attention.

Skin contact

Wash the skin immediately with soap and water. Get medical attention if irritation persists after washing.

Eye contact

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes. Get medical attention if any discomfort continues.

Health Warnings

No specific health warnings noted. No specific acute or chronic health impact noted, but this chemical may still have adverse impact on human health, either in general or on certain individuals with pre-existing or latent health problems.

Toxicological information on ingredients.

AMMONIA ...% (CAS: 1336-21-6)

Toxic Dose 1 - LD 50

350 mg/kg (oral rat)

SECTION 12: ECOLOGICAL INFORMATION

Ecotoxicity

Not regarded as dangerous for the environment.

12.1. Toxicity

Acute Fish Toxicity

Not considered toxic to fish.

Acute Toxicity - Fish

No information required.

Acute Toxicity - Aquatic Invertebrates

No information required.

Acute Toxicity - Aquatic Plants

No information required.

Acute Toxicity - Microorganisms

No information required.

Ecological information on ingredients.

AMMONIA ...% (CAS: 1336-21-6)

LC 50, 96 Hrs, Fish mg/l

<1

EC 50, 48 Hrs, Daphnia, mg/l

89

12.2. Persistence and degradability

High Viscosity Peelable Coating Mask

Degradability

There are no data on the degradability of this product.

12.3. Bioaccumulative potential

Bioaccumulative potential

No data available on bioaccumulation.

12.4. Mobility in soil

Mobility:

The product is water soluble and may spread in water systems.

12.5. Results of PBT and vPvB assessment

This product does not contain any PBT or vPvB substances.

12.6. Other adverse effects

Not known.

SECTION 13: DISPOSAL CONSIDERATIONS

13.1. Waste treatment methods

Dispose of waste and residues in accordance with local authority requirements.

SECTION 14: TRANSPORT INFORMATION

General	The product is not covered by international regulation on the transport of dangerous goods (IMDG, IATA, ADR/RID).
Road Transport Notes	Not Classified
Rail Transport Notes	Not classified.
Sea Transport Notes	Not classified.
Air Transport Notes	Not classified.

14.1. UN number

No information required.

14.2. UN proper shipping name

No information required.

14.3. Transport hazard class(es)

No information required.

ADR/RID/ADN Class Not classified for transportation.

Transport Labels

No transport warning sign required.

14.4. Packing group

No information required.

14.5. Environmental hazards

Environmentally Hazardous Substance/Marine Pollutant

No.

14.6. Special precautions for user

No information required.

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

No information required.

SECTION 15: REGULATORY INFORMATION

High Viscosity Peelable Coating Mask

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Statutory Instruments

The Chemicals (Hazard Information and Packaging for Supply) Regulations 2009 (S.I. 2009 No. 716). Control of Substances Hazardous to Health.

Guidance Notes

Workplace Exposure Limits EH40.

EU Legislation

Commission Directive 2000/39/EC of 8 June 2000 establishing a first list of indicative occupational exposure limit values in implementation of Council Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work.

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, including amendments.

Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006 with amendments.

Authorisations (Title VII Regulation 1907/2006)

No specific authorisations are noted for this product.

Restrictions (Title VIII Regulation 1907/2006)

No specific restrictions of use are noted for this product.

15.2. Chemical Safety Assessment

No chemical safety assessment has been carried out.

SECTION 16: OTHER INFORMATION

Issued By Helen O'Reilly

Revision Date APRIL 2013

Revision 2

SDS No. 10824

Risk Phrases In Full

R34 Causes burns.
R37 Irritating to respiratory system.
NC Not classified.
R50 Very toxic to aquatic organisms.

Hazard Statements In Full

H314 Causes severe skin burns and eye damage.
H335 May cause respiratory irritation.
H400 Very toxic to aquatic life.

Disclaimer

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.