

EVF2S7P44

EVlink PARKING Floor Standing 7KW 2xT2 with Shutter EV CHARGING STATION



Main

Range	EVlink
Product name	EVlink parking
Product or component type	Charging station
Device short name	EVF2
Poles description	1P + N for control circuit 1P + N for power circuit
Mounting mode	Floor-standing
Offer type	Standard
[Us] rated supply voltage	230 V AC 50/60 Hz power circuit 220...240 V AC 50/60 Hz control circuit
Earthing system	IT TN TT
Socket number	2
Socket-outlet type	Right side : T2 with shutter / silver plated contacts Left side : T2 with shutter / silver plated contacts
Supply current	32 A for T2 with shutter
Nominal output power	7 kW for T2 with shutter

Complementary

Control type	2 red push-button function : stop 2 green illuminated push-button function : start/unlock flap
Local signalling	2 green LED flashing on side device function: on charge 2 green LED on front device function: available 2 orange LED on front device function: reserved 2 red LED on front device function: not operational
Communication port protocol	OCPP 1.5
Operating mode	Standalone Clustured architecture
Function available	Load management Charge detail records Circuit breaker status Postponed charge User privilege configuration Diagnosis capabilities
Web server	Embedded
Ethernet service	Configuration via web server
Standards	IEC 61851-1 IEC 61851-22
Product certifications	CE CB EV Ready ZE Ready
Height	1146 mm
Width	413 mm
Depth	220 mm
Product weight	50 kg
Colour	White RAL 9003 on front device Grey RAL 7016 on side device

Environment

IP degree of protection	IP54 off load conforming to IEC 61851-1 IP54 on load conforming to IEC 61851-1
-------------------------	---

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

IK degree of protection	IK10 charging station conforming to IEC 61851-22 IK10 socket-outlet conforming to IEC 61851-22
ambient air temperature for operation	-25...50 °C conforming to IEC 61851-22
ambient air temperature for storage	-40...80 °C
operating altitude	0...2000 m conforming to IEC 61851-22
relative humidity	<= 95 %

Offer Sustainability

Sustainable offer status	Not Green Premium product
--------------------------	---------------------------