



## Tork Alcohol Foam Hand Sanitiser Transparent



Article	590101
Volume	47 ml
No of doses	≈117
Colour	Transparent

Help to prevent infections with leave-on Tork Alcohol Foam Hand Sanitiser with 75% denatured alcohol (w/w). It's ideal for sanitising hands when no water is available, especially in offices and other public areas. Conforms with the European Standard EN1500. This personal pocket bottle encourages frequent use.



[www.tork.co.uk](http://www.tork.co.uk)

An effective sanitiser against a variety of bacteria – conforms with EN1500

Rich and easy to spread, this perfume- and colour-free foam is gentle to the skin

A convenient pocket bottle, always in reach

Use Biocides Safely. Always read the label and product information before use

## Shipping data

	Consumer unit	Transport unit	Pallet
<b>EAN</b>	7322540740974	7322540740981	7322540780246
<b>Pieces</b>	1	12	6624
<b>Consumer units</b>	-	12	6624
<b>Height</b>	130 mm	140 mm	1281 mm
<b>Width</b>	34 mm	115 mm	1000 mm
<b>Length</b>	34 mm	145 mm	1200 mm
<b>Volume</b>	0.2 dm3	2.3 dm3	1.3 m3
<b>Net weight</b>	40 g	0.5 kg	264.96 kg
<b>Gross weight</b>	68 g	0.9 kg	510.6 kg
<b>Packing material</b>	Plastic bottle	Carton	-

## Alternative products



**420103**

**520101**

**511103**

## Contact

SCA Hygiene Products UK Ltd  
 Southfields Road  
 Dunstable  
 Bedfordshire  
 LU6 3EJ  
[customer.servicesafh@sca.com](mailto:customer.servicesafh@sca.com)  
 Tel 01582 677570  
 Fax 01582 677580

## Technical data

### Ingredients

#### Active ingredients:

65% (w/w) Ethanol, 10% (w/w) Propan-1-ol, < 0.1% (w/w) Propan-2-ol

#### Other ingredients:

Aqua, Propyl Alcohol, Bis-PEG 12 Dimethicone, Coco-Glucoside, Glyceryl Oleate, PEG-200 Hydrogenated Glyceryl Palmate, PEG-7 Glyceryl Cocate, Behentrimonium Chloride, Dihydroxypropyl PEG-5 Linoleammonium Chloride, Isopropyl Alcohol

### Method Of Use

Ensure hands are clean and dry before use.

#### For general hygiene:

Apply 1-2 doses (entire hand should be wetted) and rub well until dry (15-30 seconds).

#### For disinfection according to EN1500:

Apply 3 ml, spread evenly and rub for 30 seconds until dry.

### Shelf Life

Expiration date of 36 months after production date is printed on inner packaging. Store in original container. Protect product from Excessive sunlight. Avoid temperature extremes and store between 4°C and 30°C.

### Handling Instructions

Use disinfectants safely. Always read the label and product information before use. Avoid contact with eyes. In case of contact with eyes, rinse immediately with plenty of water (for at least 10 minutes) and seek medical advice. For more information, please refer to the Safety Data Sheet.

### Regulatory Compliance

The biocide products commercialized under the Tork brand are in compliance with the Biocidal Product Regulation (EU) No 528/2012 and are approved for human hygiene purposes. The products are registered and authorized in the respective countries, where the products are sold. The products are in conformity with the REACH regulation (EC) No. 1907/2006 and its amendments. All non-biocidal ingredients are in compliance with the Cosmetic Regulation (EC) No. 1223/2009 and are considered as safe for human health when used under normal or reasonably foreseeable conditions. The biocide products are manufactured in accordance with good manufacturing practices (GMP).

### Registrations Biocides

DE: N-58695  
DK: PR.Nr. 2417572  
EE: 1306/15  
FI: 427284  
LUX: 128/16/L  
LT: Nr. 11 (11.1)-(A-01VNO601554-15-95)-BSV-7043  
LV: LV0203 2015/1602  
NO: 320166  
SE: 535728-0  
CH: CHZN4305  
SK: bio/124/D/15/CCHLP  
IRL: Pcs no - 98122

### Certification

ISO 2271 (Good Manufacturing Practice)  
ISO 9001 & 13485 (Quality Management System)  
ISO 14001 (Environmental Management System)

### Safety Data Sheet

For safe use and handling of the products, please follow the recommendations on the Safety Data Sheets. These are available on the Tork website in all required local versions according to actual legal requirements for these regions (e.g. according to CLP for Europe).

Microbiological tests				
Effective against	Test method	Test conditions	Test durations	Test organisms
Bacteria	EN1500: hygienic hand rub	3 ml	30 sec	Escherichia coli K12 NCTC 10538
	EN 1276: Bactericidal Activity for food, industrial, domestic and institutional areas	Dirty conditions	30 sec	Staphylococcus aureus, Enterococcus hirae, Escherichia coli & Pseudomonas aeruginosa
Yeast And Fungi	EN 1275: Basic Fungicidal or Basic Yeastcidal Activity		1 minute	Candida albicans, Aspergillus niger
	EN 1650: Fungicidal activity in food, industrial, domestic and institutional areas		15 minutes	Candida albicans, Aspergillus brasiliensis
Mycrobacteria	EN 14348: Tuberculocidal activity in the medical area	Clean conditons	30 sec	Mycobaterium terrae
Viruses	Product is virucidal against Avian Influenza Virus H3N8 and H3N2, and Human Rhinovirus in 30 seconds (modified EN14476). Product is virucidal against human Rotavirus in 30 seconds (following the guideline of DW and RKI).			
Amercian Standards	In vitro time kill bacteria		15 sec	Possesses rapid germicidal activity against 29 bacteria using an exposure time of 15 second
	In vitro time kill yeast		15 sec	Candida albicans, Candida tropicalis
	In vitro time kill virus		30 sec	Herpes Simplex type 1, HIV, Influenza type H1N1 (Swine)