



### Main

Range	EVlink
Product name	EVlink Wallbox
Product or component type	Charging station
Device short name	EVH2
Poles description	3P + N
Mounting mode	Wall-mounted
Offer type	Standard
Nominal output power	22 kW 32 A
Socket outlet type	T2
Socket number	1
Output type	Socket-outlet T2
Access control system	Key

### Complementary

[Us] rated supply voltage	380...415 V AC 50/60 Hz
Earthing system	TN TT
Number of inputs	1
Input type	Contact for power limitation Contact for delayed charging
Control type	1 white button, function: stop/restart Green button, function: cable unlocking
Local signalling	1 multi-colour LED, function: status indication
Height	480 mm
Width	331.5 mm
Depth	170 mm
Product weight	5.6 kg
Colour	Grey RAL 7016

White RAL 9003

Standards	IEC 61851-22 IEC 62196-2 IEC 62196-1 IEC 61851-1
Product certifications	CB CE

## Environment

IP degree of protection	IP54 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262
Ambient air temperature for operation	-30...50 °C
Ambient air temperature for storage	-40...80 °C
Relative humidity	5...95 %

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1514 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Available