



Main

Range	Linergy
Product name	Linergy FM
IP degree of protection	IPxx B
Product or component type	Device feeder
Product compatibility	Spacial enclosures

Complementary

Mounting support	DIN rail Plain backplate Slotted backplate
Installed device	Modular device
Poles description	3P + N
[Ue] rated operational voltage	690 V AC
[Ui] rated insulation voltage	750 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	8 kV
[Ie] rated operational current	200 A
[Ipk] rated peak withstand current	20 kA
I <sup>2</sup> t on activation	6700000 A <sup>2</sup> .s
Connections - terminals	Supply : crimped lug 50 mm <sup>2</sup> Supply : flexible bars, 20 x 3 mm Distribution : quick-connect terminal strips (phase) , 12 x 4...10 mm <sup>2</sup> (flexible) Distribution : quick-connect terminal strips (phase) , 12 x 4...10 mm <sup>2</sup> (rigid) Distribution : quick-connect terminal strips (neutral) , 18 x 4...10 mm <sup>2</sup> (flexible) Distribution : quick-connect terminal strips (neutral) , 18 x 4...10 mm <sup>2</sup> (rigid)
Total number of 18 mm modules	24
Product weight	1.6 kg
Colour	Anthracite grey RAL 7016

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

Standards	IEC 61439-1 inside Prisma IEC 61439-2 inside Prisma IEC 60947-7-1
Product certifications	ASEFA

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0813 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------