


Data Sheet

Type Number:	4075
Designation IEC:	SR 44
System:	Silver oxide / Zinc / KOH - Electrolyte
Nominal Voltage [V]:	1,55
Typical Capacity C [mAh]:	145
Load 5,6 kOhm, at 20 °C down to 1,2 V	
Weight, approx [g]:	2,4
Volume [ccm]:	0,51
Coding:	Manufacturing Quarter/Year by Letter Code
Temperature Ranges [°C]:	min. max.
Storage:	-10 65
Discharge:	-10 65
Dimensions [mm]:	min. max.
Diameter :	11,25 11,6
Height [A/B]:	5 5,4
Segment:	Watch / High Drain
Main Applications:	Photo Electronic



Typical Capacities (at 20° C):

Discharge Type:	Load	End Voltage	1,2 V
Continuous	5600	Time:	545 h
24h/d, 7d/w		Capacity [mAh]:	145
Current [µA]:	275	Energy [mWh]:	215